

600V SEOPRENE® SEOOW Power Cord Non-UL/CSA with Black Jacket 105°C. Silicone-Free. MSHA Approved

600 Volt, 105°C Flexible Cord. Premium Oil Resistance, Sunlight, Water Resistance and Flame Retardant. Non UL / Non CSA Listed.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Class K stranded bare copper per ASTM B-174
- Insulation:** Heat, moisture and oil resistant TPE
- Filler:** Non-wicking polypropylene fillers, with a tissue-paper separator wrapped around the assembly
- Jacket:** Black TPE (other colors available upon request)

APPLICATIONS AND FEATURES:

Southwire Type SEOOW Flexible Cords are permitted for indoor and outdoor temporary power uses, portable industrial machinery and compressors. Type SEOOW Cords are suitable for use in temperatures between -50°C to maximum 105°C wet or dry.

SPECIFICATIONS:

- MSHA Approved
- RoHS-3 Complies with European Directive 2015/863

SAMPLE PRINT LEGEND:

SOUTHWIRE{R} SEOPRENE{R} CORD X/C X AWG (X.XX{mm²}) SEOOW 600V -50{D}C TO 105{D}C WATER RESISTANT

PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.

Table 1 – Weights and Measurements

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Insul. Color	Jacket Color
		AWG/ Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp		
550563	22553	2	5	119	45	170	1.395	1615	64	BK,WE,RD,GN,OE	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.



Table 2 – Weights and Measurements (Metric)

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity *	Insul. Color	Jacket Color
550563	22553	2	5	119	1.14	4.32	35.43	2403	64	BK,WE,RD,GN,OE	BK
		AWG/ Kcmil	No.	No.	mm	mm	mm	kg/km	Amp		

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

