



# 600V SEOPRENE® SE00W Power Cord Non-UL/CSA with Black Jacket 105°C. Silicone-Free. MSHA Approved

600 Volt, 105°C Flexible Cord. Premium Oil Resistance, Sunlight, Water Resistance and Flame Retardant. Non UL / Non CSA Listed




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Class K stranded bare copper per ASTM B-174
- Insulation:** Heat, moisture and oil resistant TPE
- Filler:** Non-wicking polypropylene fillers, with a tissue-paper separator wrapped around the assembly
- Jacket:** Black TPE (other colors available upon request)

## APPLICATIONS AND FEATURES:

Southwire Type SE00W Flexible Cords are permitted for indoor and outdoor temporary power uses, portable industrial machinery and compressors. Type SE00W Cords are suitable for use in temperatures between -50°C to maximum 105°C.

## SPECIFICATIONS:

- MSHA Approved
- RoHS-3 Complies with European Directive 2015/863

## SAMPLE PRINT LEGEND:

SOUTHWIRE® SEOPRENE® CORD 2/C 8 AWG (7.85mm<sup>2</sup>) SE00W 600V - 50C TO 105C WATER RESISTANT

## PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.

**Table 1 – Weights and Measurements**

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Insul. Color	Jacket Color
		AWG/ Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp		
550405	22421	6	4	96	45	100	0.892	555	36	BK,WE,RD,GN	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

**Table 2 – Weights and Measurements (Metric)**

550405	22421	6	4	96	1.14	2.54	22.66	826	36	BK,WE,RD,GN	BK
--------	-------	---	---	----	------	------	-------	-----	----	-------------	----

\* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.





**Color Code**

# of Conductor	Color Sequence
2	Black, White
3	Black, White, Green
4	Black, White, Red, Green
5	Black, White, Red, Green, Orange

