



# FEP 200°C 600V UL 1901

Flexible UL/CSA Approved Lead Wire, Temp Rating 200°C




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Stranded tinned, annealed copper per ASTM B33
- Insulation:** Extruded FEP fluoropolymer

## APPLICATIONS AND FEATURES:

For further processing in cables. Smaller diameter than standard UL style 1330.

Excellent chemical resistance, excellent resistance to fluids, and low coefficient of friction makes installation easier. Flexible. Good mechanical strength. Available in all colors.

## SPECIFICATIONS:

- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL AWM Appliance wire approvals as listed in Table 1
- CSA AWM I A/B 600 FT1 FT2
- RoHS-3 Complies with European Directive 2015/863

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft	Temp. Rating °C	Standard (UL or other) Style/Type
C3226X	22*	7	15	0.060	5	200	1901

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◊ Cable marked with this symbol is a standard stock item  
 Dimensions and weights for other cable configurations are available upon request.  
 \*NPC Conductor required for 200°C Rating

**Table 2 – Weights and Measurements (Metric)**

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mm	Approx. OD mm	Approx. Weight kg/km	Temp. Rating °C	Standard (UL or other) Style/Type
C3226X	22*	7	0.38	1.52	7	200	1901

