



## PFA 250°C 300V UL 1726

Flexible UL/CSA Approved Lead Wire, Temp Rating 250°C



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Stranded annealed nickel plated copper
- Insulation:** Extruded PFA fluoropolymer

### APPLICATIONS AND FEATURES:

Used for wiring of electric heaters, appliances, thermocouples, gas igniters, electrical and electronic components and other products that require a temperature rating up to 250° C.

Excellent chemical resistance, excellent resistance to fluids, and low coefficient of friction makes installation easier. Flexible. Good mechanical strength. Available in all colors.

### SPECIFICATIONS:

- UL AWM Appliance wire approvals as listed in Table 1
- CSA AWM I A/B FT1
- RoHS-3 Complies with European Directive 2015/863

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft	Temp. Rating °C	Standard (UL or other) Style/Type
CP063A	6	133	20	0.250	97	250	1726

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Dimensions and weights for other cable configurations are available upon request.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Table 2 – Weights and Measurements (Metric)**

Stock Number	Cond. Size AWG/Kcmil	Cond. Strands strand	Insul. Thickness mm	Approx. OD mm	Approx. Weight kg/km	Temp. Rating °C	Standard (UL or other) Style/Type
CP063A	6	133	0.51	6.35	144	250	1726

