PFA 250°C 600V UL 1727

Flexible UL/CSA Approved Lead Wire, Temp Rating 250°C




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Stranded annealed nickel plated copper
2. **Insulation:** Extruded PFA fluoropolymer

APPLICATIONS AND FEATURES:

Used for wiring of electric heaters, appliances, thermocouples, gas igniters, electrical and electronic components and other products that require a temperature rating up to 250° C.

Excellent chemical resistance, excellent resistance to fluids, and low coefficient of friction makes installation easier. Flexible. Good mechanical strength. Available in all colors.

SPECIFICATIONS:

- UL AWM Appliance wire approvals as listed in Table 1
- CSA AWM I A/B FT1
- RoHS-3 Complies with European Directive 2015/863

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Strands	Insul. Thickness	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	strand	mil	inch	lb/1000ft	°C	Style/Type
CP246A	24	7	20	0.055	4	250	1727

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
Dimensions and weights for other cable configurations are available upon request.
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Cond. Strands	Insul. Thickness	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	strand	mm	mm	kg/km	°C	Style/Type
CP246A	24	7	0.51	1.40	6	250	1727

Copyright © 2026 Southwire Company, LLC. All Rights Reserved