

## TGGTG CABLES

TGGTG Power Cable - Flexible Premium High Temperature Cable, Temp Rating 250°C, 600V



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Flexible stranded nickel plated, annealed copper
- Insulation:** PTFE Fluoropolymer tapes covered by wrapped fiberglass yarn
- Braid:** Fiberglass braid jacket is applied over the insulation
- Cabling:** Conductors are cabled with a left hand lay and bound with a polyester tape
- Jacket:** Fiberglass braid jacket is applied over the insulation, then treated with a high temperature saturant

### APPLICATIONS AND FEATURES:

Used in wiring equipment.

Excellent flame resistance, good weathering, sunlight, ozone, and corona resistance, and good flexibility without cold flow.  
Also available in Power and Instrumentation Cables.

### SPECIFICATIONS:

- RoHS-3 Complies with European Directive 2015/863

### Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	No.	inch	lb/1000ft	°C	Style/Type
C53330	14	12	0.615	293	250	UL

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

### Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Cond. Number	Approx. OD	Approx. Weight	Temp. Rating	Standard (UL or other)
	AWG/Kcmil	No.	mm	kg/km	°C	Style/Type
C53330	14	12	15.62	436	250	UL

