

Southwire's Patent Pending Re3™ Minimum Bend Radius Device for SIMpull THHN/THWN-2® and XHHW-2® Copper and Aluminum Conductors

Designed by CableTechSupport™ Services Engineers and proudly made in the U.S.A to simplify installation and prevent overbent damage



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

Southwire Part #: 73629240
STEP-BY-STEP INSTRUCTIONS

1. Determine the conductor size and type (A: Aluminum and C: Copper)!
2. Adjust the flexible tube to align the cable size marking in the window (For example: 500 A= 500 kcmil Aluminum); Use disks for circuit sizes
3. Position the tool against the planned cable route to verify that its minimum bending radius is not being exceeded

[Contact SW Speed to place an order](#)

[Contact Cable Tech Support for engineering support](#)

APPLICATIONS AND FEATURES:

- There is no need to calculate the Minimum Bending Radius (MBR) or search for a value on the spec sheet!
- This all-in-one adjustable device can be used on the full size range of the most common building wire products including a total of 6 specs:
 - [SPEC 10000](#)
 - [SPEC 10003](#)
 - [SPEC 10005](#)
 - [SPEC 10006](#)
 - [SPEC 10012](#)
 - [SPEC 10015](#)
- The specific conductor size is marked on the device to make installation easier.
- A durable design allows for repeated use and the overbending prevention is achieved by using the patent pending smart tool to guide each route.