

## Broadband Coax - RG59 Dual Shield




Image not to scale. See Table 1 for dimensions.

### **CONSTRUCTION:**

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Polyethylene
3. **Shield:** Aluminum braid shielded
4. **Jacket:** Polyvinyl Chloride PVC.

### **APPLICATIONS AND FEATURES:**

- CATV Applications for distributing television signals
- ALUMINUM BRAID CCTV Applications for surveillance
- Connecting security cameras, DVR or monitor using "BNC" connectors
- COPPER BRAID
- 75 Ohms Impedance

### **SPECIFICATIONS:**

- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test

### **SAMPLE PRINT LEGEND:**

{SQFTG} SOUTHWIRE® SIGNAL® 92006 RG59 XX AWG CCS DUAL SHIELD E57497 (UL) CM OR CL2 OR CATV 75°C SUN RES

**Table 1 – Physical and Electrical Data**

| Stock Number | Cable Type | Rating     | Cond. Size | Cond. Number | Cond. Type | Cond. Strands | Insul. Thickness | Jacket Thickness | Approx. OD | Approx. Weight | Shield Type |
|--------------|------------|------------|------------|--------------|------------|---------------|------------------|------------------|------------|----------------|-------------|
|              |            |            | AWG        | No.          |            | strands       | mil              | mil              | inch       | lb /1000ft     |             |
| RG59         |            |            |            |              |            |               |                  |                  |            |                |             |
| 92006        | RG59       | CM/<br>CL2 | 22         | 1            | CCS        | Solid         | 60               | 30               | 0.240      | 19             | Dual        |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item