



DURATRAY™ CU 600V XLPE Insulation. RHH/RHW-2/RW90 UL & CSA

Single Copper Conductors, XLPE Insulation, Sunlight Resistant, 600V, 90°C MAX, -40°C MIN, Gasoline & Oil Resistant



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Insulation:** Cross Linked Polyethylene (XLPE)

APPLICATIONS AND FEATURES:

Suitable for installation in Cable Trays, Underground Duct Banks - As per CE Code limitations (see Rule 12-2202) for grounding and bonding applications. Standard colour is black. Some sizes may be available in white, red, blue, yellow, brown, orange or grey. Green Duraground™ also available.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- CSA C22.2 No. 38 Thermoset-insulated wires and cables
- CSA C22.2 No.230 Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA SUN RES - for Sunlight Resistant rating
- CSA ST1 Smoke Test - marked FT4-ST1 (1/0 and Larger)
- Oil Res I & Sun Res - AWG 8 & Larger

SAMPLE PRINT LEGEND:

SOUTHWIRE E30117 {UL} XX AWG CU RHH-RHW-2 600V FOR CT USE FT4 SR PR I OR PR II 90°C WET OR DRY -40°C ---
{CSA} LL90458 XX AWG (XX.Xmm²) RW90 600V FT4 SR -40°C XLPE --- RoHS {MM/DD/YYYY}





Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand	Insul. Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Raceway 90°C†
	AWG/Kcmil	No.	mil	inch	lb/1000ft	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp
TBA	8	7	60	0.261	69	1.0	132	0.653	0.786	0.052	55
TBA	6	7	60	0.297	104	1.1	209	0.411	0.495	0.051	75
TBA	4	7	60	0.345	155	1.3	333	0.258	0.310	0.048	95
TBA	2	7	60	0.402	237	1.6	530	0.162	0.195	0.045	130
649139	1/0	19	80	0.528	395	2.1	844	0.102	0.122	0.044	170
649088◇	2/0	19	80	0.572	487	2.2	1064	0.081	0.097	0.043	195
649148	3/0	19	80	0.622	602	2.4	1342	0.064	0.078	0.042	225
649097◇	4/0	19	80	0.666	745	2.6	1692	0.051	0.062	0.041	260
TBA	250	37	95	0.748	872	2.9	2000	0.043	0.053	0.041	290
649107◇	350	37	95	0.841	1218	3.3	2800	0.031	0.039	0.040	350
649045◇	500	37	95	0.966	1705	3.8	4000	0.022	0.029	0.039	430
649048◇	750	61	110	1.200	2549	6.0	6000	0.014	0.022	0.038	535
649130◇	1000	61	110	1.349	3354	6.7	8000	0.011	0.018	0.037	615

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

†Ampacities derived from the 2015 Canadian Electrical Code - Table 1 - For single conductor in free air and based on an ambient temperature of 30°C. - Table 2 - for Cable in Conduit. Not more than 3 aluminum conductors in a conduit and based on an ambient temperature of 30°C.

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Strand	Insul. Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Raceway 90°C
	AWG/Kcmil	No.	mm	mm	kg/km	mm	newton	Ω/km	Ω/km	Ω/km	Amp
TBA	8	7	1.52	6.63	103	25.40	587	2.14	2.58	0.1706	55
TBA	6	7	1.52	7.54	155	27.94	930	1.35	1.62	0.1673	75
TBA	4	7	1.52	8.76	231	33.02	1482	0.85	1.02	0.1575	95
TBA	2	7	1.52	10.21	353	40.64	2359	0.53	0.64	0.1476	130
649139	1/0	19	2.03	13.41	588	53.34	3756	0.33	0.40	0.1444	170
649088◇	2/0	19	2.03	14.53	725	55.88	4735	0.27	0.32	0.1411	195
649148	3/0	19	2.03	15.80	896	60.96	5972	0.21	0.26	0.1378	225
649097◇	4/0	19	2.03	16.92	1109	66.04	7529	0.17	0.20	0.1345	260
TBA	250	37	2.41	19.00	1298	73.66	8900	0.14	0.17	0.1345	290
649107◇	350	37	2.41	21.36	1813	83.82	12460	0.10	0.13	0.1312	350
649045◇	500	37	2.41	24.54	2537	96.52	17800	0.07	0.10	0.1280	430
649048◇	750	61	2.79	30.48	3793	152.40	26700	0.05	0.07	0.1247	535
649130◇	1000	61	2.79	34.26	4991	170.18	35600	0.04	0.06	0.1214	615

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

†Ampacities derived from the 2015 Canadian Electrical Code - Table 1 - For single conductor in free air and based on an ambient temperature of 30°C. - Table 2 - for Cable in Conduit. Not more than 3 aluminum conductors in a conduit and based on an ambient temperature of 30°C.





Stock Codes and Colors

Size	BLACK	WHITE	RED	BLUE	YELLOW	BROWN	ORANGE	GREY
1/0	649139	649132	649134	649136	TBA	TBA	TBA	TBA
2/0	649088	649081	649083	649085	TBA	TBA	TBA	TBA
3/0	649148	649141	649143	649146	TBA	TBA	TBA	TBA
4/0	649097	649090	649092	649094	TBA	TBA	TBA	TBA
250Kcmil	TBA	TBA	TBA	TBA	TBA	TBA	TBA	TBA
350Kcmil	649107	649109	649102	649105	TBA	TBA	TBA	TBA
500Kcmil	649045	649110	649113	649115	TBA	TBA	TBA	TBA
750Kcmil	649048	649117	649119	649121	TBA	TBA	TBA	TBA
1000Kcmil	649130	649123	649125	649127	TBA	TBA	TBA	TBA

◇ Cable marked with this symbol is a standard stock item

