HVTECK CU 1/C 220TRXLPE TS PVC AIA PVC 15kV 133% CSA

Single Conductor, 220 Mils Tree Retardant Cross Linked Polyethylene, 133% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 220 Mils Tree Retardant Cross Linked Polyethylene 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Inner Jacket:** PVC inner jacket
7. **Armour:** Aluminum Interlocked Armour (AIA)
8. **Overall Jacket:** Red Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 15kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)

Copyright © 2026 Southwire Company, LLC. All Rights Reserved
UPDATED: Dec. 31, 2024, 11:07 p.m.UTC REVISION: 1.000.001

- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CU 220 TRXLPE AIA 15kV 133% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Conduit Size*
	AWG/ Kcmil	No.	inch	inch	mil	inch	mil	inch	mil	inch	lb/ 1000ft	lb/ 1000ft	inch
TBA	2	7	0.283	0.761	220	0.821	80	1.211	50	1.311	273	984	3.5
TBA	1	19	0.322	0.8	220	0.86	80	1.25	50	1.35	329	1075	3.5
TBA	1/0	19	0.362	0.84	220	0.9	80	1.29	50	1.39	400	1182	3.5
670965	2/0	19	0.405	0.884	220	0.944	80	1.468	50	1.568	493	1327	4
TBA	3/0	19	0.456	0.934	220	0.994	80	1.384	50	1.484	600	1466	4
672441^	4/0	19	0.512	0.99	220	1.05	80	1.574	60	1.694	744	1693	4.5
TBA	250	37	0.558	1.044	220	1.104	80	1.594	60	1.714	863	2007	4.5
671319	350	37	0.661	1.147	220	1.207	80	1.731	60	1.851	1183	2274	5
672047	500	37	0.789	1.275	220	1.335	80	1.859	60	1.979	1656	2856	5
641194	750	61	0.968	1.464	220	1.524	110	2.108	60	2.228	2443	3928	6
672046	1000	61	1.117	1.613	220	1.673	110	2.257	75	2.407	3226	4918	6.5
672445^	1000	61	1.117	1.613	220	1.673	110	2.257	75	2.407	3226	4909	6.5
TBA	1250	91	1.25	1.75	220	1.81	110	2.36	75	2.51	4008	6075	6.5
TBA	1500	91	1.37	1.87	220	1.93	110	2.48	75	2.63	4790	6988	7
TBA	2000	127	1.583	2.083	220	2.143	110	2.693	75	2.843	6351	8783	7.5

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 2 – Electrical and Engineering Data

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	9.2	530	0.162	0.221	0.059	0.057	0.574+j0.459	0.222+j0.063	2575	215	221
1	9.5	669	0.128	0.175	0.054	0.055	0.529+j0.442	0.176+j0.060	2696	245	247
1/0	9.7	844	0.102	0.139	0.05	0.053	0.494+j0.425	0.140+j0.058	2820	278	275
2/0	11	1064	0.082	0.112	0.047	0.053	0.465+j0.408	0.113+j0.058	2956	317	306
3/0	10.4	1342	0.064	0.087	0.043	0.049	0.441+j0.390	0.088+j0.054	3111	357	335
4/0	11.9	1692	0.051	0.07	0.04	0.049	0.421+j0.370	0.071+j0.055	3284	404	369
250	12	2000	0.043	0.059	0.037	0.047	0.409+j0.353	0.060+j0.053	3452	456	412
350	13	2800	0.031	0.043	0.033	0.045	0.387+j0.322	0.044+j0.051	3771	537	456
500	13.9	4000	0.021	0.03	0.029	0.043	0.367+j0.289	0.032+j0.048	4167	616	497
750	15.6	6000	0.014	0.021	0.024	0.041	0.344+j0.249	0.023+j0.046	4753	706	551
1000	16.8	8000	0.011	0.018	0.022	0.039	0.329+j0.222	0.020+j0.044	5215	813	596
1000	16.8	8000	0.011	0.018	0.022	0.039	0.329+j0.222	0.020+j0.044	5215	813	596
1250	17.6	10000	0.008	0.014	0.02	0.038	0.315+j0.201	0.016+j0.043	5639	889	632
1500	18.4	12000	0.007	0.014	0.018	0.037	0.305+j0.185	0.016+j0.042	6011	956	663
2000	19.9	16000	0.005	0.013	0.016	0.035	0.288+j0.160	0.015+j0.040	6671	1073	715

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
***** CEC ampacities are based on:
3-1/C in air copper and aluminum: D17M
3-1/C direct buried copper and aluminum: D17A

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Conduit Size*
	AWG/ Kcmil	No.	mm	mm	mm	mm	mm	mm	mm	mm	kg/km	kg/km	inch
TBA	2	7	7.19	19.33	5.59	20.85	2.03	30.76	1.27	33.30	406	1464	3.5
TBA	1	19	8.18	20.32	5.59	21.84	2.03	31.75	1.27	34.29	490	1600	3.5
TBA	1/0	19	9.19	21.34	5.59	22.86	2.03	32.77	1.27	35.31	595	1759	3.5
670965	2/0	19	10.29	22.45	5.59	23.98	2.03	37.29	1.27	39.83	734	1975	4
TBA	3/0	19	11.58	23.72	5.59	25.25	2.03	35.15	1.27	37.69	893	2182	4
672441^	4/0	19	13.00	25.15	5.59	26.67	2.03	39.98	1.52	43.03	1107	2519	4.5
TBA	250	37	14.17	26.52	5.59	28.04	2.03	40.49	1.52	43.54	1284	2987	4.5
671319	350	37	16.79	29.13	5.59	30.66	2.03	43.97	1.52	47.02	1760	3384	5
672047	500	37	20.04	32.39	5.59	33.91	2.03	47.22	1.52	50.27	2464	4250	5
641194	750	61	24.59	37.19	5.59	38.71	2.79	53.54	1.52	56.59	3636	5846	6
672046	1000	61	28.37	40.97	5.59	42.49	2.79	57.33	1.91	61.14	4801	7319	6.5
672445^	1000	61	28.37	40.97	5.59	42.49	2.79	57.33	1.91	61.14	4801	7305	6.5
TBA	1250	91	31.75	44.45	5.59	45.97	2.79	59.94	1.91	63.75	5965	9041	6.5
TBA	1500	91	34.80	47.50	5.59	49.02	2.79	62.99	1.91	66.80	7128	10399	7
TBA	2000	127	40.21	52.91	5.59	54.43	2.79	68.40	1.91	72.21	9451	13071	7.5

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	mm	newton	Ω/km	Ω/km	MΩ*km	Ω/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	233.68	2359	0.5315	0.73	0.0180	0.1870	0.574+j0.459	0.222+j0.063	2575	215	221
1	241.30	2977	0.4199	0.57	0.0165	0.1804	0.529+j0.442	0.176+j0.060	2696	245	247
1/0	246.38	3756	0.3346	0.46	0.0152	0.1739	0.494+j0.425	0.140+j0.058	2820	278	275
2/0	279.40	4735	0.2690	0.37	0.0143	0.1739	0.465+j0.408	0.113+j0.058	2956	317	306
3/0	264.16	5972	0.2100	0.29	0.0131	0.1608	0.441+j0.390	0.088+j0.054	3111	357	335
4/0	302.26	7529	0.1673	0.23	0.0122	0.1608	0.421+j0.370	0.071+j0.055	3284	404	369
250	304.80	8900	0.1411	0.19	0.0113	0.1542	0.409+j0.353	0.060+j0.053	3452	456	412
350	330.20	12460	0.1017	0.14	0.0101	0.1476	0.387+j0.322	0.044+j0.051	3771	537	456
500	353.06	17800	0.0689	0.10	0.0088	0.1411	0.367+j0.289	0.032+j0.048	4167	616	497
750	396.24	26700	0.0459	0.07	0.0073	0.1345	0.344+j0.249	0.023+j0.046	4753	706	551
1000	426.72	35600	0.0361	0.06	0.0067	0.1280	0.329+j0.222	0.020+j0.044	5215	813	596
1000	426.72	35600	0.0361	0.06	0.0067	0.1280	0.329+j0.222	0.020+j0.044	5215	813	596
1250	447.04	44500	0.0262	0.05	0.0061	0.1247	0.315+j0.201	0.016+j0.043	5639	889	632
1500	467.36	53400	0.0230	0.05	0.0055	0.1214	0.305+j0.185	0.016+j0.042	6011	956	663
2000	505.46	71200	0.0164	0.04	0.0049	0.1148	0.288+j0.160	0.015+j0.040	6671	1073	715

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
***** CEC ampacities are based on:
3-1/C in air copper and aluminum: D17M
3-1/C direct buried copper and aluminum: D17A

Copyright © 2026 Southwire Company, LLC. All Rights Reserved