HVTECK CU 3/C 345NLEPR TS PVC AIA PVC 28kV 133% CSA

3 Conductor, 345 Mils No Lead Ethylene Propylene Rubber (NL-EPR), 133% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 345 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Filler:** Interstices filled with non-hydroscoping/non-wicking fillers
7. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8
8. **Binder:** Polypropylene tape
9. **Inner Jacket:** PVC inner jacket
10. **Armour:** Aluminum Interlocked Armour (AIA)
11. **Overall Jacket:** Black Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 28kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 3/C [#AWG or #kcmil] CU 345 NLEPR AIA 28kV 133% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Ground	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Conduit Size*
AWG/ Kcmil	No.	inch	inch	mil	inch	No. x AWG	mil	inch	mil	inch	lb/ 1000ft	lb/ 1000ft	inch
1	19	0.322	1.05	345	1.11	1x6	110	2.954	75	3.104	1141	3683	4
1/0	19	0.362	1.09	345	1.15	1x6	125	3.07	85	3.24	1356	4083	4
2/0	19	0.405	1.133	345	1.193	1x6	125	3.163	85	3.333	1625	4482	4.5
3/0	19	0.456	1.184	345	1.244	1x4	125	3.273	85	3.443	2010	5021	4.5
4/0	19	0.512	1.24	345	1.3	1x4	125	3.394	85	3.564	2433	5613	4.5
250	37	0.558	1.294	345	1.354	1x4	125	3.511	85	3.681	2807	6163	5
350	37	0.661	1.397	345	1.457	1x3	125	3.733	85	3.903	3802	7471	5

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1	21.7	2008	0.128	0.175	0.056	0.034	0.538+j0.365	0.175+j0.051	3470	202	226
1/0	22.7	2534	0.102	0.139	0.052	0.033	0.500+j0.351	0.139+j0.049	3594	231	256
2/0	23.3	3194	0.082	0.112	0.049	0.031	0.470+j0.337	0.112+j0.047	3727	265	290
3/0	24.1	4027	0.064	0.087	0.046	0.029	0.442+j0.322	0.087+j0.045	3885	303	327
4/0	24.9	5078	0.051	0.07	0.042	0.027	0.420+j0.306	0.070+j0.044	4059	348	369
250	25.8	6000	0.043	0.059	0.04	0.026	0.405+j0.292	0.059+j0.042	4226	384	408
350	27.3	8400	0.031	0.043	0.036	0.024	0.381+j0.268	0.043+j0.040	4545	468	485

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
***** CEC ampacities are based on:
3/C in air copper and aluminum: D17N
3/C direct buried copper and aluminum: D17E

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 3 – Weights and Measurements (Metric)

Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Ground	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Conduit Size*
AWG/ Kcmil	No.	mm	mm	mm	mm	No. x AWG	mm	mm	mm	mm	kg/km	kg/km	inch
1	19	8.18	26.67	8.76	28.19	1x6	2.79	75.03	1.91	78.84	1698	5481	4
1/0	19	9.19	27.69	8.76	29.21	1x6	3.18	77.98	2.16	82.30	2018	6076	4
2/0	19	10.29	28.78	8.76	30.30	1x6	3.18	80.34	2.16	84.66	2418	6670	4.5
3/0	19	11.58	30.07	8.76	31.60	1x4	3.18	83.13	2.16	87.45	2991	7472	4.5
4/0	19	13.00	31.50	8.76	33.02	1x4	3.18	86.21	2.16	90.53	3621	8353	4.5
250	37	14.17	32.87	8.76	34.39	1x4	3.18	89.18	2.16	93.50	4177	9172	5
350	37	16.79	35.48	8.76	37.01	1x3	3.18	94.82	2.16	99.14	5658	11118	5

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
1 Comply with ICEA S-93-639 Appendix C for jacket thickness determination
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	mm	newton	Ω/km	Ω/km	MΩ*km	Ω/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1	551.18	8936	0.4199	0.57	0.0171	0.1115	0.538+j0.365	0.175+j0.051	3470	202	226
1/0	576.58	11276	0.3346	0.46	0.0158	0.1083	0.500+j0.351	0.139+j0.049	3594	231	256
2/0	591.82	14213	0.2690	0.37	0.0149	0.1017	0.470+j0.337	0.112+j0.047	3727	265	290
3/0	612.14	17920	0.2100	0.29	0.0140	0.0951	0.442+j0.322	0.087+j0.045	3885	303	327
4/0	632.46	22597	0.1673	0.23	0.0128	0.0886	0.420+j0.306	0.070+j0.044	4059	348	369
250	655.32	26700	0.1411	0.19	0.0122	0.0853	0.405+j0.292	0.059+j0.042	4226	384	408
350	693.42	37380	0.1017	0.14	0.0110	0.0787	0.381+j0.268	0.043+j0.040	4545	468	485

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
***** CEC ampacities are based on:
3/C in air copper and aluminum: D17N
3/C direct buried copper and aluminum: D17E

Copyright © 2026 Southwire Company, LLC. All Rights Reserved