



HVTECK AL 3/C 280TRXLPE TS PVC AIA PVC 28kV 100% CSA

3 Conductor, 280 Mils Tree Retardant Cross Linked Polyethylene, 100% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
2. **Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
3. **Insulation:** 280 Mils Tree Retardant Cross Linked Polyethylene 100% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helicallly wrapped 5 mil copper tape with 25% overlap
6. **Filler:** Interstices filled with non-hydroscoping/non-wicking fillers
7. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8
8. **Binder:** Polypropylene tape
9. **Inner Jacket:** PVC inner jacket
10. **Armour:** Aluminum Interlocked Armour (AIA)
11. **Overall Jacket:** Black Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 28kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable





- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 3/C [#AWG or #kcmil] CPT AL 280 TRXLPE AIA 28kV 100% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Ground Size | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Approx. Weight |
|---------------|--------|-------------------------|--------------------------|------------------|---------------------------------|-------------|------------------------|------------------|--------------------------|------------|----------------|
| AWG/ Kcmil | No. | inch | inch | mil | inch | AWG | mil | inch | mil | inch | lb/1000ft |
| 1 | 19 | 0.298 | 0.896 | 280 | 0.956 | 6 | 110 | 2.684 | 75 | 2.834 | 3027 |
| 1/0 | 19 | 0.336 | 0.934 | 280 | 0.994 | 6 | 110 | 2.766 | 75 | 2.916 | 3222 |
| 2/0 | 19 | 0.376 | 0.974 | 280 | 1.034 | 6 | 110 | 2.853 | 75 | 3.003 | 3440 |
| 3/0 | 19 | 0.422 | 1.020 | 280 | 1.080 | 6 | 110 | 2.952 | 75 | 3.102 | 3700 |
| 4/0 | 19 | 0.474 | 1.072 | 280 | 1.132 | 6 | 110 | 3.064 | 85 | 3.234 | 4072 |
| 250 | 37 | 0.520 | 1.126 | 280 | 1.186 | 4 | 125 | 3.211 | 85 | 3.381 | 4495 |
| 350 | 37 | 0.615 | 1.221 | 280 | 1.281 | 4 | 125 | 3.416 | 85 | 3.586 | 5132 |
| 500 | 37 | 0.735 | 1.341 | 280 | 1.401 | 3 | 125 | 3.675 | 85 | 3.845 | 6024 |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM





Table 2 – Electrical and Engineering Data

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Phase Short Circuit Current @ 6 Cycles | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|-------------------------|-----------------------------|--|--------------------------------|---|
| AWG/Kcmil | inch | lb | Ω/1000ft | Ω/1000ft | MΩ*1000ft | Ω/1000ft | Ω/1000ft | Ω/1000ft | Amp | Amp | Amp |
| 1 | 19.8 | 1506 | 0.211 | 0.266 | 0.070 | 0.049 | 0.634 + j0.368 | 0.266 + j0.047 | 2992 | 158 | 177 |
| 1/0 | 20.4 | 1900 | 0.168 | 0.211 | 0.065 | 0.047 | 0.577 + j0.353 | 0.211 + j0.046 | 3110 | 181 | 200 |
| 2/0 | 21.0 | 2395 | 0.133 | 0.167 | 0.061 | 0.045 | 0.530 + j0.338 | 0.167 + j0.044 | 3234 | 208 | 228 |
| 3/0 | 21.7 | 3020 | 0.105 | 0.133 | 0.056 | 0.044 | 0.492 + j0.322 | 0.133 + j0.042 | 3377 | 239 | 258 |
| 4/0 | 22.6 | 3808 | 0.084 | 0.105 | 0.052 | 0.042 | 0.459 + j0.305 | 0.105 + j0.041 | 3538 | 273 | 292 |
| 250 | 23.7 | 4500 | 0.071 | 0.090 | 0.049 | 0.041 | 0.439 + j0.289 | 0.090 + j0.039 | 3705 | 302 | 321 |
| 350 | 25.1 | 6300 | 0.050 | 0.065 | 0.044 | 0.039 | 0.405 + j0.264 | 0.065 + j0.037 | 3999 | 368 | 385 |
| 500 | 26.9 | 9000 | 0.035 | 0.046 | 0.038 | 0.037 | 0.374 + j0.236 | 0.047 + j0.035 | 4371 | 454 | 462 |

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

* CEC ampacities are based on:

3/C in air copper and aluminum: D17N

3/C direct buried copper and aluminum: D17E

Table 3 – Weights and Measurements (Metric)

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Ground Size | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Approx. Weight |
|------------|--------|-------------------------|--------------------------|------------------|---------------------------------|-------------|------------------------|------------------|--------------------------|------------|----------------|
| AWG/Kcmil | No. | mm | mm | mm | mm | AWG | mm | mm | mm | mm | kg/km |
| 1 | 19 | 7.57 | 22.76 | 7.11 | 24.28 | 6 | 2.79 | 68.17 | 1.91 | 71.98 | 4505 |
| 1/0 | 19 | 8.53 | 23.72 | 7.11 | 25.25 | 6 | 2.79 | 70.26 | 1.91 | 74.07 | 4795 |
| 2/0 | 19 | 9.55 | 24.74 | 7.11 | 26.26 | 6 | 2.79 | 72.47 | 1.91 | 76.28 | 5119 |
| 3/0 | 19 | 10.72 | 25.91 | 7.11 | 27.43 | 6 | 2.79 | 74.98 | 1.91 | 78.79 | 5506 |
| 4/0 | 19 | 12.04 | 27.23 | 7.11 | 28.75 | 6 | 2.79 | 77.83 | 2.16 | 82.14 | 6060 |
| 250 | 37 | 13.21 | 28.60 | 7.11 | 30.12 | 4 | 3.18 | 81.56 | 2.16 | 85.88 | 6689 |
| 350 | 37 | 15.62 | 31.01 | 7.11 | 32.54 | 4 | 3.18 | 86.77 | 2.16 | 91.08 | 7637 |
| 500 | 37 | 18.67 | 34.06 | 7.11 | 35.59 | 3 | 3.18 | 93.34 | 2.16 | 97.66 | 8965 |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM





Table 4 – Electrical and Engineering Data (Metric)

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Phase Short Circuit Current @ 6 Cycles | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|-------------------------|-----------------------------|--|--------------------------------|---|
| AWG/ Kcmil | mm | newton | Ω/km | Ω/km | MΩ*km | Ω/km | Ω/1000ft | Ω/1000ft | Amp | Amp | Amp |
| 1 | 502.92 | 6702 | 0.6923 | 0.87 | 0.0213 | 0.1608 | 0.634 + j0.368 | 0.266 + j0.047 | 2992 | 158 | 177 |
| 1/0 | 518.16 | 8455 | 0.5512 | 0.69 | 0.0198 | 0.1542 | 0.577 + j0.353 | 0.211 + j0.046 | 3110 | 181 | 200 |
| 2/0 | 533.40 | 10658 | 0.4364 | 0.55 | 0.0186 | 0.1476 | 0.530 + j0.338 | 0.167 + j0.044 | 3234 | 208 | 228 |
| 3/0 | 551.18 | 13439 | 0.3445 | 0.44 | 0.0171 | 0.1444 | 0.492 + j0.322 | 0.133 + j0.042 | 3377 | 239 | 258 |
| 4/0 | 574.04 | 16946 | 0.2756 | 0.34 | 0.0158 | 0.1378 | 0.459 + j0.305 | 0.105 + j0.041 | 3538 | 273 | 292 |
| 250 | 601.98 | 20025 | 0.2329 | 0.30 | 0.0149 | 0.1345 | 0.439 + j0.289 | 0.090 + j0.039 | 3705 | 302 | 321 |
| 350 | 637.54 | 28035 | 0.1640 | 0.21 | 0.0134 | 0.1280 | 0.405 + j0.264 | 0.065 + j0.037 | 3999 | 368 | 385 |
| 500 | 683.26 | 40050 | 0.1148 | 0.15 | 0.0116 | 0.1214 | 0.374 + j0.236 | 0.047 + j0.035 | 4371 | 454 | 462 |

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

* CEC ampacities are based on:

3/C in air copper and aluminum: D17N

3/C direct buried copper and aluminum: D17E

