



Fire Alarm FPLR Solid Shielded

300V, 75°C, Multi-Conductor, Shielded, Solid Copper as FPLR. Rated CMR/CL3R/FPLR CMG SUN RES FT4. Minimum Temperature -10°C, Maximum Temperature 75°C




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid bare copper per ASTM B3
2. **Insulation:** Low Smoke Polyvinyl Chloride (LS-PVC)
3. **Drain Wire:** 24 AWG tinned copper drain wire per ASTM B33
4. **Shield:** Aluminum foil shield
5. **Rip Cord:** Rip cord for ease of jacket removal
6. **Jacket:** Red Low Smoke Polyvinyl Chloride (LS-PVC)

APPLICATIONS AND FEATURES:

Fire protective signaling circuits. Also for smoke detectors, voice communications, audio control and initiating circuits. Article 760 of the NEC. Minimum Temperature -10°C, Maximum Temperature 75°C

SPECIFICATIONS:

- UL 1424 Cables for Power-Limited Fire-Alarm Circuits
- UL 1424 Listed FPLR
- ASTM B3 Soft or Annealed Copper Wire
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- NFPA 70 NFPA 101, NFPA 130, and NFPA 502
- UL 13 Power-Limited Circuit Cables
- UL 444 Communications Cables (22 AWG - 16 AWG)
- RoHS-2 (European Directive 2011/65/EU)

SAMPLE PRINT LEGEND:

XX AWG X/C E75610 c{UL}US CMR/CL3R/FPLR SUN RES -- CMG FT4 MADE IN USA ROHS-2 COMPLIANT -- {MM/DD/YY}
{HH:MM}





Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Min Bending Radius
	AWG	No.	strands	inch	mil	mil	inch	lb / 1000ft	lb / 1000ft	Ω /1000ft	Ω /1000ft	inch
18 AWG												
F40015-1	18	2	Solid	0.050	10	15	0.153	11	16	6.669	8.035	0.9
F40567-1	18	4	Solid	0.050	10	15	0.174	21	28	6.669	8.035	1.0
16 AWG												
F50010-1	16	2	Solid	0.050	10	15	0.159	17	23	4.181	5.037	0.9
F50382-1	16	4	Solid	0.050	10	15	0.202	32	41	4.181	5.037	1.2
14 AWG												
F60030-1	14	2	Solid	0.064	10	15	0.212	26	34	2.631	3.170	1.2
F60354-1	14	4	Solid	0.064	10	15	0.226	51	62	2.631	3.170	1.3
12 AWG												
F70015	12	2	Solid	0.080	10	15	0.249	41	52	1.662	2.002	1.4

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

