



Southwire® CL4SS™ Class 4 Cable LS-PVC CL4P/CMP




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B or C stranded soft-drawn bare copper per ASTM B3 and B8
2. **Insulation:** Twisted pair(s) with premium grade, lead-free, 90°C rated, flame retardant, Polyvinyl Chloride (PVC). Color code: Black/White, Black/Red with alpha-numeric print (1-ONE, 2-TWO)
3. **Jacket:** Lead-free, 90°C rated, flame retardant, LS, Polyvinyl Chloride (PVC). See Table 3 for jacket colors.

APPLICATIONS AND FEATURES:

Intended for use in Fault Managed Power Systems (FMPS), remote powering, indoor Class 4 circuits per 2023 National Electrical Code (NEC) article 726. For use, primarily, in Agriculture, Intelligent Buildings, and Wireless Densification. The power source (transmitter) for Class 4 circuits shall be supplied from a power source that has a voltage output of 450 volts (peak or DC) or less.

Ratings:

- Normal operating temperature: 90°C
- Temperature Range: -30°C to 90°C
- Cold bend: -30°C
- FT6 Horizontal Flame & Smoke Test

SPECIFICATIONS:

- Certified to Southwire's UL E352061
- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 1400-2 Fault-Managed Power Systems - Part 2: Requirements for Cables

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® CL4SS P/N CL4P1XXN06XX -- XX AWG X PAIR E537761 (UL) CL4P-FMP (2.0A) 90C OR CMP
C(UL)US 90C FT6 -- MADE IN USA ROHS-2 COMPLIANT





Table 1 – Weights and Measurements

Stock Number	Cond. Size	Number of Pairs	Diameter Over Conductor	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	DC Resistance @ 25°C
	AWG/Kcmil	pair	inch	mil	mil	inch	lb/1000ft	inch	Ω/1000ft
CL4P182N06	18	2	0.046	10	15	0.244	33	1.0	6.669
CL4P184N06	18	4	0.046	10	15	0.288	60	1.2	6.669
CL4P186N06	18	6	0.046	10	15	0.354	88	1.4	6.669
CL4P188N06	18	8	0.046	10	15	0.388	115	1.6	6.669
CL4P162N06	16	2	0.058	10	15	0.283	47	1.1	4.181
CL4P164N06	16	4	0.058	10	15	0.335	88	1.3	4.181
CL4P166N0	16	6	0.058	10	15	0.413	130	1.7	4.181
CL4P168N06	16	8	0.058	10	15	0.453	170	1.8	4.181
CL4P142N06	14	2	0.073	10	15	0.332	69	1.3	2.631
CL4P144N06	14	4	0.073	10	15	0.394	131	1.6	2.631
CL4P146N06	14	6	0.073	10	15	0.487	194	2.0	2.631
CL4P148N06	14	8	0.073	10	15	0.534	255	2.1	2.631

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

• TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Number of Pairs	Diameter Over Conductor	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	DC Resistance @ 25°C
	AWG/Kcmil	pair	inch	mm	mm	mm	lb/km	mm	Ω/km
CL4P182N06	18	2	0.046	0.25	0.38	6.20	49	25.40	21.88
CL4P184N06	18	4	0.046	0.25	0.38	7.32	89	30.48	21.88
CL4P186N06	18	6	0.046	0.25	0.38	8.99	131	35.56	21.88
CL4P188N06	18	8	0.046	0.25	0.38	9.86	171	40.64	21.88
CL4P162N06	16	2	0.058	0.25	0.38	7.19	70	27.94	13.72
CL4P164N06	16	4	0.058	0.25	0.38	8.51	131	33.02	13.72
CL4P166N0	16	6	0.058	0.25	0.38	10.49	193	43.18	13.72
CL4P168N06	16	8	0.058	0.25	0.38	11.51	253	45.72	13.72
CL4P142N06	14	2	0.073	0.25	0.38	8.43	103	33.02	8.63
CL4P144N06	14	4	0.073	0.25	0.38	10.01	195	40.64	8.63
CL4P146N06	14	6	0.073	0.25	0.38	12.37	289	50.80	8.63
CL4P148N06	14	8	0.073	0.25	0.38	13.56	379	53.34	8.63


Typical Electrical Specifications for Each Pair

Size	Capacitance
AWG	pF/ft
18	<30
16	<30
14	<30





Table 3 - Stock Code by Jacket Color

Conductor Size	Number of Pairs	Jacket Color	
AWG	num	Black	White
			
18	2	CL4P182N0608	CL4P182N0601
18	4	CL4P184N0608	CL4P184N0601
18	6	CL4P186N0608	CL4P186N0601
18	8	CL4P188N0608	CL4P188N0601
16	2	CL4P162N0608	CL4P162N0601
16	4	CL4P164N0608	CL4P164N0601
16	6	CL4P166N0608	CL4P166N0601
16	8	CL4P168N0608	CL4P168N0601
14	2	CL4P142N0608	CL4P142N0601
14	4	CL4P144N0608	CL4P144N0601
14	6	CL4P146N0608	CL4P146N0601
14	8	CL4P148N0608	CL4P148N0601

