



600V SEOPRENE® SE00W Power Cord with Black Jacket 105°C. Silicone-Free

600 Volt Cord. -50°C to maximum 105°C, Power Sizes, High Degree of Flexibility, Premium Oil Resistance, Sunlight, Water Resistance and Flame Retardant, UL/CSA Listed




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K stranded bare copper per ASTM B-174
2. **Insulation:** Heat, moisture and oil resistant TPE
3. **Filler:** Non-wicking polypropylene fillers, with a tissue-paper separator wrapped around the assembly
4. **Jacket:** Black TPE (other colors available upon request)

APPLICATIONS AND FEATURES:

Southwire Type SE00W Flexible Cords are permitted for Indoor and outdoor temporary power uses, portable industrial machinery and compressors, food processing and washdown facilities. Type SE00W Cords are suitable for use in temperatures between -50°C to maximum 105°C.

SPECIFICATIONS:

- UL 62 Flexible Cords and Cables
- CSA C22.2 No. 49 Flexible Cords and Cables
- Passes CSA FT2 Flame Test
- RoHS-3 Complies with European Directive 2015/863
- NEC Article 400 Flexible Cords, Cables and Fixture Wire
- NEC Article 501.140 Class I Division 2

SAMPLE PRINT LEGEND:

SOUTHWIRE{R} SEOPRENE{R} CORD X/C X AWG (XX.XX{mm2}) SE00W E46194 {UL} 600V -50{D}C TO 105{D}C -- CSA LL90458 SE00W 600V -50{D}C TO 105{D}C FT2 WATER RESISTANT

PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.




Table 1 – Weights and Measurements

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Insul. Color	Jacket Color
		AWG/ Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp		
598327	22316	8	3	133	60	110	0.854	401	35	BK,WE,GN	BK
598328	22591	8	4	133	60	125	0.940	516	28	BK,WE,RD,GN	BK
586939	22391	6	3	133	60	145	1.000	597	45	GN,WE,BK	BK
598329	22589	6	4	133	60	145	1.074	729	36	BK,WE,RD,GN	BK
598332	22471	4	4	133	60	165	1.280	1072	48	BK,WE,RD,GN	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12

Table 2 – Weights and Measurements (Metric)

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity *	Insul. Color	Jacket Color
		AWG/ Kcmil	No.	No.	mm	mm	mm	kg/km	Amp		
598327	22316	8	3	133	1.52	2.79	21.69	597	35	BK,WE,GN	BK
598328	22591	8	4	133	1.52	3.18	23.88	768	28	BK,WE,RD,GN	BK
586939	22391	6	3	133	1.52	3.68	25.40	888	45	GN,WE,BK	BK
598329	22589	6	4	133	1.52	3.68	27.28	1085	36	BK,WE,RD,GN	BK
598332	22471	4	4	133	1.52	4.19	32.51	1595	48	BK,WE,RD,GN	BK

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

