28kV CU 133% EPR (EAM) Full Neutral LLDPE

Single Conductor, 345 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM), 133% Insulation Level, Full Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Moisture blocked class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8 (Conductor moisture block optional and tinned copper per ASTM B33 optional)
2. **Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
3. **Insulation:** 345 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM) 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Neutral:** Helically applied soft drawn bare copper full concentric neutral
6. **Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 28kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation. 140°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40ºC and MV 90ºC optional marking available upon request

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 28000 VOLTS EPR INSULATION 345 MILS -- (NESC) -- SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

UPDATED: Aug. 10, 2025, 11:33 p.m.UTC REVISION: 1.000.001

Table 1 – Weights and Measurements

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
1 (SOLID)	0.289	1.017	345	1.137	21x14	0.154	50	1.365	1183	9.6	669
1 (19)	0.322	1.05	345	1.17	21x14	0.154	50	1.398	1211	9.8	669
1/0 (SOLID)	0.325	1.053	345	1.173	26x14	0.125	50	1.401	1346	9.8	844
1/0 (19)	0.362	1.09	345	1.21	26x14	0.125	50	1.438	1378	10.1	844
2/0 (19)	0.405	1.133	345	1.253	21x12	0.097	50	1.515	1584	10.6	1064
3/0 (19)	0.456	1.184	345	1.304	26x12	0.079	50	1.566	1833	11	1342
4/0 (19)	0.512	1.24	345	1.36	21x10	0.061	75	1.714	2246	12	1692
250 (37)	0.558	1.294	345	1.414	25x10	0.051	75	1.768	2545	12.4	2000

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Pulling tension based on pulling eye directly connected to conductor
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (SOLID)	0.128	0.175	0.059	0.057	0.27	4.4	0.320+j0.067	0.179+j0.060	7331	175	220
1 (19)	0.128	0.175	0.056	0.055	0.29	4.7	0.320+j0.068	0.179+j0.060	7331	175	220
1/0 (SOLID)	0.102	0.139	0.056	0.055	0.29	4.7	0.258+j0.055	0.143+j0.058	9076	200	250
1/0 (19)	0.102	0.139	0.052	0.053	0.31	5	0.258+j0.056	0.143+j0.058	9076	200	250
2/0 (19)	0.082	0.112	0.049	0.052	0.33	5.3	0.207+j0.046	0.118+j0.056	11636	225	280
3/0 (19)	0.064	0.087	0.046	0.05	0.35	5.7	0.164+j0.040	0.094+j0.054	14406	260	315
4/0 (19)	0.051	0.07	0.042	0.049	0.38	6.2	0.130+j0.035	0.079+j0.051	18496	295	355
250 (37)	0.043	0.059	0.04	0.048	0.41	6.6	0.110+j0.032	0.069+j0.049	22019	318	360

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3
*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.
*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.

Table 3 – Weights and Measurements (Metric)

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
1 (SOLID)	7.34	25.83	8.76	28.88	21x14	0.51	1.27	34.67	1760	243.84	2977
1 (19)	8.18	26.67	8.76	29.72	21x14	0.51	1.27	35.51	1802	248.92	2977
1/0 (SOLID)	8.25	26.75	8.76	29.79	26x14	0.41	1.27	35.59	2003	248.92	3756
1/0 (19)	9.19	27.69	8.76	30.73	26x14	0.41	1.27	36.53	2051	256.54	3756
2/0 (19)	10.29	28.78	8.76	31.83	21x12	0.32	1.27	38.48	2357	269.24	4735
3/0 (19)	11.58	30.07	8.76	33.12	26x12	0.26	1.27	39.78	2728	279.40	5972
4/0 (19)	13.00	31.50	8.76	34.54	21x10	0.20	1.91	43.54	3342	304.80	7529
250 (37)	14.17	32.87	8.76	35.92	25x10	0.17	1.91	44.91	3787	314.96	8900

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Pulling tension based on pulling eye directly connected to conductor
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (SOLID)	0.4199	0.57	0.0180	0.1870	0.886	14.4357	0.320+j0.067	0.179+j0.060	7331	175	220
1 (19)	0.4199	0.57	0.0171	0.1804	0.951	15.4199	0.320+j0.068	0.179+j0.060	7331	175	220
1/0 (SOLID)	0.3346	0.46	0.0171	0.1804	0.951	15.4199	0.258+j0.055	0.143+j0.058	9076	200	250
1/0 (19)	0.3346	0.46	0.0158	0.1739	1.017	16.4042	0.258+j0.056	0.143+j0.058	9076	200	250
2/0 (19)	0.2690	0.37	0.0149	0.1706	1.083	17.3885	0.207+j0.046	0.118+j0.056	11636	225	280
3/0 (19)	0.2100	0.29	0.0140	0.1640	1.148	18.7008	0.164+j0.040	0.094+j0.054	14406	260	315
4/0 (19)	0.1673	0.23	0.0128	0.1608	1.247	20.3412	0.130+j0.035	0.079+j0.051	18496	295	355
250 (37)	0.1411	0.19	0.0122	0.1575	1.345	21.6535	0.110+j0.032	0.069+j0.049	22019	318	360

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3
*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.
*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.

Concentric Neutral Calculator

Copyright © 2026 Southwire Company, LLC. All Rights Reserved