



Southwire® Machine Flex® Power Thermoset LSZH-TS

90°C Wet or Dry. 600 Volts or 1000 Volts. Flexible Stranded Copper Conductor. Thermoset Low Smoke Zero Halogen (LSZH-TS). Oil & Gasoline Resistant. Sunlight Resistant. Rated UL VW-1 and CSA FT1 & VW-1 Flame Resistant for sizes smaller than 2 AWG. Rated UL FT4-ST1 and CSA FT4-ST1 Flame Resistant for sizes 2 AWG and larger.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** 8 - 4/0 AWG: Class K, Flexible stranded bare copper. 250 - 750 kcmil: Class I, Flexible stranded bare copper
2. **Insulation:** Thermoset Low Smoke Zero Halogen (LSZH-TS)

APPLICATIONS AND FEATURES:

Southwire's Machine Flex® power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. 1/0 AWG & Larger rated for CT use.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1685 FT4-Vertical-Tray Fire Propagation and Smoke Release Test (2 AWG and Larger)
- CSA C22.2 No. 38 Thermoset-insulated wires and cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- **CE/RoHS-2 – The CE Marking has been applied solely to express the conformance to the material restrictions identified in the RoHS-2 (2011/65/EU) Directive**
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661





SAMPLE PRINT LEGEND:

8AWG-6AWG:

SOUTHWIRE® E30117 (PLANT ID) (UL) (XX AWG) # OF STRANDS STRAND CLASS X XX mm² TYPE XHHW-2-HF 600V/1000V SR PR11 GR11 90(D)C DRY OR WET -40(D)C VW-1 --- (CSA) LL90458 RW90 HAL-FREE 600V/100V SR PR11 GR11 -40(D)C XLPO --- CE RoHS-2 MADE IN USA --- (MM/DD/YYYY)

2AWG & Larger:

SOUTHWIRE® E30117 (PLANT ID) (UL) (XX AWG) # OF STRANDS STRAND CLASS X XX mm² TYPE XHHW-2--HF 600V/1000V SR PR11 GR11 90(D)C DRY OR WET -40(D)C FOR CT USE FT4-ST1 --- (CSA) LL90458 RW90 HAL-FREE 600V/100V SR PR11 GR11 -40(D)C XLPO FT4-ST1 --- CE RoHS-2 MADE IN USA --- (MM/DD/YYYY)

Table 1 – Weights and Measurements

Cond. Size AWG/Kcmil	Cond. Strands No.	Diameter Over Conductor inch	Insul. Thickness mil	Diameter Over Insulation inch	Approx. OD inch	Approx. Weight lb/1000ft
8	168	0.153	35	0.223	0.223	62
6	273	0.198	35	0.268	0.268	102
4	413	0.235	50	0.335	0.335	153
2	665	0.302	50	0.402	0.402	238
1	836	0.397	60	0.517	0.517	310
2/0	1330	0.400	60	0.520	0.520	426
1/0	1044	0.400	60	0.520	0.520	379
3/0	1672	0.533	60	0.653	0.653	593
4/0	2109	0.550	60	0.670	0.670	735
250	627	0.605	70	0.745	0.745	841
300	735	0.638	70	0.778	0.778	1010
350	855	0.670	70	0.810	0.810	1145
500	1221	0.858	70	0.998	0.998	1620
600	1480	0.963	80	1.123	1.123	1995
750	1850	1.094	80	1.254	1.254	2521
1000	2516	1.19	80	1.350	1.350	3211

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item





Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance	Max Pull Tension	Max Pull Tension	Min Bending Radius	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	Ω/1000ft	lb	lb	inch	Amp	Amp
8	0.715	0.861	0.052	132	132	0.8	50	55
6	0.450	0.541	0.051	209	209	0.0	65	75
4	0.282	0.340	0.048	333	333	1.3	85	95
2	0.179	0.216	0.045	530	530	1.6	115	130
1	0.143	0.172	0.046	669	669	2.0	130	145
2/0	0.090	0.108	0.043	1064	1064	2.0	175	195
1/0	0.113	0.136	0.044	844	844	2.0	150	170
3/0	0.072	0.087	0.042	1342	1342	2.6	200	225
4/0	0.057	0.069	0.041	1692	1692	2.6	230	260
250	0.047	0.057	0.041	2000	2000	2.9	255	290
300	0.039	0.048	0.041	2400	2400	3.1	285	320
350	0.033	0.042	0.040	2800	2800	3.2	310	350
500	0.023	0.031	0.039	4000	4000	3.9	380	430
600	0.019	0.027	0.039	4800	4800	5.6	420	475
750	0.016	0.024	0.038	6000	6000	6.2	475	535
1000	0.012	0.020	0.037	8000	8000	6.7	545	615

† Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

† Ampacities have been adjusted for more than Three Current-Carrying Conductors.

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

