



Southwire[®] Machine Flex[®] Power XLPE RW90

Type XHHW-2 600 Volts or 1000 Volts and Type RW90 600V. Rated 90°C Dry/Wet, -40°C. Flexible Bare Copper Conductors. Cross-Linked Polyethylene (XLPE) Insulation. Rated High-Heat, Flame, Moisture, Gasoline, Oil and Sunlight Resistant.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** 8 AWG - 4/0 AWG: Class K, flexible stranded, soft-drawn bare copper. 250 kcmil - 750 kcmil; Class I, flexible concentric ropelay stranded, soft-drawn bare copper
2. **Insulation:** Black, sunlight, gas, & oil resistant Cross-Linked Polyethylene (XLPE)

APPLICATIONS AND FEATURES:

Southwire Type XHHW-2 & RW90 conductors are primarily used in conduit, cable tray or other recognized raceways for service, feeders, and branch circuit wiring as specified in the National Electric Code (NEC) and the Canadian Electrical Code (CE Code). XHHW-2 & RW90 conductors may be used at conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. Voltage rating for XHHW-2 conductors is 600 volts and 1000 volts. Voltage rating for RW90 conductors is 600 volts. Flexible bare copper stranding allows for ease of installation in locations with limited space, as well as including for use in electrical equipment for industrial facilities with harsh chemical environments, telecommunications applications and data centers.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No. 38 Thermoset-insulated wires and cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- **CE/RoHS-2 – The CE Marking has been applied solely to express the conformance to the material restrictions identified in the RoHS-2 (2011/65/EU) Directive**
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661
- Sunlight Resistance





SAMPLE PRINT LEGEND:

8 AWG - 1 AWG:

SOUTHWIRE® E30117 (PLANT ID) (UL) (XX AWG) # OF STRANDS STRAND CLASS X XX mm² TYPE XHHW-2 1000V SR PR II GR II 90°C DRY OR WET -40°C VW-1 OR SIS 600V --- (CSA) LL90458 RW90 600V SR -40°C XLPE --- (NOM) – ANCE LS --- CE RoHS-2 MADE IN USA --- (MM/DD/YYYY)

1/0 AWG - 4/0 AWG:

SOUTHWIRE® E30117 (PLANT ID) (UL) (XX AWG) # OF STRANDS STRAND CLASS X XX mm² TYPE XHHW-2 1000V SR PR II GR II 90°C DRY OR WET -40°C FOR CT USE FT4 OR SIS 600V --- (CSA) LL90458 RW90 600V TC SR -40°C XLPE FT4 --- (NOM) – ANCE LS --- CE RoHS-2 MADE IN USA --- (MM/DD/YYYY)

250 kcmil - 750 kcmil:

SOUTHWIRE® E30117 (PLANT ID) (UL) (XX AWG) # OF STRANDS STRAND CLASS X XX mm² TYPE XHHW-2 1000V SR PR II GR II 90°C DRY OR WET -40°C FOR CT USE FT4 --- (CSA) LL90458 RW90 600V TC SR -40°C XLPE FT4 --- (NOM) – ANCE LS --- CE RoHS-2 MADE IN USA --- (MM/DD/YYYY)

Table 1 – Weights and Measurements

Stock Number	Cond. Size AWG/Kcmil	Cond. Number No.	Cond. Strands No.	Diameter Over Conductor inch	Insul. Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft
TBA	8	1	168	0.153	45	0.243	66
TBA	6	1	266	0.198	45	0.288	106
TBA	4	1	420	0.235	45	0.325	150
TBA	2	1	665	0.302	45	0.392	240
TBA	1	1	836	0.397	55	0.507	306
TBA	1/0	1	1064	0.400	55	0.510	374
459838!	2/0	1	1330	0.420	60	0.542	542
457084	4/0	1	2109	0.520	55	0.642	730
457126	3/0	1	1666	0.533	55	0.603	578
457085	250	1	627	0.605	65	0.746	850
457086	300	1	741	0.638	65	0.778	1020
457087	350	1	893	0.670	65	0.810	1179
459839	500	1	1221	0.858	70	0.998	1632
459840	600	1	1480	0.963	85	1.135	2024
138906	750	1	1850	1.094	80	1.266	2553
TBA	1000	1	2527	1.190	80	1.350	3211

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

! Green insulation

^ Green with yellow stripe insulation

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.





Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance	Max Pull Tension	Max Pull Tension	Min Bending Radius	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	Ω/1000ft	lb	lb	inch	Amp	Amp
8	0.715	0.861	0.052	132	132	0.9	50	55
6	0.450	0.541	0.051	209	209	1.1	65	75
4	0.282	0.340	0.048	333	333	1.3	85	95
2	0.179	0.216	0.045	530	530	1.5	115	130
1	0.143	0.172	0.046	669	669	2.0	130	145
1/0	0.113	0.136	0.044	844	844	2.0	150	170
2/0	0.090	0.108	0.043	1064	1064	2.2	175	195
4/0	0.057	0.069	0.041	1692	1692	2.6	230	260
3/0	0.072	0.087	0.042	1342	1342	2.5	200	225
250	0.047	0.057	0.041	2000	2000	2.9	255	290
300	0.039	0.051	0.041	2400	2400	3.1	285	320
350	0.033	0.042	0.040	2800	2800	3.2	310	350
500	0.023	0.031	0.039	4000	4000	4.0	380	430
600	0.019	0.027	0.039	4800	4800	5.7	420	475
750	0.016	0.024	0.038	6000	6000	6.3	475	535
1000	0.012	0.020	0.037	8000	8000	6.7	545	615

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

