



CU 600/1000V XLPE Insulation Thermoplastic LSZH-TP XHHW-2. CT Rated - Sunlight Resistant - For Direct Burial - Silicone Free

Type TC-ER Power Cable 600 or 1000 Volt Three Conductor Copper, Cross Linked Polyethylene (XLPE) insulation XHHW-2 Thermoplastic SOLONON® Low Smoke Zero Halogen (LSZH-TP) Jacket with 1 Bare CU Ground. CT Rated - Sunlight Resistant - For Direct Burial - Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
- Insulation:** Cross Linked Polyethylene (XLPE) Type XHHW-2
- Grounding Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (cable size 8 & 6 has insulated green ground)
- Filler:** Paper filler (cable size 8 & 6 uses Polypropylene filler)
- Binder:** Polyester flat thread binder tape for cable sizes larger than 2 AWG
- Overall Jacket:** Thermoplastic SOLONON® Low Smoke Zero Halogen (LSZH-TP) Jacket

APPLICATIONS AND FEATURES:

Southwire's 600 or 1000 Volt Type TC-ER power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10. Sunlight Resistant - For Direct Burial - Silicone Free

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Cable Conductor Identification Method 3 (1-BLACK, 2-RED, 3-BLUE)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- NFPA 130 Standard for Fixed Guideway Transit and Passenger Rail Systems (500kcmil & Larger)





SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® {UL} XXX AWG CU 3/C TYPE TC-ER XHHW-2 CDRS GW 1 X X AWG CU SOLONON® 90°C JACKET SUN RES OIL RES I FOR DIRECT BURIAL 600V

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Strand Count	Diameter Over Conductor	Insul. Thickness	Ground	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Jacket Color
	AWG/ Kcmil		No. of Strands	inch	mil	No. x AWG	mil	inch	lb/1000ft	lb/1000ft	
561568	8	3	7	0.141	45	1 x 10 GG	60	0.710	186	340	Black
561567	6	3	7	0.177	45	1 x 8 GG	60	0.795	297	480	Black
551378	2	3	7	0.282	45	1 x 6	80	0.980	702	979	Black
TBA	1	3	19	0.322	55	1 x 6	80	1.095	863	1172	Black
TBA	1/0	3	19	0.361	55	1 x 6	80	1.179	1067	1408	Black
561564	2/0	3	19	0.405	55	1 x 6	80	1.302	1326	1719	Black
565815	3/0	3	19	0.456	55	1 x 4	80	1.406	1699	2132	Black
959718	4/0	3	19	0.512	55	1 x 4	80	1.531	2109	2615	Black
TBA	250	3	37	0.558	65	1 x 4	80	1.648	2465	3029	Black
TBA	350	3	37	0.661	65	1 x 3	110	1.931	3435	4217	Black
564938	500	3	37	0.789	65	1 x 2	110	2.183	4884	5745	Black
552362	500	3	37	0.789	65	3 x 6	110	2.233	4923	5965	Black
TBA	750	3	61	0.968	80	1 x 1	110	2.658	7268	8547	Black

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

Stock Number	Cond. Size	Cond. Number	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/ Kcmil		inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
561568	8	3	2.8	396	0.653	0.786	0.052	50	55
561567	6	3	3.2	629	0.411	0.495	0.051	65	75
551378	2	3	3.9	1592	0.162	0.195	0.045	115	130
TBA	1	3	5.5	2008	0.128	0.154	0.046	130	145
TBA	1/0	3	5.9	2534	0.102	0.122	0.044	150	170
561564	2/0	3	6.5	3194	0.081	0.097	0.043	175	195
565815	3/0	3	7.0	4027	0.064	0.078	0.042	200	225
959718	4/0	3	7.7	5078	0.051	0.062	0.041	230	260
TBA	250	3	8.2	6000	0.043	0.053	0.041	255	290
TBA	350	3	9.7	8400	0.031	0.039	0.040	310	350
564938	500	3	13.1	12000	0.022	0.029	0.039	380	430
552362	500	3	13.4	12000	0.022	0.029	0.039	380	430
TBA	750	3	15.9	18000	0.014	0.022	0.038	475	535

* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

