



3-Layer 25kV AAAC CAMV™ Tree Wire/Spacer Cable

An Alternative and Robust Design to Bare AAAC Conductors to Harden the Electrical Grids.

3-Layer 25kV AAAC Tree Wire Concentrically Stranded AAAC Track-Resistant Crosslinked Polyethylene.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Aluminum-alloy 6201-T81 wires, concentrically stranded
2. **Strand Shield:** Semi-conducting cross linked polymer
3. **Inner Layer:** Low-Density Crosslinked Polyethylene (LDXLPE)
4. **Outer Layer:** High-Density Track-Resistant Crosslinked Polyethylene

APPLICATIONS AND FEATURES:

Used for primary and secondary overhead distribution where limited space is available or desired for rights-of-way. Installed the same as bare conductors, however, covering is effective in preventing direct shorts and instantaneous flashovers should tree limbs or other objects contact conductors in such close proximity.

- Tree Wire - Used for spans where trees crowd the right-of-way, such as in wooded residential areas, when a minimum of interference with the environment is desired. Covering minimizes power outages due to conductor contact with tree limbs, reducing the need for frequent or severe trimming.
- Covered Aerial MV Cable (CAMV)/Spacer Cable - Installed with other Covered Aerial MV cables and a supporting messenger through a series of space-maintaining devices (spacers). The resulting close-proximity configuration minimizes the amount of space and hardware required for line installation, particularly useful in congested areas.
- Covering Rated 90°C Normal and 130°C Emergency Operation. Unless adequate knowledge of the thermal characteristics of the environment is known, the permissible conductor temperature should be reduced by 10°C or in accordance with available data.

SPECIFICATIONS:

- ASTM B398 Standard Specification for Aluminum-Alloy 6201-T81 and 6201-T83 Wire for Electrical Purposes
- ASTM B400 Standard Specification for Compact Round Concentric-Lay-Stranded, Aluminum 1350 Conductors
- ICEA S-121-733 Tree Wire and Messenger Supported Spacer Cable



Table 1 – Weights and Measurements

Cond. Size	Cond. Strands	Diameter Over Conductor	Conductor Shield Thickness	Inner Layer Thickness	Outer Layer Thickness	Approx. OD	Approx. Weight	Rated Strength
AWG/Kcmil	#	inch	mil	mil	mil	inch	lb/1000ft	lb
48.69	7	0.250	15	125	125	0.780	225	1584
77.47	7	0.316	15	125	125	0.846	275	2520
123.3	7	0.398	15	125	125	0.928	348	4014
155.4	7	0.447	15	125	125	0.977	396	4851
195.7	7	0.502	15	125	125	1.032	454	6111
246.9	7	0.563	15	125	125	1.093	525	7704

All dimensions are nominal and subject to normal manufacturing tolerances
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.