



## AL 2000V XLPE Insulation. RHH/RHW-2 PV

Single Conductor Photovoltaic (Type PV) Power Cable 2000 Volt Aluminum Conductor XLPE Insulation. Sizes 6 AWG through 1000 kcmil. Heat, Moisture, and Sunlight Resistant RoHS. 90°C



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** AlumaFlex® Compact Stranded Aluminum Alloy (AA-8176)
2. **Insulation:** Cross-linked Polyethylene (XLPE)

### APPLICATIONS AND FEATURES:

The cable is available in sizes 6 AWG through 1000 kcmil. The product is approved for use in solar power applications per the NEC article 690 and is rated 90°C for exposed or concealed wiring in wet or dry locations. Individual conductors are stranded aluminum alloy covered with a cross-linked polyethylene (XLPE) insulation and is rated for direct burial. The cable is sunlight resistant, oil resistant PRI and PRIL, RoHS compliant, passes -40°C cold bend. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions.

### SPECIFICATIONS:

- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 4703 Standard for Photovoltaic Wire
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661
- VW-1 Vertical-Wire Flame Test (Optional)
- AA 8176 Stranded Aluminum Alloy Conductors

### SAMPLE PRINT LEGEND:

SOUTHWIRE E316464 {UL} PV WIRE XXX KCMIL (XXX.XXX{mm<sup>2</sup>}) COMPACT AL. --- AlumaFlex® AA8176 2000V 90°C WET OR DRY -40°C SUN RES DIRECT BURIAL OR RHH-RHW-2 2000V --- RoHS {MMM/DD/YYYY} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET





**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Insul. Thickness	Insulation Color	Approx. OD	Aluminum Weight	Approx. Weight	Jacket Color
	AWG/ Kcmil	No. of Strands	inch	mil		inch	lb/1000ft	lb/1000ft	
585843	6	7	0.169	85	BK	0.349	24	59	BK
586673	4	7	0.212	85	BK	0.383	39	77	BK
586672	2	6	0.268	85	BK	0.438	62	104	BK
619879	1	8	0.298	105	BK	0.519	78	146	BK
591256	1/0	10	0.336	105	BK	0.546	99	164	BK
583673	2/0	12	0.376	105	BK	0.586	125	195	BK
577100	3/0	16	0.422	105	BK	0.633	158	235	BK
583678	4/0	19	0.474	105	BK	0.685	199	284	BK
577101	250	22	0.520	120	BK	0.760	235	350	BK
584290	300	21	0.569	120	BK	0.810	282	397	BK
582174	350	35	0.615	120	BK	0.856	329	462	BK
584291	400	35	0.659	120	BK	0.899	376	518	BK
582267	500	34	0.735	120	BK	0.978	471	615	BK
585499	600	37	0.812	135	BK	1.083	565	745	BK
607592	700	58	0.877	135	BK	1.147	659	851	BN
586013	750	61	0.908	135	BK	1.178	706	904	BK
641387	1000	58	1.060	135	BK	1.330	942	1168	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.





**Table 2 – Electrical and Engineering Data**

Stock Number	Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
585843	6	1.4	157	0.674	0.812	0.051	50	55
586673	4	1.5	250	0.424	0.510	0.048	65	75
586672	2	1.8	398	0.267	0.321	0.045	90	100
619879	1	2.1	502	0.211	0.254	0.046	100	115
591256	1/0	2.2	633	0.168	0.201	0.044	120	135
583673	2/0	2.3	798	0.133	0.160	0.043	135	150
577100	3/0	2.5	1006	0.105	0.126	0.042	155	175
583678	4/0	2.7	1269	0.084	0.100	0.041	180	205
577101	250	3.0	1500	0.071	0.086	0.041	205	230
584290	300	3.2	1800	0.059	0.071	0.041	230	260
582174	350	3.4	2100	0.050	0.062	0.040	250	280
584291	400	3.6	2400	0.044	0.054	0.040	270	305
582267	500	3.9	3000	0.035	0.044	0.039	310	350
585499	600	5.4	3600	0.029	0.037	0.039	340	385
607592	700	5.7	4200	0.025	0.033	0.038	375	425
586013	750	5.9	4500	0.024	0.031	0.038	385	435
641387	1000	6.7	6000	0.018	0.025	0.037	445	500

\* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

\* Inductive Reactance is based on non-ferrous conduit with one diameter spacing center-to-center.

**Stock Codes and Colors**

Size	Black	Brown	Orange	Yellow	White	Red	Green
AWG/Kcmil							
6	585843						
4	586673						
2	586672						589171
1	619879						589051
1/0	591256				591241		
2/0	583673						
3/0	577100	669515	669516	669517	577843		669518
4/0	583678				597698	607400	591242
250	577101				577844	668535	
300	584290				589170	675225	
350	582174				597996	592618	
400	584291				596689	652801	
500	582267	591243	591244	591245	586671	588797	591246
600	585499				591247	588799	
700	607592	591248	591249	591250			
750						592619	
1000	641387				641386		

