# HVTECK AL 1/C 140TRXLPE CB PVC AIA PVC 8kV 133% CSA

Single Conductor, 140 Mils Tree Retardant Cross Linked Polyethylene, 133% Insulation Level, Concentric Bond, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket





Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
2. **Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
3. **Insulation:** 140 Mils Tree Retardant Cross Linked Polyethylene 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Shield:** Concentrically applied copper bond / shield wires. Complies with greater than the minimum requirement as per Table 44, CSA Standard C68.10 and Table 16A, Canadian Electrical Code Part 1
6. **Neutral Separator:** Mylar tape
7. **Inner Jacket:** PVC inner jacket
8. **Armour:** Aluminum Interlocked Armour (AIA)
9. **Overall Jacket:** Orange Polyvinyl Chloride (PVC) Jacket

## APPLICATIONS AND FEATURES:

Southwire's 8kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

## SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)



Copyright © 2026 Southwire Company, LLC. All Rights Reserved

- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

## SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CPT AL 140 TRXLPE AIA 8kV 133% INS LEVEL CB [No. x SIZE] AWG SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

## Table 1 – Weights and Measurements

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Concentric Neutral | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Copper Weight | Approx. Weight | Conduit Size* |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| AWG/ Kcmil | No. | inch | inch | mil | inch | No. x AWG | mil | inch | mil | inch | lb/ 1000ft | lb/ 1000ft | inch |
| 2 | 7 | 0.268 | 0.586 | 140 | 0.646 | 5x12 | 80 | 1.306 | 50 | 1.406 | 134 | 1030 | 3.5 |
| 1 | 19 | 0.299 | 0.617 | 140 | 0.677 | 5x12 | 80 | 1.337 | 50 | 1.437 | 137 | 1079 | 3.5 |
| 1/0 | 19 | 0.336 | 0.654 | 140 | 0.714 | 5x12 | 80 | 1.374 | 50 | 1.474 | 140 | 1139 | 4 |
| 2/0 | 19 | 0.376 | 0.694 | 140 | 0.754 | 7x12 | 80 | 1.414 | 50 | 1.514 | 191 | 1257 | 4 |
| 3/0 | 19 | 0.423 | 0.741 | 140 | 0.801 | 7x12 | 80 | 1.561 | 60 | 1.681 | 195 | 1513 | 4.5 |
| 4/0 | 19 | 0.475 | 0.793 | 140 | 0.853 | 7x12 | 80 | 1.613 | 60 | 1.733 | 199 | 1615 | 4.5 |
| 250 | 37 | 0.52 | 0.846 | 140 | 0.906 | 9x12 | 80 | 1.666 | 60 | 1.786 | 242 | 1756 | 4.5 |
| 350 | 37 | 0.616 | 0.942 | 140 | 1.002 | 11x12 | 80 | 1.762 | 60 | 1.882 | 287 | 2003 | 5 |
| 500 | 37 | 0.736 | 1.062 | 140 | 1.122 | 13x12 | 80 | 1.882 | 60 | 2.002 | 351 | 2342 | 5 |
| 750 | 61 | 0.908 | 1.244 | 140 | 1.304 | 17x12 | 110 | 2.124 | 60 | 2.244 | 433 | 2989 | 6 |
| 1000 | 61 | 1.117 | 1.453 | 140 | 1.513 | 17x12 | 110 | 2.333 | 75 | 2.483 | 450 | 3552 | 6.5 |

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Strand count meets minimum number per ASTM
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.


Copyright © 2026 Southwire Company, LLC. All Rights Reserved

## Table 2 – Electrical and Engineering Data

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Phase Short Circuit Current @ 6 Cycles | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|---|---|---|---|---|---|---|---|---|---|---|---|
| AWG/ Kcmil | inch | lb | Ω/1000ft | Ω/1000ft | MΩ*1000ft | Ω/1000ft | Ω/1000ft | Ω/1000ft | Amp | Amp | Amp |
| 2 | 9.8 | 398 | 0.266 | 0.365 | 0.044 | 0.06 | 0.665+j0.195 | 0.368+j0.065 | 2770 | 169 | 176 |
| 1 | 10.1 | 502 | 0.211 | 0.289 | 0.041 | 0.058 | 0.589+j0.192 | 0.292+j0.061 | 2770 | 194 | 198 |
| 1/0 | 10.3 | 633 | 0.167 | 0.229 | 0.038 | 0.056 | 0.528+j0.191 | 0.232+j0.059 | 2770 | 222 | 223 |
| 2/0 | 10.6 | 798 | 0.133 | 0.182 | 0.035 | 0.054 | 0.426+j0.121 | 0.186+j0.057 | 3879 | 255 | 250 |
| 3/0 | 11.8 | 1006 | 0.105 | 0.144 | 0.032 | 0.053 | 0.387+j0.120 | 0.148+j0.057 | 3879 | 290 | 278 |
| 4/0 | 12.1 | 1269 | 0.084 | 0.115 | 0.03 | 0.051 | 0.358+j0.119 | 0.119+j0.055 | 3879 | 329 | 309 |
| 250 | 12.5 | 1500 | 0.07 | 0.096 | 0.027 | 0.05 | 0.297+j0.084 | 0.101+j0.053 | 4987 | 370 | 347 |
| 350 | 13.2 | 2100 | 0.051 | 0.07 | 0.024 | 0.047 | 0.240+j0.062 | 0.076+j0.050 | 6095 | 446 | 402 |
| 500 | 14 | 3000 | 0.036 | 0.05 | 0.021 | 0.045 | 0.197+j0.049 | 0.057+j0.047 | 7203 | 533 | 451 |
| 750 | 15.7 | 4500 | 0.023 | 0.033 | 0.017 | 0.042 | 0.148+j0.034 | 0.041+j0.044 | 9420 | 631 | 500 |
| 1000 | 17.4 | 6000 | 0.017 | 0.025 | 0.015 | 0.04 | 0.140+j0.035 | 0.033+j0.043 | 9420 | 707 | 539 |

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
***** CEC ampacities are based on:
3-1/C in air copper and aluminum: D17M
3-1/C direct buried copper and aluminum: D17A

## Table 3 – Weights and Measurements (Metric)

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Concentric Neutral | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Copper Weight | Approx. Weight | Conduit Size* |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| AWG/ Kcmil | No. | mm | mm | mm | mm | No. x AWG | mm | mm | mm | mm | kg/km | kg/km | inch |
| 2 | 7 | 6.81 | 14.88 | 3.56 | 16.41 | 5x12 | 2.03 | 33.17 | 1.27 | 35.71 | 199 | 1533 | 3.5 |
| 1 | 19 | 7.59 | 15.67 | 3.56 | 17.20 | 5x12 | 2.03 | 33.96 | 1.27 | 36.50 | 204 | 1606 | 3.5 |
| 1/0 | 19 | 8.53 | 16.61 | 3.56 | 18.14 | 5x12 | 2.03 | 34.90 | 1.27 | 37.44 | 208 | 1695 | 4 |
| 2/0 | 19 | 9.55 | 17.63 | 3.56 | 19.15 | 7x12 | 2.03 | 35.92 | 1.27 | 38.46 | 284 | 1871 | 4 |
| 3/0 | 19 | 10.74 | 18.82 | 3.56 | 20.35 | 7x12 | 2.03 | 39.65 | 1.52 | 42.70 | 290 | 2252 | 4.5 |
| 4/0 | 19 | 12.07 | 20.14 | 3.56 | 21.67 | 7x12 | 2.03 | 40.97 | 1.52 | 44.02 | 296 | 2403 | 4.5 |
| 250 | 37 | 13.21 | 21.49 | 3.56 | 23.01 | 9x12 | 2.03 | 42.32 | 1.52 | 45.36 | 360 | 2613 | 4.5 |
| 350 | 37 | 15.65 | 23.93 | 3.56 | 25.45 | 11x12 | 2.03 | 44.75 | 1.52 | 47.80 | 427 | 2981 | 5 |
| 500 | 37 | 18.69 | 26.97 | 3.56 | 28.50 | 13x12 | 2.03 | 47.80 | 1.52 | 50.85 | 522 | 3485 | 5 |
| 750 | 61 | 23.06 | 31.60 | 3.56 | 33.12 | 17x12 | 2.79 | 53.95 | 1.52 | 57.00 | 644 | 4448 | 6 |
| 1000 | 61 | 28.37 | 36.91 | 3.56 | 38.43 | 17x12 | 2.79 | 59.26 | 1.91 | 63.07 | 670 | 5286 | 6.5 |

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Strand count meets minimum number per ASTM
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.


Copyright © 2026 Southwire Company, LLC. All Rights Reserved

## Table 4 – Electrical and Engineering Data (Metric)

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Phase Short Circuit Current @ 6 Cycles | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|---|---|---|---|---|---|---|---|---|---|---|---|
| AWG/ Kcmil | mm | newton | Ω/km | Ω/km | MΩ*km | Ω/km | Ω/1000ft | Ω/1000ft | Amp | Amp | Amp |
| 2 | 248.92 | 1771 | 0.8727 | 1.20 | 0.0134 | 0.1969 | 0.665+j0.195 | 0.368+j0.065 | 2770 | 169 | 176 |
| 1 | 256.54 | 2234 | 0.6923 | 0.95 | 0.0125 | 0.1903 | 0.589+j0.192 | 0.292+j0.061 | 2770 | 194 | 198 |
| 1/0 | 261.62 | 2817 | 0.5479 | 0.75 | 0.0116 | 0.1837 | 0.528+j0.191 | 0.232+j0.059 | 2770 | 222 | 223 |
| 2/0 | 269.24 | 3551 | 0.4364 | 0.60 | 0.0107 | 0.1772 | 0.426+j0.121 | 0.186+j0.057 | 3879 | 255 | 250 |
| 3/0 | 299.72 | 4477 | 0.3445 | 0.47 | 0.0098 | 0.1739 | 0.387+j0.120 | 0.148+j0.057 | 3879 | 290 | 278 |
| 4/0 | 307.34 | 5647 | 0.2756 | 0.38 | 0.0091 | 0.1673 | 0.358+j0.119 | 0.119+j0.055 | 3879 | 329 | 309 |
| 250 | 317.50 | 6675 | 0.2297 | 0.31 | 0.0082 | 0.1640 | 0.297+j0.084 | 0.101+j0.053 | 4987 | 370 | 347 |
| 350 | 335.28 | 9345 | 0.1673 | 0.23 | 0.0073 | 0.1542 | 0.240+j0.062 | 0.076+j0.050 | 6095 | 446 | 402 |
| 500 | 355.60 | 13350 | 0.1181 | 0.16 | 0.0064 | 0.1476 | 0.197+j0.049 | 0.057+j0.047 | 7203 | 533 | 451 |
| 750 | 398.78 | 20025 | 0.0755 | 0.11 | 0.0052 | 0.1378 | 0.148+j0.034 | 0.041+j0.044 | 9420 | 631 | 500 |
| 1000 | 441.96 | 26700 | 0.0558 | 0.08 | 0.0046 | 0.1312 | 0.140+j0.035 | 0.033+j0.043 | 9420 | 707 | 539 |

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
***** CEC ampacities are based on:
3-1/C in air copper and aluminum: D17M
3-1/C direct buried copper and aluminum: D17A


Copyright © 2026 Southwire Company, LLC. All Rights Reserved