Titan2™ Type UL Liquidtight Flexible Metal Conduit

Liquidtight Flexible Metal Conduit Metal Conduit. UL Listed. CSA Listed. Oil-Resistant. Sunlight-Resistant. Temperature Rated -55ºC to 80ºC




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Armor:** Titan2™ Type UL is manufactured with a spiral wound strip of heavy gauge, corrosion-resistant, hot-dipped galvanized steel. For 3/8" through 1-1/4" trade sizes, the core is constructed with a square locked steel strip with an integral copper-bonding strip enclosed within the steel convolutions.
2. **Jacket:** A rugged, flame retardant, gray flexible PVC jacket is extruded over the steel core. The jacket provides protection from liquids, oil, certain chemicals, temperature, extreme weather and sunlight.

APPLICATIONS AND FEATURES:

Titan2™ Type UL is suitable for the following installations:

- For extreme temperature environments
- For the installation and protection of electrical conductors in circuits of 600 Volts nominal, or less.
- Where the conditions of installation, operation, or maintenance require flexibility or protection from liquids, vapors, solids, or weather
- Used in industrial and commercial applications for conveyors, blowers, cranes, air conditioners, machine tooling and lubrication equipment
- Exposed or concealed installations
- Applications requiring movement, crossover connections, or tight bends
- Permitted for equipment grounding in sizes 3/8" through 1-1/4" in lengths not exceeding 6 feet per NEC 250.118(6)
- For flexible connections to swimming pool, spa, and hot tub motors per NEC® 680.21(A)(3) & 680.42(A)(1)
- Electric signs and outline lighting supply and secondary-circuit conductors per NEC® 600.7, 600.31 (1000 volts or less) & 600.32 (over 1000 volts)
- Floating building feeders and services per NEC® 553.7
- Boatyards & Marinas in accordance with NEC® 555.13
- Cranes & Hoists in accordance with NEC® 610.11(C)
- For Elevator, Dumbwaiters, Escalators, Moving Walks, Wheel Chair Lifts & Stairway Chair Lifts in accordance with NEC® 620.21 (where expressly permitted)
- Under raised floors in information technology equipment conductors and cables in accordance with NEC® 645.5 (D) & 645.5(D)(2)
- Service entrance in lengths up to six feet per NEC® 230.43(15)
- Electric signs and outline lighting supply and secondary-circuit per NEC 600.31 (1000 Volts or less) & NEC 600.32 (over 1000 Volts)
- Approved for use in lengths longer than 6 feet per NEC® 356.10(5)

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

- **Hazardous location:**
- Class I, Div. 2 - NEC® 501.10(B)(2) and 501.30(B)
- Class II, Div. 1 and 2 - NEC® 502.10(A)(2) and 502.30(B) and NEC 502.10(B)(2)
- Class III, Div. 1 and 2 - NEC® 503.10(A)(2) and 503.30(B) and NEC 503.10(A)(2)

Titan2™ Type UL Features

- A protective combination of thermoplastic materials formed into a conduit/raceway which seals out water, liquids, abrasives, alcohol, coolants, corrosive fumes and gases, dirt, grease, mineral acids, non-concentrated fixed alkalines, petroleum oils, salt air and spray, and weather
- Smooth interior for easy wire pulling
- UV sunlight resistant jacket
- Rated for temperature range of -30°C to 80°C , 60°C Oil (-22 to +176, 140°F Oil)
- Accepts standard liquid-tight fittings for use with LFNC-B
- Rated for direct burial applications including concrete encasement

SPECIFICATIONS:

- UL 360 Liquidtight Flexible Steel Conduit
- CSA 22.2 No. 56 Flexible metal conduit and liquid-tight flexible metal conduit
- NFPA 70 (National Electrical Code), Article 350 - Liquidtight Flexible Metal Conduit

SAMPLE PRINT LEGEND:

{SQFTG_DUAL} {SOUTHWIRE} X" {TITAN2_TM} TYPE UL, {UL} -55{D}C TO 80{D}C DRY, 60{D}C WET, 60{D}C OIL RES, DIR BUR SUNLIGHT RESISTANT --- {CSA} LIQUID-TIGHT CONDUIT 75{D}C, FT1

Titan2™ Type UL

Trade Size	Inner Diam (Min/Max)	Outer Diam (Min/Max)	Weight	Minimum Bend Radius
Inch	Inch	Inch	Lb/100ft	Inch
3/8	0.484/0.504	0.690/0.710	24	3*
1/2	0.622/0.642	0.820/0.840	30	4
3/4	0.820/0.840	1.030/1.050	38	5
1	1.041/1.066	1.290/1.315	60	8
1-1/4	1.380/1.410	1.630/1.660	80	10
1-1/2	1.575/1.600	1.865/1.900	113	12
2	2.020/2.045	2.340/2.375	149	16
2-1/2	2.480/2.505	2.840/2.875	198	20
3	3.070/3.100	3.460/3.500	265	24
3-1/2	3.500/3.540	3.960/4.000	300	28
4	4.000/4.040	4.460/4.500	310	32

*Suggestion only. Non-NEC requirement

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Put Ups Gray

TRADE SIZE (Inch)	25 ft	50 ft	100 ft	150 ft	250 ft	400 ft	500 ft	600 ft	1000 ft
3/8			55092903				55092901	55092905	
1/2			55082603				55082605		55082602
3/4			55082703				55082705		55082702
1			55093003			55093004			
1-1/4		55093305			55093303				
1-1/2		55093205		55093201					
2		55093105	55093101						
2-1/2	55106401		55106403						
3	55106504		55106503						
3-1/2	55106604		55106603						
4	55106704		55106702						

Copyright © 2026 Southwire Company, LLC. All Rights Reserved