AACSR

Aluminum Alloy Conductor, Steel Reinforced

Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Core:** Stranded standard strength steel core with Class A hot dipped zinc galvanization coating (also available in zinc-5% aluminum-mischmetal alloy coating)
2. **Stranding:** Heat-treated aluminum-alloy (6201-T81) round wire shaped strands with 52.5% conductivity

APPLICATIONS AND FEATURES:

AACSR (Aluminum Alloy Conductor, Steel Reinforced) is a concentrically stranded conductor consisting of one or more layers of heat-treated 6201-T81 aluminum-alloy wires surrounding a coated steel core. The aluminum-alloy strands contribute greater strength than 1350-H19 aluminum, while the steel core provides additional mechanical reinforcement.

AACSR is used for overhead transmission and distribution applications where high tensile strength, a favorable strength-to-weight ratio, and controlled sag are important. It is well suited for long spans, heavy mechanical loading, and line designs that require greater strength than conventional aluminum conductors, with moderate electrical conductivity.

Continuous operating temperature - 75°C
Emergency operating temperature - 100°C

SPECIFICATIONS:

- ASTM B398 Standard Specification for Aluminum-Alloy 6201-T81 and 6201-T83 Wire for Electrical Purposes
- ASTM B498 Standard Specification for Zinc-Coated (Galvanized) Steel Core Wire for Use in Overhead Electrical Conductors
- ASTM B500 Standard Specification for Metallic Coated or Aluminum-Clad Stranded Steel Core for Use in Overhead Electrical Conductors
- ASTM B711 Standard Specification for Concentric-Lay-Stranded Aluminum-Alloy Conductors, Steel Reinforced (AACSR) (6201)
- ASTM B802 Standard Specification for Zin-5% Aluminum-Mischmetal Alloy-Coated Steel Core Wire for Use in Overhead Electrical Conductors

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

UPDATED: Oct. 28, 2026, 8:14 p.m.UTC REVISION: 1.000.001

Weights, Measurements, Electrical and Engineering Data

Stock Number	Conductor Size	Stranding	Cross-Sectional Area		Layers of Al Alloy	Diameter				Weight		Rated Breaking Strength			DC Resistance @ 20°C
						Individual Strands		Steel Core	Complete Conductor						
			Al Alloy	Total		Al Alloy	St			Al Alloy	Total	Std	HS	UHS	
	AWG/kcmil	Al/St	in²	in²		in	in	in	in	lb/1000 ft	lb/1000 ft	lb	lb	lb	Ω/mile
TBA	6	6/1	0.0206	0.0240	1	0.0661	0.0661	0.0661	0.198	24.34	35.80	1,640	1,720	1,890	3.9359
TBA	4	6/1	0.0328	0.0383	1	0.0834	0.0834	0.0834	0.250	38.75	57.30	2,610	2,740	3,010	2.4710
TBA	4	7/1	0.0328	0.0411	1	0.0772	0.1029	0.1029	0.257	38.75	66.74	3,150	3,350	3,710	2.4396
TBA	2	6/1	0.0522	0.0609	1	0.1052	0.1052	0.1052	0.316	61.67	91.01	4,110	4,320	4,700	1.5529
TBA	2	7/1	0.0522	0.0655	1	0.0974	0.1299	0.1299	0.325	61.67	106.5	5,010	5,270	5,840	1.5325
TBA	1	6/1	0.0657	0.0767	1	0.1181	0.1181	0.1181	0.354	77.62	114.7	5,180	5,450	5,920	1.2337
TBA	1/0	6/1	0.0830	0.0968	1	0.1327	0.1327	0.1327	0.398	98.06	144.6	6,390	6,650	7,250	0.9767
TBA	2/0	6/1	0.1045	0.1219	1	0.1489	0.1489	0.1489	0.447	123.5	182.2	7,960	8,290	9,040	0.7757
TBA	3/0	6/1	0.1317	0.1537	1	0.1672	0.1672	0.1672	0.502	155.6	229.8	10,000	10,500	11,400	0.6155
TBA	4/0	6/1	0.1662	0.1939	1	0.1878	0.1878	0.1878	0.563	196.4	289.8	12,700	13,200	14,400	0.4877
TBA	13.125	3/4	0.0103	0.0240	0.5	0.0661	0.0661	---	0.198	12.17	58.87	3,240	3,570	4,230	6.7079
TBA	20.87	3/4	0.0164	0.0383	0.5	0.0834	0.0834	---	0.250	19.38	94.04	5,160	5,680	6,730	4.2100
TBA	33.185	3/4	0.0261	0.0609	0.5	0.1052	0.1052	---	0.316	30.84	149.4	8,040	8,880	10,400	2.6461
TBA	52.77	3/4	0.0414	0.0966	0.5	0.1326	0.1326	---	0.398	48.91	237.1	12,700	13,800	16,100	1.6682
TBA	54.95	7/1	0.0432	0.0542	1	0.0886	0.1181	0.1181	0.295	51.04	88.13	4,140	4,410	4,880	1.8518
TBA	57.50	3/4	0.0451	0.1053	0.5	0.1384	0.1384	---	0.415	53.28	258.5	13,800	15,000	17,600	1.5310
TBA	66.54	3/4	0.0522	0.1219	0.5	0.1489	0.1489	---	0.447	61.67	299.3	15,700	17,000	20,000	1.3227
TBA	80.00	8/1	0.0628	0.0846	1	0.1000	0.1667	0.1667	0.367	74.56	148.1	7,090	7,500	8,450	1.2625
TBA	101.8	12/7	0.0799	0.1265	1	0.0921	0.0921	0.2763	0.461	95.33	253.1	12,900	14,000	16,000	0.9635
TBA	110.8	12/7	0.0870	0.1378	1	0.0961	0.0961	0.2883	0.481	103.8	275.8	14,000	15,200	17,400	0.8848
TBA	134.6	12/7	0.1057	0.1674	1	0.1059	0.1059	0.3177	0.530	126.1	335.0	17,000	18,500	21,100	0.7283
TBA	159.0	12/7	0.1249	0.1977	1	0.1151	0.1151	0.3453	0.576	149.0	395.5	20,100	21,800	25,000	0.6164
TBA	176.9	12/7	0.1389	0.2199	1	0.1214	0.1214	0.3642	0.607	165.7	439.9	22,300	23,900	27,400	0.5542
TBA	190.8	12/7	0.1499	0.2373	1	0.1261	0.1261	0.3783	0.631	178.8	474.7	24,100	25,800	29,600	0.5136
TBA	203.0	8/7	0.1594	0.2025	1	0.1593	0.0885	0.2655	0.584	189.3	335.2	15,700	16,800	18,800	0.5032
TBA	203.2	16/19	0.1596	0.3020	1	0.1127	0.0977	0.4885	0.714	190.4	673.5	34,500	37,800	43,800	0.4621
TBA	211.3	12/7	0.1660	0.2628	1	0.1327	0.1327	0.3981	0.664	198.1	525.8	26,400	28,200	32,400	0.4638
TBA	228.2	18/1	0.1792	0.1892	2	0.1126	0.1126	0.1126	0.563	212.8	246.5	9,960	10,200	10,600	0.4623
TBA	266.8	18/1	0.2094	0.2210	2	0.1217	0.1217	0.1217	0.609	248.6	287.7	11,600	11,900	12,400	0.3956
TBA	266.8	22/7	0.2095	0.2301	2	0.1101	0.0612	0.1836	0.624	250.0	319.7	13,500	14,000	15,000	0.3948
TBA	266.8	24/7	0.2094	0.2366	2	0.1054	0.0703	0.2109	0.633	249.8	341.9	14,800	15,500	16,800	0.3931
TBA	266.8	26/7	0.2095	0.2436	2	0.1013	0.0788	0.2364	0.642	250.0	365.4	16,200	17,100	18,700	0.3909
TBA	266.8	30/7	0.2095	0.2584	2	0.0943	0.0943	0.2829	0.660	250.6	416.2	19,000	20,100	22,300	0.3877
TBA	266.8	45/7	0.2095	0.2240	3	0.0770	0.0513	0.1539	0.616	250.0	299.1	12,100	12,400	13,100	0.3965
TBA	286.2	18/19	0.2248	0.4621	1	0.1261	0.1261	0.6305	0.883	268.2	1073.0	55,600	60,000	69,900	0.3209
TBA	300.0	26/7	0.2355	0.2738	2	0.1074	0.0835	0.2505	0.680	281.0	410.7	18,200	19,200	21,000	0.3478
TBA	336.4	18/1	0.2642	0.2789	2	0.1367	0.1367	0.1367	0.684	313.7	363.3	14,200	14,500	15,100	0.3136
TBA	336.4	20/7	0.2642	0.2824	2	0.1297	0.0576	0.1728	0.692	315.2	376.8	15,000	15,400	16,300	0.3145
TBA	336.4	22/7	0.2644	0.2903	2	0.1237	0.0687	0.2061	0.701	315.5	403.2	17,000	17,700	18,900	0.3128
TBA	336.4	24/7	0.2642	0.2984	2	0.1184	0.0789	0.2367	0.710	315.2	431.0	18,700	19,500	21,200	0.3116

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Stock Number	Conductor Size	Stranding	Cross-Sectional Area		Layers of Al Alloy	Diameter				Weight		Rated Breaking Strength			DC Resistance @ 20°C
						Individual Strands		Steel Core	Complete Conductor						
			Al Alloy	Total		Al Alloy	St			Al Alloy	Total	Std	HS	UHS	
	AWG/kcmil	Al/St	in²	in²		in	in	in	in	lb/1000 ft	lb/1000 ft	lb	lb	lb	Ω/mile
TBA	336.4	26/7	0.2640	0.3070	2	0.1137	0.0884	0.2652	0.720	315.0	460.6	20,400	21,500	23,500	0.3102
TBA	336.4	30/7	0.2642	0.3259	2	0.1059	0.1059	0.3177	0.741	316.0	524.9	23,900	25,400	28,100	0.3074
TBA	397.5	18/1	0.3122	0.3295	2	0.1486	0.1486	0.1486	0.743	370.7	429.0	16,700	17,000	17,800	0.2654
TBA	397.5	20/7	0.3123	0.3339	2	0.1410	0.0627	0.1881	0.752	372.6	445.7	17,700	18,200	19,300	0.2660
TBA	397.5	22/7	0.3121	0.3428	2	0.1344	0.0747	0.2241	0.762	372.4	476.3	19,500	20,300	21,700	0.2650
TBA	397.5	24/7	0.3122	0.3527	2	0.1287	0.0858	0.2574	0.772	372.5	509.6	21,500	22,500	24,400	0.2636
TBA	397.5	26/7	0.3120	0.3628	2	0.1236	0.0961	0.2883	0.783	372.2	544.2	23,900	25,100	27,300	0.2625
TBA	397.5	30/7	0.3121	0.3849	2	0.1151	0.1151	0.3453	0.806	373.3	619.8	28,300	30,000	33,200	0.2602
TBA	477.0	18/1	0.3747	0.3955	2	0.1628	0.1628	0.1628	0.814	444.9	515.0	20,000	20,400	21,300	0.2211
TBA	477.0	20/7	0.3745	0.4004	2	0.1544	0.0686	0.2058	0.823	446.8	534.5	21,200	21,900	23,100	0.2218
TBA	477.0	22/7	0.3744	0.4112	2	0.1472	0.0818	0.2454	0.834	446.7	571.3	23,400	24,300	26,100	0.2209
TBA	477.0	24/7	0.3747	0.4233	2	0.1410	0.0940	0.2820	0.846	447.1	611.6	25,600	26,800	28,900	0.2197
TBA	477.0	26/7	0.3744	0.4354	2	0.1354	0.1053	0.3159	0.858	446.7	653.2	28,000	29,500	32,100	0.2187
TBA	477.0	30/7	0.3747	0.4621	2	0.1261	0.1261	0.3783	0.883	448.1	744.0	33,900	35,600	39,400	0.2168
TBA	500.0	30/7	0.3927	0.4843	2	0.1291	0.1291	0.3873	0.904	469.7	779.8	34,800	36,600	40,600	0.2068
TBA	556.5	18/1	0.4369	0.4612	2	0.1758	0.1758	0.1758	0.879	518.7	600.6	23,400	23,800	24,900	0.1896
TBA	556.5	20/7	0.4370	0.4672	2	0.1668	0.0741	0.2223	0.890	521.4	623.6	24,800	25,500	27,000	0.1901
TBA	556.5	22/7	0.4368	0.4797	2	0.1590	0.0883	0.2649	0.901	521.1	666.3	27,300	28,400	30,400	0.1893
TBA	556.5	24/7	0.4372	0.4938	2	0.1523	0.1015	0.3045	0.914	521.6	713.2	29,900	31,200	33,700	0.1883
TBA	556.5	26/7	0.4371	0.5083	2	0.1463	0.1138	0.3414	0.927	521.5	762.5	32,700	34,400	37,500	0.1874
TBA	556.5	30/7	0.4371	0.5391	2	0.1362	0.1362	0.4086	0.953	522.8	868.1	38,800	40,700	45,100	0.1858
TBA	605.0	24/7	0.4753	0.5370	2	0.1588	0.1059	0.3177	0.953	567.1	776.0	32,500	33,900	36,600	0.1732
TBA	605.0	26/7	0.4749	0.5522	2	0.1525	0.1186	0.3558	0.966	566.6	828.3	35,500	37,400	40,700	0.1724
TBA	605.0	30/7	0.4751	0.5860	2	0.1420	0.1420	0.4260	0.994	568.2	943.7	41,600	43,700	48,500	0.1709
TBA	605.0	30/19	0.4751	0.5834	2	0.1420	0.0852	0.4260	0.994	568.2	935.6	41,500	44,000	49,000	0.1711
TBA	605.0	54/7	0.4747	0.5362	3	0.1058	0.1058	0.3174	0.952	566.4	774.6	32,800	34,300	37,000	0.1734
TBA	636.0	18/1	0.4997	0.5275	2	0.1880	0.1880	0.1880	0.940	593.3	687.0	26,700	27,200	28,400	0.1658
TBA	636.0	36/1	0.4994	0.5133	3	0.1329	0.1329	0.1329	0.930	592.9	639.8	23,600	23,900	24,500	0.1666
TBA	636.0	20/7	0.4994	0.5339	2	0.1783	0.0792	0.2376	0.951	595.8	712.6	28,300	29,100	30,800	0.1664
TBA	636.0	22/7	0.4994	0.5484	2	0.1700	0.0944	0.2832	0.963	595.8	761.7	31,000	32,200	34,300	0.1656
TBA	636.0	24/7	0.4996	0.5643	2	0.1628	0.1085	0.3255	0.977	596.1	815.1	34,100	35,700	38,500	0.1648
TBA	636.0	26/7	0.4995	0.5808	2	0.1564	0.1216	0.3648	0.990	596.0	871.2	37,400	38,900	42,400	0.1640
TBA	636.0	30/7	0.4995	0.6160	2	0.1456	0.1456	0.4368	1.019	597.4	991.8	43,700	46,000	51,000	0.1626
TBA	636.0	30/19	0.4995	0.6135	2	0.1456	0.0874	0.4370	1.019	597.4	984.1	43,600	46,300	51,600	0.1627
TBA	636.0	54/7	0.4993	0.5640	3	0.1085	0.1085	0.3255	0.977	595.7	814.7	34,500	36,100	38,900	0.1649
TBA	666.6	24/7	0.5238	0.5917	2	0.1667	0.1111	0.3333	1.000	624.9	854.8	35,800	37,400	40,300	0.1571
TBA	666.6	26/7	0.5234	0.6086	2	0.1601	0.1245	0.3735	1.014	624.5	912.9	39,200	40,800	44,500	0.1565
TBA	666.6	54/7	0.5235	0.5914	3	0.1111	0.1111	0.3333	1.000	624.6	854.5	36,200	37,800	40,800	0.1572
TBA	715.5	24/7	0.5622	0.6350	2	0.1727	0.1151	0.3453	1.036	670.8	917.3	38,400	40,100	43,300	0.1464
TBA	715.5	26/7	0.5620	0.6535	2	0.1659	0.1290	0.3870	1.051	670.5	980.3	42,000	43,800	47,800	0.1457
TBA	715.5	30/19	0.5617	0.6897	2	0.1544	0.0926	0.4630	1.081	671.8	1106	48,400	51,400	56,800	0.1447
TBA	715.5	54/7	0.5619	0.6347	3	0.1151	0.1151	0.3453	1.036	670.4	916.9	38,900	40,600	43,800	0.1465

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Stock Number	Conductor Size	Stranding	Cross-Sectional Area		Layers of Al Alloy	Diameter				Weight		Rated Breaking Strength			DC Resistance @ 20°C
						Individual Strands		Steel Core	Complete Conductor						
			Al Alloy	Total		Al Alloy	St			Al Alloy	Total	Std	HS	UHS	
	AWG/kcmil	Al/St	in²	in²		in	in	in	in	lb/1000 ft	lb/1000 ft	lb	lb	lb	Ω/mile
TBA	795.0	36/1	0.6244	0.6417	3	0.1486	0.1486	0.1486	1.040	741.3	799.6	29,500	29,800	30,500	0.1333
TBA	795.0	24/7	0.6244	0.7053	2	0.1820	0.1213	0.3639	1.092	745.0	1019	42,600	44,200	47,700	0.1318
TBA	795.0	26/7	0.6247	0.7264	2	0.1749	0.1360	0.4080	1.108	745.3	1090	46,700	48,700	53,100	0.1311
TBA	795.0	30/7	0.6245	0.7702	2	0.1628	0.1628	0.4884	1.140	746.9	1240	54,700	57,500	63,800	0.1301
TBA	795.0	30/19	0.6245	0.7669	2	0.1628	0.0977	0.4885	1.140	746.9	1230	53,900	57,200	63,100	0.1302
TBA	795.0	42/7	0.6246	0.6567	3	0.1376	0.0764	0.2292	1.055	745.2	853.9	32,600	33,400	34,900	0.1334
TBA	795.0	45/7	0.6242	0.6674	3	0.1329	0.0886	0.2658	1.063	744.7	891.0	34,800	35,900	37,900	0.1331
TBA	795.0	54/7	0.6240	0.7049	3	0.1213	0.1213	0.3639	1.092	744.5	1018	43,200	44,700	48,200	0.1319
TBA	900.0	45/7	0.7066	0.7555	3	0.1414	0.0943	0.2829	1.131	843.0	1009	39,200	40,400	42,500	0.1176
TBA	900.0	54/7	0.7069	0.7985	3	0.1291	0.1291	0.3873	1.162	843.4	1154	47,600	49,400	53,300	0.1164
TBA	954.0	30/7	0.7491	0.9239	2	0.1783	0.1783	0.5349	1.248	895.9	1488	65,600	69,000	76,500	0.1084
TBA	954.0	30/19	0.7491	0.9199	2	0.1783	0.1070	0.5350	1.248	895.9	1475	64,600	68,600	75,700	0.1085
TBA	954.0	42/7	0.7491	0.7876	3	0.1507	0.0837	0.2511	1.155	893.8	1024	39,100	40,000	41,900	0.1112
TBA	954.0	45/7	0.7492	0.8010	3	0.1456	0.0971	0.2913	1.165	893.9	1069	41,600	42,800	45,000	0.1109
TBA	954.0	48/7	0.7495	0.8157	3	0.1410	0.1097	0.3291	1.175	894.2	1118	44,400	46,000	48,800	0.1105
TBA	954.0	54/7	0.7491	0.8462	3	0.1329	0.1329	0.3987	1.196	893.8	1223	50,500	52,300	56,500	0.1099
TBA	1033.5	42/7	0.8121	0.8539	3	0.1569	0.0872	0.2616	1.203	968.9	1110	42,400	43,400	45,400	0.1026
TBA	1033.5	45/7	0.8112	0.8673	3	0.1515	0.1010	0.3030	1.212	967.8	1158	45,000	46,300	48,800	0.1024
TBA	1033.5	48/7	0.8113	0.8829	3	0.1467	0.1141	0.3423	1.223	968.0	1210	48,000	49,800	52,900	0.1021
TBA	1033.5	54/7	0.8112	0.9164	3	0.1383	0.1383	0.4149	1.245	967.8	1324	54,700	56,700	61,200	0.1015
TBA	1113.0	42/7	0.8743	0.9192	3	0.1628	0.0904	0.2712	1.248	1043	1195	45,400	46,500	48,500	0.0953
TBA	1113.0	45/7	0.8745	0.9350	3	0.1573	0.1049	0.3147	1.259	1043	1248	48,500	50,000	52,600	0.0950
TBA	1113.0	48/7	0.8744	0.9516	3	0.1523	0.1185	0.3555	1.269	1043	1304	51,800	53,700	57,000	0.0947
TBA	1113.0	54/19	0.8746	0.9855	3	0.1436	0.0862	0.4310	1.293	1049	1425	58,300	60,800	66,000	0.0946
TBA	1192.5	42/7	0.9366	0.9848	3	0.1685	0.0936	0.2808	1.292	1117	1280	48,700	49,800	51,900	0.0889
TBA	1192.5	45/7	0.9367	1.0014	3	0.1628	0.1085	0.3255	1.302	1118	1337	51,900	53,500	56,300	0.0887
TBA	1192.5	48/7	0.9364	1.0190	3	0.1576	0.1226	0.3678	1.313	1117	1397	55,500	57,000	60,600	0.0885
TBA	1192.5	54/19	0.9365	1.0552	3	0.1486	0.0892	0.4460	1.338	1123	1526	62,400	65,200	70,700	0.0884
TBA	1272.0	42/7	0.9987	1.0501	3	0.1740	0.0967	0.2901	1.334	1192	1366	51,900	53,200	55,400	0.0834
TBA	1272.0	45/7	0.9987	1.0678	3	0.1681	0.1121	0.3363	1.345	1192	1426	55,400	57,100	60,000	0.0832
TBA	1272.0	48/7	0.9992	1.0873	3	0.1628	0.1266	0.3798	1.357	1192	1490	59,200	60,900	64,700	0.0829
TBA	1272.0	54/19	0.9993	1.1259	3	0.1535	0.0921	0.4605	1.382	1198	1628	66,000	68,900	74,200	0.0828
TBA	1351.5	42/7	1.0617	1.1163	3	0.1794	0.0997	0.2991	1.376	1267	1452	55,200	56,500	58,900	0.0785
TBA	1351.5	45/7	1.0614	1.1347	3	0.1733	0.1155	0.3465	1.386	1266	1514	58,900	60,600	63,800	0.0783
TBA	1351.5	54/19	1.0614	1.1958	3	0.1582	0.0949	0.4745	1.424	1273	1729	70,100	73,200	78,800	0.0780
TBA	1431.0	42/7	1.1241	1.1820	3	0.1846	0.1026	0.3078	1.415	1341	1537	58,400	59,800	62,300	0.0741
TBA	1431.0	45/7	1.1236	1.2013	3	0.1783	0.1189	0.3567	1.427	1341	1604	62,300	64,200	67,600	0.0739
TBA	1431.0	48/7	1.1244	1.2236	3	0.1727	0.1343	0.4029	1.439	1342	1678	66,600	68,500	72,800	0.0737
TBA	1431.0	54/19	1.1241	1.2665	3	0.1628	0.0977	0.4885	1.465	1348	1831	74,200	77,500	83,500	0.0736
TBA	1510.5	45/7	1.1862	1.2682	3	0.1832	0.1221	0.3663	1.466	1415	1693	65,800	67,400	70,900	0.0700
TBA	1510.5	54/19	1.1856	1.3357	3	0.1672	0.1003	0.5015	1.505	1421	1930	78,300	81,700	88,000	0.0698
TBA	1590.0	45/7	1.2492	1.3355	3	0.1880	0.1253	0.3759	1.504	1490	1782	69,300	70,900	74,700	0.0665

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Stock Number	Conductor Size	Stranding	Cross-Sectional Area		Layers of Al Alloy	Diameter				Weight		Rated Breaking Strength			DC Resistance @ 20°C
						Individual Strands		Steel Core	Complete Conductor						
			Al Alloy	Total		Al Alloy	St			Al Alloy	Total	Std	HS	UHS	
	AWG/kcmil	Al/St	in²	in²		in	in	in	in	lb/1000 ft	lb/1000 ft	lb	lb	lb	Ω/mile
TBA	1590.0	48/7	1.2487	1.3589	3	0.1820	0.1416	0.4248	1.517	1490	1863	73,400	75,600	80,300	0.0663
TBA	1590.0	54/19	1.2489	1.4072	3	0.1716	0.1030	0.5150	1.545	1497	2034	82,500	86,100	92,800	0.0663
TBA	1780.0	84/19	1.3986	1.5126	4	0.1456	0.0874	0.4370	1.602	1677	2064	80,200	82,800	88,100	0.0596
TBA	1843.0	72/7	1.4476	1.5102	4	0.1600	0.1067	0.3201	1.600	1736	1948	72,300	73,800	76,500	0.0579
TBA	1869.0	68/7	1.4681	1.5147	4	0.1658	0.0921	0.2763	1.603	1760	1918	70,000	71,100	73,100	0.0572
TBA	2034.5	72/7	1.5979	1.6670	4	0.1681	0.1121	0.3363	1.681	1916	2150	79,800	81,400	84,400	0.0525
TBA	2057.0	76/19	1.6152	1.7032	4	0.1645	0.0768	0.3840	1.700	1936	2235	84,100	86,100	90,200	0.0518
TBA	2156.0	84/19	1.6931	1.8309	4	0.1602	0.0961	0.4805	1.762	2030	2497	96,400	99,600	105,300	0.0492
TBA	2167.0	72/7	1.7022	1.7758	4	0.1735	0.1157	0.3471	1.735	2041	2290	85,000	86,700	89,900	0.0492
TBA	2312.0	76/19	1.8155	1.9144	4	0.1744	0.0814	0.4070	1.802	2177	2513	94,500	96,800	101,400	0.0461
TBA	2515.0	76/19	1.9750	2.0826	4	0.1819	0.0849	0.4245	1.880	2368	2733	102,800	105,300	110,300	0.0424

Copyright © 2026 Southwire Company, LLC. All Rights Reserved