Armorlite® Type AC THHN/THWN Circuit Size Copper Conductor 120/208V Colors

14 AWG through 10 AWG THHN/THWN Insulated Singles Wrapped in Moisture-Resistant, Flame-Retardant Paper. 16 AWG Aluminum Bond Wire. UL Listed. 600 Volts. Rated VW-1. Lightweight Aluminum Interlocked Armor.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid copper per ASTM B3
2. **Insulation:** Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Paper Covering:** Moisture-resistant, flame-retardant paper covering
4. **Bond Wire:** Solid #16 AWG aluminum
5. **Armor:** Aluminum Interlocked Armor

APPLICATIONS AND FEATURES:

Southwire Armorlite® Type AC Cable is suitable for use as follows:

- Branch and service power distribution in commercial, industrial, institutional, and multi-residential buildings
- Fished or embedded in plaster
- Concealed or exposed installations
- Dry locations only
- Environmental air-handling spaces per NEC 300.22 (C)
- Installation in cable tray and approved raceways
- Under raised floors for information technology equipment conductors and cables per NEC Article 645
- Conductors are individually wrapped with a moisture-resistant, flame-retardant paper covering
- Type THHN/THWN rated 90ºC dry
- Anti-Short bushing are required

Southwire Armorlite® Type AC Cable meets or exceeds the following requirements:

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 320
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 4 Armored Cables
- RoHS-2 (European Directive 2011/65/EU)

Copyright © 2026 Southwire Company, LLC. All Rights Reserved
UPDATED: Jan. 7, 2026, 8:22 p.m.UTC REVISION: 1.000.008

- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

SAMPLE PRINT LEGEND:

TYPE AC-THH AL ARMOR COPPER THHN CONDUCTORS W/ ALUMINUM BOND WIRE MAXIMUM VOLTS 600V, FOR USE IN CABLE TRAYS-90(D) C - DRY LOCATIONS GAS. & OIL REST.COND.(AL.BOND WIRE)-NOT FOR USE ON DC CIRCUITS *CAUTION:NOT TO BE USED WITH SETSCREW CONNECTOR

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Diameter Over Armor	Copper Weight	Overall Weight
	AWG/ Kcmil			inch		mils	inch	lbs/1000ft	lbs/1000ft
14 AWG | SOLID Strands									
610293	14	2	BK,WE	0.064	SOLID	15	0.468	25	88
610294	14	3	BK,RD,WE	0.064	SOLID	15	0.488	37	108
610296	14	4	BK,RD,BE,WE	0.064	SOLID	15	0.52	50	128
12 AWG | SOLID Strands									
610231	12	2	BK,WE	0.081	SOLID	15	0.502	40	108
553270	12	2	BN,GY	0.081	SOLID	15	0.502	40	108
553273	12	2	GY,OE	0.081	SOLID	15	0.502	40	109
553274	12	2	GY,YW	0.081	SOLID	15	0.502	40	108
610232	12	3	BK,RD,WE	0.081	SOLID	15	0.524	59	136
553276	12	3	BN,GY,OE	0.081	SOLID	15	0.524	59	136
610297	12	4	BK,RD,BE,WE	0.081	SOLID	15	0.561	79	165
10 AWG | SOLID Strands									
610298	10	2	BK,WE	0.102	SOLID	20	0.556	61	139
610299	10	3	BK,RD,WE	0.102	SOLID	20	0.583	92	180
610300	10	4	BK,RD,BE,WE	0.102	SOLID	20	0.626	123	222

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 2 – Electrical and Engineering Data

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/ Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
14 AWG | SOLID Strands							
14	2	3.3	2.631	3.265	0.058	20	25
14	3	3.4	2.631	3.265	0.058	20	25
14	4	3.6	2.631	3.265	0.058	16	20
12 AWG | SOLID Strands							
12	2	3.5	1.662	2.063	0.054	25	30
12	2	3.5	1.662	2.063	0.054	25	30
12	2	3.5	1.662	2.063	0.054	25	30
12	2	3.5	1.662	2.063	0.054	25	30
12	3	3.7	1.662	2.063	0.054	25	30
12	3	3.7	1.662	2.063	0.054	25	30
12	4	3.9	1.662	2.063	0.054	20	24
10 AWG | SOLID Strands							
10	2	3.9	1.04	1.291	0.05	35	40
10	3	4.1	1.04	1.291	0.05	35	40
10	4	4.4	1.04	1.291	0.05	28	32

***** Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

***** Ampacities have been adjusted for more than Three Current-Carrying Conductors.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved