



CU 600 V PE/PVC Insulation

Single Conductor 600 Volt Copper Conductors, Polyethylene and Polyvinyl Chloride (PE/PVC) Insulation. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** 7 strands class B compressed bare copper per ASTM B3 and ASTM B8
2. **Insulation:** 30 mils Polyethylene (PE)
3. **Jacket:** 15 mils Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 600 Volt control cables are suited for use in wet and dry areas, conduits, ducts, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 75°C for normal operation in wet and dry locations, 90°C for emergency overload, and 150°C for short circuit conditions.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE 12 AWG CU PE/PVC 600V 75(D)C SUN. RES.



Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance	Min Bending Radius	Allowable Ampacity 75°C	Allowable Ampacity 90°C	Jacket Color
	AWG	No.	strands	inch	mil	mil	inch	lb / 1000ft	lb / 1000ft	Ω /1000ft	Ω /1000ft	Ω/1000ft	inch	Amp	Amp	
12 AWG																
621324	12	1	7	0.088	30	15	0.188	20	30	1.662	2.002	0.054	0.8	25	30	RD
621323	12	1	7	0.088	30	15	0.188	20	30	1.662	2.002	0.054	0.8	25	30	GN
621322	12	1	7	0.088	30	15	0.188	20	30	1.662	2.002	0.054	0.8	25	30	WE
621320	12	1	7	0.088	30	15	0.188	20	30	1.662	2.002	0.054	0.8	25	30	RD/BK
621317	12	1	7	0.088	30	15	0.188	20	30	1.662	2.002	0.054	0.8	25	30	GN/BK
621325	12	1	7	0.088	30	15	0.188	20	30	1.662	2.002	0.054	0.8	25	30	BK
621321	12	1	7	0.088	30	15	0.188	20	30	1.662	2.002	0.054	0.8	25	30	BE
621319	12	1	7	0.088	30	15	0.188	20	30	1.662	2.002	0.054	0.8	25	30	WE/BK
2 AWG																
626221	2	1	7	0.282	45	45	0.563	204	241	0.162	0.195	0.045	6.8	115	130	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.