600V AMERICAN MUSTANG® SOOW Cord with Yellow Jacket 105°C. MSHA Approved

600V, 105°C Flexible Cord. Heat, Moisture and Oil Resistant EPDM Rubber Insulation and Heat, Moisture and Oil Resistant Flexible CPE Jacket, UL/CSA Listed.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K stranded bare copper per ASTM B-174
2. **Insulation:** Heat, moisture and oil resistant EPDM
3. **Filler:** Waxed paper or rubber fillers, with a full cotton serve or paper separator wrapped around the assembly
4. **Jacket:** Yellow CPE (Other colors available upon request)

APPLICATIONS AND FEATURES:

Southwire Type SOOW Flexible Cords UL/ CSA listed are permitted for use as specified by Article 400 and related articles of the 2014 National Electrical Code. The cable is rated -40°C to 105°C, water, oil, and weather resistant. Southwire Type SOOW Flexible Cords are designed for extra hard usage on industrial equipment, heavy tools, battery chargers, portable lights, welding leads, marine dockside power, power extensions and mining applications.

SPECIFICATIONS:

- UL 62 Flexible Cords and Cables
- CSA C22.2 No. 49 Flexible Cords and Cables
- MSHA flame test - P07-KA070018-1MSHA
- Passes CSA FT2 Flame Test
- RoHS-3 Complies with European Directive 2015/863
- NEC Article 400 Flexible Cords, Cables and Fixture Wire
- Federal Specification J-C-580B

SAMPLE PRINT LEGEND:

SOUTHWIRE® American Mustang® CORD X/C XX AWG (XXmm2) SOOW E46194 (UL) 600V -40C TO 105C -- CSA LL90458 SOOW 600V -40C TO 105C FT2 WATER RESISTANT

PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Insul. Color	Jacket Color
	AWG/ Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp		
570214	16	2	65	30	70	0.370	74	13	BK,WE	YW
630730	16	3	26	30	70	0.390	90	10	BK,WE,GN	YW
630727	16	4	26	30	65	0.415	106	8	BK,WE,RD,GN	YW
598334	14	2	41	45	90	0.513	133	18	BK,WE	YW
630721	14	3	41	45	85	0.525	157	15	BK,WE,GN	YW
596981	14	4	41	45	85	0.565	193	12	BK,WE,RD,GN	YW
570210	12	3	65	45	115	0.606	217	20	BK,WE,GN	YW
595327	12	3	65	45	115	0.609	218	20	BK,WE,GN	YW
630722	12	4	65	45	115	0.668	274	16	BK,WE,RD,GN	YW
630724	10	3	104	45	115	0.655	280	25	BK,WE,GN	YW
630725	10	4	104	45	105	0.710	336	20	BK,WE,RD,GN	YW

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity *	Insul. Color	Jacket Color
	AWG/ Kcmil	No.	No.	mm	mm	mm	kg/km	Amp		
570214	16	2	65	0.76	1.78	9.40	110	13	BK,WE	YW
630730	16	3	26	0.76	1.78	9.91	134	10	BK,WE,GN	YW
630727	16	4	26	0.76	1.65	10.54	158	8	BK,WE,RD,GN	YW
598334	14	2	41	1.14	2.29	13.03	198	18	BK,WE	YW
630721	14	3	41	1.14	2.16	13.33	234	15	BK,WE,GN	YW
596981	14	4	41	1.14	2.16	14.35	287	12	BK,WE,RD,GN	YW
570210	12	3	65	1.14	2.92	15.39	323	20	BK,WE,GN	YW
595327	12	3	65	1.14	2.92	15.47	324	20	BK,WE,GN	YW
630722	12	4	65	1.14	2.92	16.97	408	16	BK,WE,RD,GN	YW
630724	10	3	104	1.14	2.92	16.64	417	25	BK,WE,GN	YW
630725	10	4	104	1.14	2.67	18.03	500	20	BK,WE,RD,GN	YW

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved