



## Flat Parallel Pump 600 Volt Cable Type THW

600 Volts, Stranded Copper Conductors. Polyvinyl Chloride (PVC) Insulation. Water Well Cable, Moisture Resistant, Flat Parallel. Rated 75°C,




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Solid soft drawn or fully annealed bare copper per ASTM B3. Stranded class B compressed bare copper ASTM B8
2. **Insulation:** Polyvinyl Chloride (PVC) Type THW

### APPLICATIONS AND FEATURES:

For use in residential, farm and industrial water well applications. Grounded and ungrounded water well cable systems. Conductors are twisted and colored black, red, and yellow when supplied with three conductors and green ground. Cable is supplied without an overall jacket.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables

### SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® SUBMERSIBLE PUMP CABLE TYPE THW X AWG (X.XX{mm<sup>2</sup>}) W/GRD 600 VOLTS



**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Conductor	Insul. Thickness	Ground	Approx. OD	Approx. Weight
	AWG/Kcmil	No.	No.	inch	mil	No. x AWG	inch	lb/1000ft
563658◇	14	2	7	0.070	30	1 x 14	0.166 X 0.558	70
563669◇	14	2	7	0.070	30	x None	0.166 X 0.362	46
563659◇	14	3	7	0.070	30	1 x 14	0.166 X 0.745	91
563660◇	12	2	19	0.090	30	1 x 12	0.185 X 0.615	95
563671◇	12	2	19	0.090	30	x None	0.185 X 0.402	63
563661◇	12	3	19	0.090	30	1 x 12	0.185 X 0.830	126
563672◇	12	3	19	0.090	30	x None	0.185 X 0.615	95
563662◇	10	2	19	0.117	30	1 x 10	0.210 X 0.690	136
563673◇	10	2	19	0.117	30	x None	0.209 X 0.448	91
563663◇	10	3	19	0.117	30	1 x 10	0.210 X 0.930	182
563674◇	10	3	19	0.117	30	x None	0.210 X 0.690	136
563665◇	8	3	19	0.143	45	1 x 10	0.270 X 1.109	276
563664◇	8	3	19	0.143	45	x None	0.027 X 0.809	202
563666◇	6	3	19	0.179	60	1 x 8	0.304 X 1.272	402
563667◇!	4	3	19	0.226	60	1 x 8	0.365 X 1.490	568

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

\* Cond. Number does not include ground conductor.

! 4 AWG (563667) is all Yellow with identifying stripes printed on the Yellow insulation.

**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance	Max Pull Tension	Max Pull Tension	Min Bending Radius	Allowable Ampacity At 75°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	Ω/1000ft	lb	lb	inch	Amp
14	2.631	3.170	0.058	98	98	2.2	20
14	2.631	3.170	0.058	65	65	1.4	20
14	2.631	3.170	0.058	105	105	3.0	16
12	1.662	2.002	0.054	156	156	2.5	25
12	1.662	2.002	0.054	104	104	1.6	25
12	1.662	2.002	0.054	167	167	3.3	20
12	1.662	2.002	0.054	156	156	2.5	25
10	1.040	1.253	0.050	249	249	2.8	35
10	1.040	1.253	0.050	166	166	1.8	35
10	1.040	1.253	0.050	265	265	3.7	28
10	1.040	1.253	0.050	249	249	2.8	35
8	0.653	0.786	0.052	422	422	5.5	40
8	0.653	0.786	0.052	396	396	3.2	50
6	0.411	0.495	0.051	671	671	6.4	52
4	0.258	0.310	0.048	1068	1068	7.5	68

