



28kV AL 133% TRXLPE Full Neutral LLDPE

Single Conductor, 345 Mils Tree Retardant Cross Linked Polyethylene, 133% Insulation Level, Full Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Moisture blocked class B compressed Aluminum ASTM B231 1350 ¾ hard H16/H26 (Non Moisture Blocked Optional)
2. **Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; Supersmooth conductor shield optional; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
3. **Insulation:** 345 Mils Tree Retardant Cross Linked Polyethylene 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Neutral:** Helically applied soft drawn bare copper full concentric neutral
6. **Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 28kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation, 130°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ASTM B609 Standard Specification for Aluminum 1350 Round Wire, Annealed and Intermediate Tempers, for Electrical Purposes
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] AL 28000 VOLTS TRXLPE INSULATION 345 MILS -- (NESC) --
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET





Table 1 – Weights and Measurements

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
1 (Solid)	0.289	1.017	345	1.127	13x14	0.202	50	1.355	865	10.8	502
1 (19)	0.322	1.050	345	1.160	13x14	0.202	50	1.388	890	11.1	502
1/0 (Solid)	0.324	1.052	345	1.162	16x14	0.164	50	1.390	953	11.1	633
1/0 (19)	0.351	1.079	345	1.189	16x14	0.164	50	1.417	973	11.3	633
2/0 (19)	0.395	1.123	345	1.233	20x14	0.131	50	1.461	1088	11.7	798
3/0 (19)	0.443	1.171	345	1.281	25x14	0.105	50	1.509	1225	12.1	1006
4/0 (19)	0.498	1.226	345	1.336	20x12	0.083	50	1.598	1388	12.8	1269
250 (37)	0.558	1.294	345	1.404	24x12	0.069	75	1.716	1647	13.7	1500
350 (37)	0.661	1.397	345	1.507	21x10	0.049	75	1.861	2032	14.9	2100

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (Solid)	0.129	0.162	0.077	0.057	0.209	1.0	0.216 + j1.201	0.162 + j0.509	4533	140	170
1 (19)	0.211	0.266	0.072	0.055	0.221	1.1	0.320 + j1.143	0.266 + j0.452	4533	140	170
1/0 (Solid)	0.102	0.128	0.072	0.055	0.223	1.1	0.182 + j1.139	0.128 + j0.448	5579	155	195
1/0 (19)	0.167	0.211	0.069	0.054	0.233	1.1	0.265 + j1.099	0.211 + j0.410	5579	155	195
2/0 (19)	0.133	0.167	0.064	0.052	0.249	1.2	0.221 + j1.048	0.167 + j0.360	6974	180	220
3/0 (19)	0.105	0.132	0.060	0.050	0.266	1.3	0.186 + j1.002	0.132 + j0.316	8718	205	250
4/0 (19)	0.084	0.105	0.056	0.049	0.287	1.4	0.159 + j0.958	0.105 + j0.276	11081	235	285
250 (37)	0.071	0.090	0.051	0.048	0.311	1.5	0.144 + j0.920	0.090 + j0.243	13298	254	307
350 (37)	0.050	0.065	0.046	0.045	0.348	1.7	0.119 + j0.870	0.065 + j0.199	18496	305	365





*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.

Table 3 – Weights and Measurements (Metric)

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
1 (Solid)	7.34	25.83	8.76	28.63	13x14	0.66	1.27	34.42	1287	274.32	2234
1 (19)	8.18	26.67	8.76	29.46	13x14	0.66	1.27	35.26	1324	281.94	2234
1/0 (Solid)	8.23	26.72	8.76	29.51	16x14	0.54	1.27	35.31	1418	281.94	2817
1/0 (19)	8.92	27.41	8.76	30.20	16x14	0.54	1.27	35.99	1448	287.02	2817
2/0 (19)	10.03	28.52	8.76	31.32	20x14	0.43	1.27	37.11	1619	297.18	3551
3/0 (19)	11.25	29.74	8.76	32.54	25x14	0.34	1.27	38.33	1823	307.34	4477
4/0 (19)	12.65	31.14	8.76	33.93	20x12	0.27	1.27	40.59	2066	325.12	5647
250 (37)	14.17	32.87	8.76	35.66	24x12	0.23	1.91	43.59	2451	347.98	6675
350 (37)	16.79	35.48	8.76	38.28	21x10	0.16	1.91	47.27	3024	378.46	9345

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor





Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (Solid)	0.4232	0.53	0.0235	0.1870	0.686	3.2808	0.216 + j1.201	0.162 + j0.509	4533	140	170
1 (19)	0.6923	0.87	0.0219	0.1804	0.725	3.6089	0.320 + j1.143	0.266 + j0.452	4533	140	170
1/0 (Solid)	0.3346	0.42	0.0219	0.1804	0.732	3.6089	0.182 + j1.139	0.128 + j0.448	5579	155	195
1/0 (19)	0.5479	0.69	0.0210	0.1772	0.764	3.6089	0.265 + j1.099	0.211 + j0.410	5579	155	195
2/0 (19)	0.4364	0.55	0.0195	0.1706	0.817	3.9370	0.221 + j1.048	0.167 + j0.360	6974	180	220
3/0 (19)	0.3445	0.43	0.0183	0.1640	0.873	4.2651	0.186 + j1.002	0.132 + j0.316	8718	205	250
4/0 (19)	0.2756	0.34	0.0171	0.1608	0.942	4.5932	0.159 + j0.958	0.105 + j0.276	11081	235	285
250 (37)	0.2329	0.30	0.0155	0.1575	1.020	4.9213	0.144 + j0.920	0.090 + j0.243	13298	254	307
350 (37)	0.1640	0.21	0.0140	0.1476	1.142	5.5774	0.119 + j0.870	0.065 + j0.199	18496	305	365

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.

CN
Calculator

