



# DURAGROUND™ CU 1000V XLPE RHH/RHW-2/RW90 UL & CSA FT4 Tray Rated Ground Cable

Single Copper Conductors, XLPE Insulation, Sunlight Resistant, 1000V, 90°C MAX, -40°C MIN, Gasoline & Oil Resistant



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Insulation:** Cross Linked Polyethylene (XLPE) Type RW90

## APPLICATIONS AND FEATURES:

Suitable for installation in Cable Trays and Underground Duct Banks- As per CE Code limitations (see Rule 12-2202) for grounding and bonding applications.

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- CSA C22.2 No. 38 Thermoset-insulated wires and cables
- CSA SUN RES - for Sunlight Resistant rating
- CT USE Sizes 1/0 AWG and Larger
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- RoHS-2 (European Directive 2011/65/EU)

## SAMPLE PRINT LEGEND:

E30117 {UL} XXXX KCMIL CU RHH-RHW-2 1000V FOR CT USE FT4 SR PR I OR PR II 90°C WET OR DRY -40°C --- {CSA}  
LL90458 XXXX KCMIL (XXX{mm<sup>2</sup>}) RW90 1000V TC FT4 SR -40°C XLPE --- RoHS {MMM/DD/YYYY}



**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Strand	Insul. Thickness	Insulation Color	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Raceway 90°C†
	AWG/ Kcmil	No.	mil		inch	lb/1000ft	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp
TBA	8	7	60	Green	0.261	69	1.0	132	0.653	0.786	0.052	55
TBA	6	7	60	Green	0.300	108	1.2	209	0.411	0.495	0.051	75
TBA	4	7	60	Green	0.345	155	1.3	333	0.258	0.310	0.048	95
649040	2	7	60	Green	0.403	245	1.6	530	0.162	0.195	0.045	130
TBA	1/0	19	80	Green	0.521	382	2.0	844	0.102	0.122	0.044	170
649042	2/0	19	80	Green	0.572	486	2.2	1064	0.081	0.097	0.043	195
TBA	3/0	19	80	Green	0.616	588	2.4	1342	0.064	0.078	0.042	225
649044	4/0	19	80	Green	0.666	743	2.6	1692	0.051	0.062	0.041	260
TBA	250	37	95	Green	0.748	872	2.9	2000	0.043	0.053	0.041	290
649055	350	37	95	Green	0.841	1216	3.3	2800	0.031	0.039	0.040	350
649057	500	37	95	Green	0.966	1702	3.8	4000	0.022	0.029	0.039	430
649059	750	61	110	Green	1.200	2544	6.0	6000	0.014	0.022	0.038	535
649062	1000	61	110	Green	1.349	3349	6.7	8000	0.011	0.018	0.037	615

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

†Ampacities derived from the 2015 Canadian Electrical Code - Table 1 - For single conductor in free air and based on an ambient temperature of 30°C. - Table 2 - for Cable in Conduit. Not more than 3 aluminum conductors in a conduit and based on an ambient temperature of 30°C.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Table 2 – Weights and Measurements (Metric)**

Stock Number	Cond. Size	Strand	Insul. Thickness	Insulation Color	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Raceway 90°C
	AWG/ Kcmil	No.	mm		mm	kg/km	mm	newton	Ω/km	Ω/km	Ω/km	Amp
TBA	8	7	1.52	Green	6.63	103	25.40	587	2.14	2.58	0.1706	55
TBA	6	7	1.52	Green	7.62	161	30.48	930	1.35	1.62	0.1673	75
TBA	4	7	1.52	Green	8.76	231	33.02	1482	0.85	1.02	0.1575	95
649040	2	7	1.52	Green	10.24	365	40.64	2359	0.53	0.64	0.1476	130
TBA	1/0	19	2.03	Green	13.23	568	50.80	3756	0.33	0.40	0.1444	170
649042	2/0	19	2.03	Green	14.53	723	55.88	4735	0.27	0.32	0.1411	195
TBA	3/0	19	2.03	Green	15.65	875	60.96	5972	0.21	0.26	0.1378	225
649044	4/0	19	2.03	Green	16.92	1106	66.04	7529	0.17	0.20	0.1345	260
TBA	250	37	2.41	Green	19.00	1298	73.66	8900	0.14	0.17	0.1345	290
649055	350	37	2.41	Green	21.36	1810	83.82	12460	0.10	0.13	0.1312	350
649057	500	37	2.41	Green	24.54	2533	96.52	17800	0.07	0.10	0.1280	430
649059	750	61	2.79	Green	30.48	3786	152.40	26700	0.05	0.07	0.1247	535
649062	1000	61	2.79	Green	34.26	4984	170.18	35600	0.04	0.06	0.1214	615

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item





†Ampacities derived from the 2015 Canadian Electrical Code - Table 1 - For single conductor in free air and based on an ambient temperature of 30°C. - Table 2 - for Cable in Conduit. Not more than 3 aluminum conductors in a conduit and based on an ambient temperature of 30°C.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

