



EPEC 40 (Schedule 40) With 1250 lb Mule Tape



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- High-Density Polyethylene (HDPE)
- 1250 lb Mule Tape

APPLICATIONS AND FEATURES:

Designed to house and protect wire and cable products in various underground applications for commercial constructions, EV infrastructure expansions, Utility grid-hardening efforts, airports, mass transit, renewables, petrochemical, agriculture, and data centers. May be installed directly buried or encased in concrete as permitted by The National Electrical Code® Article 353. For above ground applications, HDPE conduit must be encased in a minimum of 2 inches of concrete.

SPECIFICATIONS:

- ASTM D3350 Standard Specification for Polyethylene Plastics Pipe and Fittings Materials
- ASTM F2160 Standard Specification for Solid Wall High Density Polyethylene (HDPE) Conduit Based on Controlled Outside Diameter (OD)
- UL 651A High Density Polyethylene (HPDE) Conduit
- CSA [CSA marking is available upon request](#)
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify “Made in the USA Only!” when ordering to ensure your project receives American made products.
- NEMA TC-7 Smooth-Wall Coilable Electrical Polyethylene Conduit

SAMPLE PRINT LEGEND:

{SQFTG} FEET (LOGO) SOUTHWIRE CONDUIT (UL) HDPE X" SCH40 NEMA TC 7 / ASTM F2160 {MMM/DD/YYYY} {MACH/
SHFT/OP}





Table 1 – Physical and Electrical Data

Stock Number	Duct Nominal Size	Duct Nominal Outside Dia.	Duct Min. Wall Thickness	Duct Nominal Inside Dia.	Duct Min. Bending Radius	Duct Max. Pull Tension	Duct Color	Approx. Cable and Duct Weight
	inch	inch	inch	inch	inch	lb		lb/1000ft
632029	0.75	1.050	0.113	0.804	12	710	BLACK	149
632998	0.75	1.050	0.113	0.804	12	710	GRAY	149
631244	1.00	1.315	0.133	1.029	14	1050	BLACK	219
633568	1.00	1.315	0.133	1.029	14	1050	BK/3-ORG Stripes	219
632321	1.00	1.315	0.133	1.029	14	1050	GRAY	219
632344	1.25	1.660	0.140	1.360	18	1420	BLACK	297
633273	1.25	1.660	0.140	1.360	18	1420	GRAY	297
631013	1.50	1.900	0.145	1.590	21	1700	BLACK	354
632345	1.50	1.900	0.145	1.590	21	1700	BK/3-RD Stripes	354
631245	2.00	2.375	0.154	2.047	26	2280	BLACK	475
632112	2.00	2.375	0.154	2.047	26	2280	ORANGE	475
633531	2.00	2.375	0.154	2.047	26	2280	BK/3-ORG Stripes	475
633612	2.50	2.875	0.203	2.445	32	3615	GRAY	749
633070	2.50	2.875	0.203	2.445	32	365	RED	749
632173	3.00	3.500	0.216	3.042	39	4740	BK/3-RD Stripes	981
TBA	4.00	4.500	0.237	3.998	50	6745		1396

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

Cell Classification for HDPE Conduit

Property	Test Method	Value
Density	D4883	0.953 g/cc
Melt Index	D1238	0.25 g/10 min
Flexural Modulus	D790	168,000 psi
Tensile Strength	D638	3900 yield @ 2 in/min
SP-NCLS ESCR	F2136	>1000 hrs
Hydrostatic Design Basis	D2837	N/A

- (PE436580C-BK), (PE436580E-Colors)

CIC Labor Saving Calculator

