



Cable-in-Conduit (CIC) AL 15kV UD Primary EPEC-40/SCH 40



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductors: 15kV AL TRXLPE Full Neutral LLDPE JKT
- Conduit: High-Density Polyethylene (HDPE)

APPLICATIONS AND FEATURES:

Southwire's *SIMPull*® CIC has been utilized by end users in various applications, including the US Department of Transportation (DOT), the US Department of Energy (DOE), commercial constructions, EV infrastructure expansions, Utility grid-hardening efforts, airports, mass transit, renewables, petrochemical, agriculture, and data centers. Manufactured by continuously extruding HDPE loosely around the cable assembly with no adhesion between the conduit and the cable, thus leaving the cables free in the conduit. Lubrication is applied to the cable, allowing for cables to be pulled out and replaced if necessary.

SPECIFICATIONS:

- ASTM D3350 Standard Specification for Polyethylene Plastics Pipe and Fittings Materials
- ASTM D3485 Standard Specification for Coilable High Density Polyethylene (HDPE) Cable in Conduit (CIC)
- ASTM F2160 Standard Specification for Solid Wall High Density Polyethylene (HDPE) Conduit Based on Controlled Outside Diameter (OD)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661
- NEMA TC-7 Smooth-Wall Coilable Electrical Polyethylene Conduit

SAMPLE PRINT LEGEND:

{SQFTG} FEET (LOGO) SOUTHWIRE CABLE IN CONDUIT HDPE X" EPEC-40 NEMA TC 7 / SCH40 ASTM F2160 (NESC)
{MMM/DD/YYYY} {MACH/SHFT/OP}





Table 1 – Physical and Electrical Data

Stock Number	Description	Cable Color	Duct Nominal Size	Duct Nominal Outside Dia.	Duct Min. Wall Thickness	Duct Nominal Inside Dia.	Duct Min. Bending Radius	Duct Max. Pull Tension	Duct Color	Approx. Cable and Duct Weight
			inch	inch	inch	inch	inch	lb		lb/1000ft
630135	1 x #2 AWG STR AL 220 mil 15kV Primary UD	BK/RD Stripe	1.50	1.900	0.145	1.590	21	1700	BK/3-RD Stripes	888
616990	1 x #2 AWG SOL AL 175 mil 15kV Primary UD	BK/RD Stripe	1.50	1.900	0.145	1.590	21	1700	BK/3-RD Stripes	826
630474	1 x #2 AWG SOL AL 220 mil 15kV Primary UD	BK/RD Stripe	1.50	1.900	0.145	1.590	21	1700	BK/3-RD Stripes	865
634368	1 x 4/0 AWG STR AL 220 mi 15kV Primary UD	BK/RD Stripe	2.00	2.375	0.154	2.047	26	2280	RD	1550

All dimensions are nominal and subject to normal manufacturing tolerances
 ◊ Cable marked with this symbol is a standard stock item

Cable Specification

CIC Stock Number	Cable Conductor Size (AWG)	Cable Conductor Strand Count (num)	Cable Specification
630135	2	7	612538* on SPEC 81111
616990	2	7	491167* on SPEC 81101
630474	2	1 (solid)	613418 on SPEC 81111
634368	4/0	19	610406 on SPEC 81111

* See SPEC for similar conductor size and strand count

Cell Classification for HDPE Conduit

Property	Test Method	Value
Density	D4883	0.953 g/cc
Melt Index	D1238	0.25 g/10 min
Flexural Modulus	D790	168,000 psi
Tensile Strength	D638	3900 yield @ 2 in/min
SP-NCLS ESCR	F2136	>1000 hrs
Hydrostatic Design Basis	D2837	N/A

CIC Labor
Saving
Calculator

- (PE436580C-BK), (PE436580E-Colors)

