



## HVTECK AL 1/C 115NLEPR TS PVC AIA PVC 5kV 133% CSA

Single Conductor, 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR), 133% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
2. **Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
3. **Insulation:** 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Inner Jacket:** PVC inner jacket
7. **Armour:** Aluminum Interlocked Armour (AIA)
8. **Overall Jacket:** Orange Polyvinyl Chloride (PVC) Jacket

### APPLICATIONS AND FEATURES:

Southwire's 5kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

### SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)





- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

**SAMPLE PRINT LEGEND:**

(CSA) SOUTHWIRE (NESC) #P# 1/C [#AWG or #kcmil] CPT AL 115 NLEPR AIA 5kV 133% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

**Table 1 – Weights and Measurements**

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Approx. Weight |
|------------|--------|-------------------------|--------------------------|------------------|---------------------------------|------------------------|------------------|--------------------------|------------|----------------|
| AWG/ Kcmil | No.    | inch                    | inch                     | mil              | inch                            | mil                    | inch             | mil                      | inch       | lb/1000ft      |
| 2          | 7      | 0.268                   | 0.536                    | 115              | 0.596                           | 65                     | 0.968            | 50                       | 1.068      | 502            |
| 1          | 19     | 0.298                   | 0.566                    | 115              | 0.626                           | 65                     | 0.998            | 50                       | 1.098      | 539            |
| 1/0        | 19     | 0.336                   | 0.604                    | 115              | 0.664                           | 65                     | 1.036            | 50                       | 1.136      | 585            |
| 2/0        | 19     | 0.376                   | 0.644                    | 115              | 0.704                           | 80                     | 1.106            | 50                       | 1.206      | 671            |
| 3/0        | 19     | 0.422                   | 0.690                    | 115              | 0.750                           | 80                     | 1.152            | 50                       | 1.252      | 736            |
| 4/0        | 19     | 0.474                   | 0.742                    | 115              | 0.802                           | 80                     | 1.204            | 50                       | 1.304      | 813            |
| 250        | 37     | 0.520                   | 0.796                    | 115              | 0.856                           | 80                     | 1.368            | 50                       | 1.468      | 902            |
| 350        | 37     | 0.615                   | 0.891                    | 115              | 0.951                           | 80                     | 1.463            | 50                       | 1.563      | 1063           |
| 500        | 37     | 0.735                   | 1.011                    | 115              | 1.071                           | 80                     | 1.583            | 60                       | 1.703      | 1325           |
| 750        | 61     | 0.908                   | 1.194                    | 115              | 1.254                           | 80                     | 1.790            | 60                       | 1.910      | 1738           |
| 1000       | 61     | 1.060                   | 1.346                    | 115              | 1.406                           | 80                     | 1.942            | 60                       | 2.062      | 2184           |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.



**Table 2 – Electrical and Engineering Data**

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Phase Short Circuit Current @ 6 Cycles | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|-------------------------|-----------------------------|--|--------------------------------|---|
| AWG/Kcmil  | inch               | lb               | Ω/1000ft             | Ω/1000ft             | MΩ*1000ft                   | Ω/1000ft                   | Ω/1000ft                | Ω/1000ft                    | Amp                                    | Amp                            | Amp                                     |
| 2          | 12.8               | 398              | 0.267                | 0.336                | 0.032                       | 0.053                      | 0.690 + j0.516          | 0.337 + j0.053              | 1877                                   | 169                            | 176                                     |
| 1          | 13.2               | 502              | 0.211                | 0.266                | 0.030                       | 0.052                      | 0.623 + j0.498          | 0.267 + j0.050              | 1970                                   | 194                            | 198                                     |
| 1/0        | 13.6               | 633              | 0.168                | 0.211                | 0.027                       | 0.050                      | 0.571 + j0.478          | 0.212 + j0.048              | 2088                                   | 222                            | 223                                     |
| 2/0        | 14.5               | 798              | 0.133                | 0.167                | 0.025                       | 0.048                      | 0.529 + j0.457          | 0.168 + j0.047              | 2212                                   | 255                            | 250                                     |
| 3/0        | 15.0               | 1006             | 0.105                | 0.133                | 0.023                       | 0.047                      | 0.496 + j0.435          | 0.134 + j0.045              | 2354                                   | 290                            | 278                                     |
| 4/0        | 15.6               | 1269             | 0.084                | 0.105                | 0.021                       | 0.045                      | 0.469 + j0.411          | 0.106 + j0.043              | 2515                                   | 329                            | 309                                     |
| 250        | 17.6               | 1500             | 0.071                | 0.090                | 0.019                       | 0.046                      | 0.452 + j0.389          | 0.091 + j0.044              | 2683                                   | 370                            | 347                                     |
| 350        | 18.8               | 2100             | 0.050                | 0.065                | 0.017                       | 0.043                      | 0.423 + j0.352          | 0.066 + j0.042              | 2977                                   | 446                            | 402                                     |
| 500        | 20.4               | 3000             | 0.035                | 0.046                | 0.014                       | 0.041                      | 0.397 + j0.312          | 0.047 + j0.039              | 3349                                   | 533                            | 451                                     |
| 750        | 22.9               | 4500             | 0.024                | 0.033                | 0.012                       | 0.039                      | 0.369 + j0.262          | 0.034 + j0.037              | 3916                                   | 631                            | 500                                     |
| 1000       | 24.7               | 6000             | 0.018                | 0.026                | 0.011                       | 0.037                      | 0.348 + j0.228          | 0.027 + j0.036              | 4387                                   | 707                            | 539                                     |

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

\* CEC ampacities are based on:

3-1/C in air copper and aluminum: D17M

3-1/C direct buried copper and aluminum: D17A

**Table 3 – Weights and Measurements (Metric)**

| Cond. Size | Strand | Diameter Over Conductor | Diameter Over Insulation | Insul. Thickness | Diameter Over Insulation Shield | Inner Jacket Thickness | Dia. Over Armour | Overall Jacket Thickness | Approx. OD | Approx. Weight |
|------------|--------|-------------------------|--------------------------|------------------|---------------------------------|------------------------|------------------|--------------------------|------------|----------------|
| AWG/Kcmil  | No.    | mm                      | mm                       | mm               | mm                              | mm                     | mm               | mm                       | mm         | kg/km          |
| 2          | 7      | 6.81                    | 13.61                    | 2.92             | 15.14                           | 1.65                   | 24.59            | 1.27                     | 27.13      | 747            |
| 1          | 19     | 7.57                    | 14.38                    | 2.92             | 15.90                           | 1.65                   | 25.35            | 1.27                     | 27.89      | 802            |
| 1/0        | 19     | 8.53                    | 15.34                    | 2.92             | 16.87                           | 1.65                   | 26.31            | 1.27                     | 28.85      | 871            |
| 2/0        | 19     | 9.55                    | 16.36                    | 2.92             | 17.88                           | 2.03                   | 28.09            | 1.27                     | 30.63      | 999            |
| 3/0        | 19     | 10.72                   | 17.53                    | 2.92             | 19.05                           | 2.03                   | 29.26            | 1.27                     | 31.80      | 1095           |
| 4/0        | 19     | 12.04                   | 18.85                    | 2.92             | 20.37                           | 2.03                   | 30.58            | 1.27                     | 33.12      | 1210           |
| 250        | 37     | 13.21                   | 20.22                    | 2.92             | 21.74                           | 2.03                   | 34.75            | 1.27                     | 37.29      | 1342           |
| 350        | 37     | 15.62                   | 22.63                    | 2.92             | 24.16                           | 2.03                   | 37.16            | 1.27                     | 39.70      | 1582           |
| 500        | 37     | 18.67                   | 25.68                    | 2.92             | 27.20                           | 2.03                   | 40.21            | 1.52                     | 43.26      | 1972           |
| 750        | 61     | 23.06                   | 30.33                    | 2.92             | 31.85                           | 2.03                   | 45.47            | 1.52                     | 48.51      | 2586           |
| 1000       | 61     | 26.92                   | 34.19                    | 2.92             | 35.71                           | 2.03                   | 49.33            | 1.52                     | 52.37      | 3250           |

All dimensions are nominal and subject to normal manufacturing tolerances





◇ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Table 4 – Electrical and Engineering Data (Metric)**

| Cond. Size | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 90°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Zero Sequence Impedance | Positive Sequence Impedance | Phase Short Circuit Current @ 6 Cycles | Allowable Ampacity In Air 90°C | Allowable Ampacity Directly Buried 90°C |
|------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|-------------------------|-----------------------------|--|--------------------------------|---|
| AWG/Kcmil  | mm                 | newton           | Ω/km                 | Ω/km                 | MΩ*km                       | Ω/km                       | Ω/1000ft                | Ω/1000ft                    | Amp                                    | Amp                            | Amp                                     |
| 2          | 325.12             | 1771             | 0.8760               | 1.10                 | 0.0098                      | 0.1739                     | 0.690 + j0.516          | 0.337 + j0.053              | 1877                                   | 169                            | 176                                     |
| 1          | 335.28             | 2234             | 0.6923               | 0.87                 | 0.0091                      | 0.1706                     | 0.623 + j0.498          | 0.267 + j0.050              | 1970                                   | 194                            | 198                                     |
| 1/0        | 345.44             | 2817             | 0.5512               | 0.69                 | 0.0082                      | 0.1640                     | 0.571 + j0.478          | 0.212 + j0.048              | 2088                                   | 222                            | 223                                     |
| 2/0        | 368.30             | 3551             | 0.4364               | 0.55                 | 0.0076                      | 0.1575                     | 0.529 + j0.457          | 0.168 + j0.047              | 2212                                   | 255                            | 250                                     |
| 3/0        | 381.00             | 4477             | 0.3445               | 0.44                 | 0.0070                      | 0.1542                     | 0.496 + j0.435          | 0.134 + j0.045              | 2354                                   | 290                            | 278                                     |
| 4/0        | 396.24             | 5647             | 0.2756               | 0.34                 | 0.0064                      | 0.1476                     | 0.469 + j0.411          | 0.106 + j0.043              | 2515                                   | 329                            | 309                                     |
| 250        | 447.04             | 6675             | 0.2329               | 0.30                 | 0.0058                      | 0.1509                     | 0.452 + j0.389          | 0.091 + j0.044              | 2683                                   | 370                            | 347                                     |
| 350        | 477.52             | 9345             | 0.1640               | 0.21                 | 0.0052                      | 0.1411                     | 0.423 + j0.352          | 0.066 + j0.042              | 2977                                   | 446                            | 402                                     |
| 500        | 518.16             | 13350            | 0.1148               | 0.15                 | 0.0043                      | 0.1345                     | 0.397 + j0.312          | 0.047 + j0.039              | 3349                                   | 533                            | 451                                     |
| 750        | 581.66             | 20025            | 0.0787               | 0.11                 | 0.0037                      | 0.1280                     | 0.369 + j0.262          | 0.034 + j0.037              | 3916                                   | 631                            | 500                                     |
| 1000       | 627.38             | 26700            | 0.0591               | 0.09                 | 0.0034                      | 0.1214                     | 0.348 + j0.228          | 0.027 + j0.036              | 4387                                   | 707                            | 539                                     |

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

\* CEC ampacities are based on:

3-1/C in air copper and aluminum: D17M

3-1/C direct buried copper and aluminum: D17A

