



# CU Compressed 5/8kV TRXLPE Insulation 133/100% IL PVC Jacket. MV 105 - Sunlight Resistant - For Direct Burial

Type MV-105 Three Conductor Copper, 115 Mils Tree Retardant Cross Linked Polyethylene (TRXLPE) 133% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Jacket.. Silicone Free



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 115 Mils Tree Retardant Cross Linked Polyethylene (TRXLPE) 133% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
7. **Filler:** Wax paper filler
8. **Binder:** Poly glass tape
9. **Overall Jacket:** Polyvinyl Chloride (PVC)

## APPLICATIONS AND FEATURES:

Southwire's 5KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend when UL listed. Rated at -40°C for cold bend and cold impact and marked with "LTGG" when CSA listed or dual UL/CSA listed. For uses in Class I and II, Division 2 hazardous locations per NEC Article 501 and 502. Rated for 1000 lbs./FT maximum sidewall pressure.

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)





- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

**SAMPLE PRINT LEGEND:**

{SQFTG\_DUAL} SOUTHWIRE® POWER CABLE {UL} 3/C XX AWG CU 115 MILS XLP 5KV 133% INS LEVEL 25%TS GW 1 X XX AWG CU MV-105 SUN. RES. FOR DIRECT BURIAL {NESC}

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Ground	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius
	AWG/Kcmil	No. of Strands	inch	inch	inch	No. x AWG	mil	inch	lb/1000ft	lb/1000ft	lb	inch
673414	2	7	0.282	0.545	0.605	1x6	80	1.538	867	1545	1592	10.7
673413	1	19	0.322	0.590	0.650	1x4	80	1.622	1086	1822	2008	11.3
673412	1/0	19	0.361	0.630	0.690	1x4	110	1.768	1299	2205	2534	12.3
673411	2/0	19	0.405	0.674	0.734	1x4	110	1.863	1565	2542	3194	13.0
673410	3/0	19	0.456	0.724	0.784	1x3	110	1.971	1934	2998	4027	13.7
673409	4/0	19	0.512	0.766	0.826	1x3	110	2.062	2353	3494	5078	14.4
673408	250	37	0.558	0.818	0.878	1x3	110	2.174	2723	3978	6000	15.2
673407	350	37	0.661	0.917	0.977	1x2	110	2.388	3723	5115	8400	16.7
673364	500	37	0.789	1.042	1.102	1x1	110	2.658	5208	6848	12000	18.6
TBA	750	61	0.968	1.254	1.314	1x1/0	135	3.163	7414	9626	18000	22.1

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.204	0.045	0.040	0.499 + j0.404	0.133 + j0.045	1920	135/145	140/154
1	0.128	0.162	0.041	0.039	0.499 + j0.404	0.133 + j0.045	2044	155/165	160/180
1/0	0.102	0.128	0.037	0.037	0.499 + j0.404	0.133 + j0.045	2165	175/190	185/205
2/0	0.081	0.102	0.034	0.036	0.499 + j0.429	0.128 + j0.044	2302	200/220	215/240
3/0	0.064	0.081	0.031	0.035	0.499 + j0.429	0.128 + j0.044	2459	230/250	250/280
4/0	0.051	0.065	0.028	0.034	0.499 + j0.429	0.128 + j0.044	2633	265/280	285/320
250	0.043	0.056	0.027	0.033	0.499 + j0.429	0.128 + j0.044	2800	290/315	320/355
350	0.031	0.041	0.023	0.032	0.499 + j0.429	0.128 + j0.044	3120	355/380	395/440
500	0.022	0.030	0.020	0.030	0.499 + j0.429	0.128 + j0.044	3516	430/460	485/545
750	0.014	0.023	0.017	0.029	0.499 + j0.429	0.128 + j0.044	4102	530/570	615/685

\* NEC ampacities are based on:

\* For Duct: Table 310.60(C)(13) Detail 1.

\* For Free Air: Table 310.60(C)(5).

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.





- \* Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.
- \* Capacitive Reactance is between Phase-to-Shield.

