HVTECK AL 3/C 260NLEPR TS PVC AIA PVC 25kV 100% CSA

3 Conductor, 260 Mils No Lead Ethylene Propylene Rubber (NL-EPR), 100% Insulation Level, Tape Shield, Polyvinyl Chloride (PVC) Inner Jacket, Aluminum Interlocked Armour (AIA), Polyvinyl Chloride (PVC) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
2. **Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
3. **Insulation:** 260 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 100% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Filler:** Interstices filled with non-hydroscoping/non-wicking fillers
7. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8
8. **Binder:** Polypropylene tape
9. **Inner Jacket:** PVC inner jacket
10. **Armour:** Aluminum Interlocked Armour (AIA)
11. **Overall Jacket:** Black Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 25kV HVTECK is a CSA armoured cable for industrial and commercial medium voltage applications. Rated FT4, -40°C, Hazardous Locations (HL). These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated for 1000 lbs /FT maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemical soils and acids and are flame retardant.

SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C68.3 Shielded & Concentric Neutral Power Cable - 5 to 46 kV
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating
- CSA SUN RES - for Sunlight Resistant rating
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

- ICEA T-29-520 Flame Test (210,000 BTU/Hr)
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)

SAMPLE PRINT LEGEND:

(CSA) SOUTHWIRE (NESC) #P# 3/C [#AWG or #kcmil] CPT AL 260 NLEPR AIA 25kV 100% INS LEVEL 25% TS SUN RES 105°C FT4 HL (-40°C) LTGG RoHS YEAR [SEQUENTIAL METER MARKS]

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Ground	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Conduit Size*
	AWG/ Kcmil	No.	inch	inch	mil	inch	No. x AWG	mil	inch	mil	inch	lb/ 1000ft	lb/ 1000ft	inch
TBA	1	19	0.299	0.857	260	0.917	1x6	110	2.537	75	2.687	312	2411	3.5
585951	1/0	10	0.336	0.894	260	0.954	1x6	110	2.674	75	2.824	329	3221	3.5
TBA	2/0	19	0.376	0.934	260	0.994	1x6	110	2.703	75	2.853	331	2761	3.5
TBA	3/0	19	0.423	0.981	260	1.041	1x6	110	2.805	75	2.955	343	2989	4
TBA	4/0	19	0.475	1.033	260	1.093	1x6	110	2.917	75	3.067	356	3255	4
TBA	250	37	0.52	1.086	260	1.146	1x4	110	3.031	85	3.201	416	3624	4
TBA	350	37	0.616	1.182	260	1.242	1x4	125	3.269	85	3.439	440	4187	4.5
TBA	500	37	0.736	1.302	260	1.362	1x3	125	3.528	85	3.698	508	4989	5

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Strand count meets minimum number per ASTM
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1	18.8	1506	0.211	0.289	0.049	0.032	0.660+j0.426	0.289+j0.046	2872	158	177
1/0	19.8	1900	0.167	0.229	0.045	0.03	0.599+j0.411	0.229+j0.045	2987	181	200
2/0	20	2395	0.133	0.182	0.042	0.028	0.551+j0.395	0.182+j0.043	3111	208	228
3/0	20.7	3020	0.105	0.144	0.039	0.027	0.511+j0.377	0.144+j0.041	3256	239	258
4/0	21.5	3808	0.084	0.115	0.037	0.025	0.479+j0.359	0.115+j0.040	3418	273	292
250	22.4	4500	0.07	0.096	0.034	0.024	0.457+j0.342	0.096+j0.039	3582	302	321
350	24.1	6300	0.051	0.07	0.03	0.022	0.425+j0.314	0.070+j0.037	3879	368	385
500	25.9	9000	0.036	0.05	0.027	0.02	0.395+j0.283	0.050+j0.035	4251	454	462

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
***** CEC ampacities are based on:

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

3/C in air copper and aluminum: D17N
3/C direct buried copper and aluminum: D17E

Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Ground	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Conduit Size*
	AWG/ Kcmil	No.	mm	mm	mm	mm	No. x AWG	mm	mm	mm	mm	kg/km	kg/km	inch
TBA	1	19	7.59	21.77	6.60	23.29	1x6	2.79	64.44	1.91	68.25	464	3588	3.5
585951	1/0	10	8.53	22.71	6.60	24.23	1x6	2.79	67.92	1.91	71.73	490	4793	3.5
TBA	2/0	19	9.55	23.72	6.60	25.25	1x6	2.79	68.66	1.91	72.47	493	4109	3.5
TBA	3/0	19	10.74	24.92	6.60	26.44	1x6	2.79	71.25	1.91	75.06	510	4448	4
TBA	4/0	19	12.07	26.24	6.60	27.76	1x6	2.79	74.09	1.91	77.90	530	4844	4
TBA	250	37	13.21	27.58	6.60	29.11	1x4	2.79	76.99	2.16	81.31	619	5393	4
TBA	350	37	15.65	30.02	6.60	31.55	1x4	3.18	83.03	2.16	87.35	655	6231	4.5
TBA	500	37	18.69	33.07	6.60	34.59	1x3	3.18	89.61	2.16	93.93	756	7424	5

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Strand count meets minimum number per ASTM
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Phase Short Circuit Current @ 6 Cycles	Allowable Ampacity In Air 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	mm	newton	Ω/km	Ω/km	MΩ*km	Ω/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1	477.52	6702	0.6923	0.95	0.0149	0.1050	0.660+j0.426	0.289+j0.046	2872	158	177
1/0	502.92	8455	0.5479	0.75	0.0137	0.0984	0.599+j0.411	0.229+j0.045	2987	181	200
2/0	508.00	10658	0.4364	0.60	0.0128	0.0919	0.551+j0.395	0.182+j0.043	3111	208	228
3/0	525.78	13439	0.3445	0.47	0.0119	0.0886	0.511+j0.377	0.144+j0.041	3256	239	258
4/0	546.10	16946	0.2756	0.38	0.0113	0.0820	0.479+j0.359	0.115+j0.040	3418	273	292
250	568.96	20025	0.2297	0.31	0.0104	0.0787	0.457+j0.342	0.096+j0.039	3582	302	321
350	612.14	28035	0.1673	0.23	0.0091	0.0722	0.425+j0.314	0.070+j0.037	3879	368	385
500	657.86	40050	0.1181	0.16	0.0082	0.0656	0.395+j0.283	0.050+j0.035	4251	454	462

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
***** CEC ampacities are based on:
3/C in air copper and aluminum: D17N
3/C direct buried copper and aluminum: D17E

Copyright © 2026 Southwire Company, LLC. All Rights Reserved