CU 600V EPR Insulation Thermoset LSZH-TS Jacket RHH/RHW-2. CT Rated - Sunlight Resistant - For Direct Burial - Silicone Free

Power Cable 600Volt Single Conductor Copper, Ethylene Propylene Rubber (EPR) insulation RHH/RHW-2 USE-2 Thermoset SOLONON® Low Smoke Zero Halogen (LSZH-TS) Jacket. CT Rated 1/0 and Larger - Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare or tinned copper per ASTM B3, ASTM B8 and ASTM B33
2. **Binder Tape:** Mylar Tape
3. **Insulation:** Ethylene Propylene Rubber (EPR) Type RHH/RHW-2 USE-2
4. **Overall Jacket:** Thermoset SOLONON® Low Smoke Zero Halogen (LSZH-TS) Silicone-Free Jacket

APPLICATIONS AND FEATURES:

Southwire's 600 Volt power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. CT Rated 1/0 and Larger - Silicone Free

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- CT USE Sizes 1/0 AWG and Larger

SAMPLE PRINT LEGEND:

SOUTHWIRE {UL} XXX AWG CU TYPE RHH OR RHW-2 OR USE-2 XX MILS EPR XX MILS SOLONON® ST1 FOR CT USE SUN RES 600 VOLTS {YYYY} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Min. Avg. Insul. Thickness	Dia. Over Insulation	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Jacket Color
	AWG/ Kcmil	No. of Strands	inch	mil	inch	mil	inch	lb/1000ft	lb/1000ft	
890660	8	7	0.142	15	0.172	15	0.271	51	75	BK
890659	6	7	0.178	30	0.238	30	0.342	81	120	BK
551088	2	7	0.283	45	0.373	30	0.447	205	260	BK
TBA	1	19	0.322	55	0.432	45	0.432	258	295	BK
561561	1/0	19	0.362	45	0.452	45	0.575	326	419	BK
561560	2/0	19	0.405	55	0.515	45	0.617	411	512	BK
581799	3/0	19	0.456	45	0.546	45	0.669	518	629	BK
561556	4/0	19	0.512	45	0.602	45	0.711	653	771	BK
561554	250	37	0.558	65	0.688	65	0.817	772	945	BK
561553	350	37	0.661	65	0.791	65	0.916	1081	1281	BK
890658	500	37	0.789	65	0.919	65	1.041	1544	1775	BK
566011	600	61	0.866	65	0.996	65	1.167	1853	2133	BK
551091	750	61	0.968	65	1.098	65	1.275	2316	2633	BK
TBA	1000	61	1.117	80	1.277	65	1.277	3088	3258	BK

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.
* Tinned Copper

Table 2 – Electrical and Engineering Data

Stock Number	Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity At 75°C	Allowable Ampacity At 90°C
	AWG/ Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
890660	8	1.1	132	0.653	0.81	0.052	50	55
890659	6	1.4	209	0.411	0.51	0.051	65	75
551088	2	1.8	530	0.162	0.201	0.045	115	130
TBA	1	1.7	669	0.128	0.159	0.046	130	145
561561	1/0	2.3	844	0.102	0.127	0.044	150	170
561560	2/0	2.5	1064	0.082	0.102	0.043	175	195
581799	3/0	2.7	1342	0.064	0.079	0.042	200	225
561556	4/0	2.8	1692	0.051	0.063	0.041	230	260
561554	250	3.3	2000	0.043	0.053	0.041	255	290
561553	350	3.7	2800	0.031	0.039	0.04	310	350
890658	500	5.2	4000	0.021	0.027	0.039	380	430
566011	600	5.8	4800	0.018	0.024	0.039	420	475
551091	750	6.4	6000	0.014	0.019	0.038	475	535
TBA	1000	6.4	8000	0.011	0.016	0.037	545	615

***** Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.
***** Inductive Reactance is based on non-ferrous conduit with one diameter spacing center-to-center.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved