600V SEOPRENE® SEOOW Power Cord Non-UL/CSA with Black Jacket 105°C. Silicone-Free. MSHA Approved

600 Volt, 105°C Flexible Cord. Premium Oil Resistance, Sunlight, Water Resistance and Flame Retardant. Non UL / Non CSA Listed.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K stranded bare copper per ASTM B-174
2. **Insulation:** Heat, moisture and oil resistant TPE
3. **Filler:** Non-wicking polypropylene fillers, with a tissue-paper separator wrapped around the assembly
4. **Jacket:** Black TPE (other colors available upon request)

APPLICATIONS AND FEATURES:

Southwire Type SEOOW Flexible Cords are permitted for indoor and outdoor temporary power uses, portable industrial machinery and compressors. Type SEOOW Cords are suitable for use in temperatures between -50°C to maximum 105°C wet or dry.

SPECIFICATIONS:

- MSHA Approved
- RoHS-3 Complies with European Directive 2015/863

SAMPLE PRINT LEGEND:

SOUTHWIRE{R} SEOPRENE{R} CORD X/C X AWG (X.XX{mm2}) SEOOW 600V -50{D}C TO 105{D}C WATER RESISTAN

PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 1 – Weights and Measurements

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Insul. Color	Jacket Color
		AWG/ Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp		
550449	22320	8	3	96	45	90	0.701	324	35	BK,WE,GN	BK
550450	22420	8	4	96	45	100	0.783	417	28	BK,WE,RD,GN	BK
551140	22470	8	5	96	45	125	0.851	497	28	BK,WE,RD,GN,OE	BK
550556	22321	6	3	96	45	125	0.818	441	45	BK,WE,GN	BK
550405	22421	6	4	96	45	100	0.892	555	36	BK,WE,RD,GN	BK
598330	22521	6	5	96	45	140	0.992	681	36	BK,WE,RD,GN,OE	BK
598331	22322	4	3	96	45	110	0.913	608	60	BK,WE,GN	BK
550404	22422	4	4	96	45	125	1.027	801	48	BK,WE,RD,GN	BK
553942	22323	2	3	119	45	155	1.158	1030	80	BK,WE,GN	BK
550473	22423	2	4	119	45	125	1.260	1302	64	BK,WE,RD,GN	BK

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Weights and Measurements (Metric)

Stock Number	CCI Part #	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity *	Insul. Color	Jacket Color
		AWG/ Kcmil	No.	No.	mm	mm	mm	kg/km	Amp		
550449	22320	8	3	96	1.14	2.29	17.81	482	35	BK,WE,GN	BK
550450	22420	8	4	96	1.14	2.54	19.89	621	28	BK,WE,RD,GN	BK
551140	22470	8	5	96	1.14	3.18	21.62	740	28	BK,WE,RD,GN,OE	BK
550556	22321	6	3	96	1.14	3.18	20.78	656	45	BK,WE,GN	BK
550405	22421	6	4	96	1.14	2.54	22.66	826	36	BK,WE,RD,GN	BK
598330	22521	6	5	96	1.14	3.56	25.20	1013	36	BK,WE,RD,GN,OE	BK
598331	22322	4	3	96	1.14	2.79	23.19	905	60	BK,WE,GN	BK
550404	22422	4	4	96	1.14	3.18	26.09	1192	48	BK,WE,RD,GN	BK
553942	22323	2	3	119	1.14	3.94	29.41	1533	80	BK,WE,GN	BK
550473	22423	2	4	119	1.14	3.18	32.00	1938	64	BK,WE,RD,GN	BK

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved