



3/C CU 25KV Type SHD-GC RHINOSHIELD™ CPE Mining Cable 90°C. MSHA Approved

Flexible Copper conductors, EPR 100% Insulation Level, Cu/Nylon Braid Shield, Extra Heavy Duty Two Layer Chlorinated Polyethylene (CPE) Jacket with Optional Reflective Stripes



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Tin coated, soft drawn, annealed, flexible, rope-lay stranded copper per ASTM B33 and B172
2. **Separator Tape:** Semi-conducting tape applied between the conductor and insulation to facilitate stripping
3. **Conductor Shield:** Semi-conducting cross-linked copolymer
4. **Insulation:** Ethylene Propylene Rubber (EPR)
5. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
6. **Braid Shield:** Tin coated, soft drawn, annealed, copper braid shield (60% minimum coverage), combined with color coded nylon (Black, Blue, Red) with a 40% maximum coverage
7. **Ground Conductor:** Two uninsulated, tin coated, soft drawn, annealed, rope stranded, flexible lay copper per ASTM B33 and B172
8. **Ground Check Conductor:** Tin coated, soft drawn, annealed, rope stranded, flexible lay copper per ASTM B33 and B172 with high strength yellow, polypropylene insulation
9. **Filler:** Rubber fillers as needed
10. **Reinforcement:** Reinforcing twine applied over core
11. **Inner Jacket:** Black, mold cured, extra heavy-duty integral fill, flame resistant, thermosetting Chlorinated Polyethylene (CPE)
12. **Outer Jacket:** Black, mold cured, extra heavy-duty, flame resistant, thermosetting Chlorinated Polyethylene (CPE). Alternate jacket colors available
13. **Reflective Stripe:** Highly visible reflective stripe embedded into the outer jacket to increase safety and help prevent cable runover (optional, contact your sales representative for part number)

APPLICATIONS AND FEATURES:

RHINOSHIELD™ Type SHD-GC is a heavy-duty trailing cable where flexibility and maximum protection is required. For use with mobile, reeling, or stationary mining equipment, continuous mining machines, longwall mining systems, and blast hole drillers. It is also an excellent choice for shovels, draglines, dredges, cranes and marine shore-to-ship power supplies, and anytime extra-durable, flexible cable is required. Suitable for continuous submersion in water. Ground check conductor provides fail-safe ground monitoring. Embossed print legend for easy cable identification. Cold Bend and Impact Tested to -50°C. For vertical drop requirements consult with factory application specialist.

SPECIFICATIONS:





- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- ICEA S-75-381 Portable and Power Feeder Cables for Use in Mines
- MSHA Approved

SAMPLE PRINT LEGEND:

SOUTHWIRE (R) RHINO™ BRAND CABLE # AWG CU 3/C EPR TYPE SHD-GC 25000V -50°C 90°C P-07-KA140005 MSHA

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Conductor	Insul. Thickness	Diameter Over Insulation	Ground	Ground Check Size	Inner Jacket Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Jacket Color
	AWG/ Kcmil	No.	No.	inch	mil	inch	No. x AWG	AWG	mil	mil	inch	lb/1000ft	
590578	1/0	3	273	0.379	295	1.018	2 x 4	8	105	160	3.050	4558	RD
674824	1/0	3	273	0.379	295	1.018	2 x 4	8	105	160	3.050	4558	GN
590591	2/0	3	324	0.400	295	1.058	2 x 3	8	170	175	3.271	6060	RD
589222	3/0	3	418	0.480	295	1.148	2 x 2	8	130	165	3.330	6330	OE
599032	4/0	3	532	0.550	260	1.145	2 x 1	2	130	310	3.500	7373	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance	Working Tension	Min Bending Radius	Allowable Ampacity In Air 90°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	Ω/1000ft	lb	inch	Amp
1/0	0.109	0.137	0.044	722	24.4	218
1/0	0.109	0.137	0.044	722	24.4	218
2/0	0.087	0.109	0.044	910	26.1	249
3/0	0.069	0.087	0.042	1147	26.6	286
4/0	0.057	0.073	0.039	1447	28.0	327

* Ampacities based upon ICEA S-75-381 Table H-1.

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

