



Multi-Conductor Tinned CU Unshielded Signal Cable 1000V

Multi-Conductor Unshielded Signal cables 1000 Volt Single Conductor Tinned Copper, Ethylene Propylene Rubber (EPR) insulation Thermoset SOLONON® Low Smoke Zero Halogen (LSZH-TS) Jacket.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Stranded tinned copper per ASTM B33 and ASTM B8
2. **Insulation:** Ethylene Propylene Rubber (EPR)
3. **Separator:** Silicone polymer
4. **Overall Jacket:** Black, Thermoset, SOLONON® Low Smoke Zero Halogen (LSZH-TS)

APPLICATIONS AND FEATURES:

Southwire's Railroad Signal cables 1000 Volt conform to requirements in AREMA Signal Manual Part 10.3.16 and are suited for use in air or non-plenum ducts.

SPECIFICATIONS:

- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-73-532 Standard for Control, Thermocouple Extension and Instrumentation Cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy

SAMPLE PRINT LEGEND:

SOUTHWIRE XX AWG X/C EPR CDRS 90C SOLONON® JKT 1000V SUN. RES. {SEQUENTIAL FOOTAGE MARKS} SEQ FEET




Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Strand Class	Strand Count	Cond. Cmil	Cond. Number	Diameter Over Conductor	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Max Pull Tension
	AWG/kcmil		No. of Strands	cmil	No.	inch	mil	mil	inch	lb/1000ft	Ω/1000ft	Ω/1000ft	lb
457588	14	C	19	4110	3	0.074	80	80	0.708	222	2.631	3.170	98
457590	14	C	19	4110	5	0.074	80	80	0.837	317	2.631	3.170	164
457572	14	C	19	4110	7	0.074	80	95	0.942	433	2.631	3.170	230
457592	12	C	19	6530	3	0.090	80	80	0.742	258	1.662	2.002	156
457594	9	C	19	13090	3	0.127	80	80	0.821	350	0.825	0.994	314
457596	9	C	19	13090	4	0.127	80	95	0.928	466	0.825	0.994	418
457598	9	C	19	13090	8	0.127	80	95	1.193	808	0.825	0.994	837
TBA	6	C	19	26240	2	0.179	95	95	0.926	442	0.411	0.495	629
457600	6	C	19	26240	3	0.179	95	95	1.035	593	0.411	0.495	629
TBA	6	C	19	26240	7	0.179	95	95	1.294	1094	0.411	0.495	1469

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

