25kV AL 133% TRXLPE Full Neutral LLDPE

Single Conductor, 320 Mils Tree Retardant Cross Linked Polyethylene, 133% Insulation Level, Full Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Moisture blocked class B compressed Aluminum ASTM B231 1350 ¾ hard H16/H26 (Non Moisture Blocked Optional)
2. **Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; Supersmooth conductor shield optional; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
3. **Insulation:** 320 Mils Tree Retardant Cross Linked Polyethylene 133% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Neutral:** Helically applied soft drawn bare copper full concentric neutral
6. **Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 25kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation. 130°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ASTM B609 Standard Specification for Aluminum 1350 Round Wire, Annealed and Intermediate Tempers, for Electrical Purposes
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40ºC and MV 90ºC optional marking available upon request

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] AL 25000 VOLTS TRXLPE INSULATION 320 MILS -- (NESC) -- SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET

We've got it MADE IN AMERICA

Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 1 – Weights and Measurements

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
1 (SOLID)	0.289	0.967	320	1.067	13x14	0.249	50	1.295	829	9.1	502
1 (19)	0.322	1	320	1.12	13x14	0.249	50	1.348	876	9.4	502
1/0 (SOLID)	0.325	1.003	320	1.123	16x14	0.203	50	1.351	938	9.5	633
1/0 (19)	0.352	1.03	320	1.15	16x14	0.203	50	1.378	960	9.6	633
2/0 (19)	0.395	1.073	320	1.193	20x14	0.162	50	1.421	1073	9.9	798
3/0 (19)	0.443	1.121	320	1.241	25x14	0.13	50	1.469	1210	10.3	1006
4/0 (19)	0.498	1.176	320	1.296	20x12	0.102	50	1.558	1374	10.9	1269
250 (37)	0.558	1.244	320	1.364	24x12	0.085	75	1.676	1623	11.7	1500
350 (37)	0.661	1.347	320	1.467	21x10	0.061	75	1.821	2006	12.7	2100

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Pulling tension based on pulling eye directly connected to conductor
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (SOLID)	0.129	0.177	0.074	0.056	0.2	2.8	0.394+j0.110	0.179+j0.059	4538	140	170
1 (19)	0.211	0.289	0.07	0.055	0.21	3	0.506+j0.111	0.291+j0.060	4538	140	170
1/0 (SOLID)	0.102	0.14	0.069	0.054	0.21	3	0.324+j0.085	0.143+j0.058	5585	155	195
1/0 (19)	0.167	0.229	0.066	0.053	0.22	3.2	0.413+j0.086	0.232+j0.058	5585	155	195
2/0 (19)	0.133	0.182	0.062	0.051	0.23	3.4	0.334+j0.066	0.185+j0.056	6982	180	220
3/0 (19)	0.105	0.144	0.058	0.049	0.25	3.6	0.268+j0.053	0.148+j0.054	8727	205	250
4/0 (19)	0.084	0.115	0.053	0.048	0.27	3.9	0.214+j0.043	0.120+j0.052	11082	235	285
250 (37)	0.07	0.096	0.049	0.047	0.29	4.2	0.179+j0.038	0.102+j0.050	13298	254	307
350 (37)	0.051	0.07	0.044	0.045	0.33	4.8	0.130+j0.031	0.079+j0.047	18496	305	365

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3
*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.
*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.

Table 3 – Weights and Measurements (Metric)

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
1 (SOLID)	7.34	24.56	8.13	27.10	13x14	0.82	1.27	32.89	1234	231.14	2234
1 (19)	8.18	25.40	8.13	28.45	13x14	0.82	1.27	34.24	1304	238.76	2234
1/0 (SOLID)	8.25	25.48	8.13	28.52	16x14	0.67	1.27	34.32	1396	241.30	2817
1/0 (19)	8.94	26.16	8.13	29.21	16x14	0.67	1.27	35.00	1429	243.84	2817
2/0 (19)	10.03	27.25	8.13	30.30	20x14	0.53	1.27	36.09	1597	251.46	3551
3/0 (19)	11.25	28.47	8.13	31.52	25x14	0.43	1.27	37.31	1801	261.62	4477
4/0 (19)	12.65	29.87	8.13	32.92	20x12	0.33	1.27	39.57	2045	276.86	5647
250 (37)	14.17	31.60	8.13	34.65	24x12	0.28	1.91	42.57	2415	297.18	6675
350 (37)	16.79	34.21	8.13	37.26	21x10	0.20	1.91	46.25	2985	322.58	9345

We've got it MADE IN AMERICA

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Pulling tension based on pulling eye directly connected to conductor
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (SOLID)	0.4232	0.58	0.0226	0.1837	0.656	9.1864	0.394+j0.110	0.179+j0.059	4538	140	170
1 (19)	0.6923	0.95	0.0213	0.1804	0.689	9.8425	0.506+j0.111	0.291+j0.060	4538	140	170
1/0 (SOLID)	0.3346	0.46	0.0210	0.1772	0.689	9.8425	0.324+j0.085	0.143+j0.058	5585	155	195
1/0 (19)	0.5479	0.75	0.0201	0.1739	0.722	10.4987	0.413+j0.086	0.232+j0.058	5585	155	195
2/0 (19)	0.4364	0.60	0.0189	0.1673	0.755	11.1549	0.334+j0.066	0.185+j0.056	6982	180	220
3/0 (19)	0.3445	0.47	0.0177	0.1608	0.820	11.8110	0.268+j0.053	0.148+j0.054	8727	205	250
4/0 (19)	0.2756	0.38	0.0162	0.1575	0.886	12.7953	0.214+j0.043	0.120+j0.052	11082	235	285
250 (37)	0.2297	0.31	0.0149	0.1542	0.951	13.7795	0.179+j0.038	0.102+j0.050	13298	254	307
350 (37)	0.1673	0.23	0.0134	0.1476	1.083	15.7480	0.130+j0.031	0.079+j0.047	18496	305	365

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3
*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.
*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.

Concentric Neutral Calculator

We've got it MADE IN AMERICA

Copyright © 2026 Southwire Company, LLC. All Rights Reserved