



35kV CU 100% EPR (EAM) LCT LLDPE

Single Conductor, 345 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM), 100% Insulation Level, Longitudinally Corrugated Tape Shield, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Moisture blocked class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8 (Conductor moisture block optional and tinned copper per ASTM B33 optional)
2. **Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
3. **Insulation:** 345 Mils Ethylene Propylene Rubber (EPR) / Ethylene Alkene Copolymer (EAM) 100% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Tape Shield:** 10 mils Longitudinally Corrugated Tape Shield
6. **Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 35kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation. 140°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 35000 VOLTS EPR INSULATION 345 MILS -- (NESC) --
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET





Table 1 – Weights and Measurements

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	inch	inch	mil	inch	mil	inch	lb /1000ft	inch	lb
1/0 (Solid)	0.324	1.052	345	1.132	80	1.392	1098	16.7	844
1/0 (19)	0.361	1.089	345	1.169	80	1.429	1131	17.1	844
2/0 (19)	0.405	1.133	345	1.213	80	1.473	1256	17.7	1064
3/0 (19)	0.456	1.184	345	1.264	80	1.524	1409	18.3	1342
4/0 (19)	0.512	1.240	345	1.320	80	1.580	1593	19.0	1692
250 (37)	0.558	1.294	345	1.374	80	1.634	1764	19.6	2000
350 (37)	0.661	1.397	345	1.477	110	1.797	2272	21.6	2800
500 (37)	0.789	1.525	345	1.605	110	1.925	2857	23.1	4000
750 (61)	0.968	1.714	345	1.794	110	2.114	3818	25.4	6000
1000 (61)	1.117	1.863	345	1.943	110	2.263	4733	27.2	8000

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor





Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0 (Solid)	0.102	0.128	0.055	0.055	0.363	63.1	0.403 + j0.162	0.129 + j0.056	4405	210	250
1/0 (19)	0.102	0.128	0.052	0.053	0.386	67.1	0.397 + j0.155	0.129 + j0.054	4531	210	250
2/0 (19)	0.081	0.102	0.048	0.051	0.412	71.6	0.364 + j0.146	0.103 + j0.052	4679	235	280
3/0 (19)	0.064	0.081	0.045	0.049	0.443	77.0	0.336 + j0.137	0.082 + j0.050	4852	265	320
4/0 (19)	0.051	0.065	0.042	0.048	0.476	82.7	0.312 + j0.129	0.066 + j0.048	5042	300	360
250 (37)	0.043	0.056	0.039	0.046	0.508	88.3	0.296 + j0.121	0.057 + j0.047	5225		
350 (37)	0.031	0.041	0.035	0.045	0.568	98.7	0.269 + j0.109	0.043 + j0.045	5573	400	470
500 (37)	0.022	0.030	0.031	0.042	0.643	111.7	0.244 + j0.096	0.032 + j0.043	6007	485	560
750 (61)	0.014	0.023	0.026	0.040	0.751	130.5	0.218 + j0.081	0.025 + j0.040	6646	595	670
1000 (61)	0.011	0.019	0.024	0.038	0.837	145.5	0.202 + j0.072	0.021 + j0.038	7151	675	745

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.





Table 3 – Weights and Measurements (Metric)

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	mm	mm	mm	mm	mm	mm	kg/km	mm	newton
1/0 (Solid)	8.23	26.72	8.76	28.75	2.03	35.36	1634	424.18	3756
1/0 (19)	9.17	27.66	8.76	29.69	2.03	36.30	1683	434.34	3756
2/0 (19)	10.29	28.78	8.76	30.81	2.03	37.41	1869	449.58	4735
3/0 (19)	11.58	30.07	8.76	32.11	2.03	38.71	2097	464.82	5972
4/0 (19)	13.00	31.50	8.76	33.53	2.03	40.13	2371	482.60	7529
250 (37)	14.17	32.87	8.76	34.90	2.03	41.50	2625	497.84	8900
350 (37)	16.79	35.48	8.76	37.52	2.79	45.64	3381	548.64	12460
500 (37)	20.04	38.73	8.76	40.77	2.79	48.89	4252	586.74	17800
750 (61)	24.59	43.54	8.76	45.57	2.79	53.70	5682	645.16	26700
1000 (61)	28.37	47.32	8.76	49.35	2.79	57.48	7043	690.88	35600

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor





Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0 (Solid)	0.3346	0.42	0.0168	0.1804	1.191	207.0210	0.403 + j0.162	0.129 + j0.056	4405	210	250
1/0 (19)	0.3346	0.42	0.0158	0.1739	1.266	220.1444	0.397 + j0.155	0.129 + j0.054	4531	210	250
2/0 (19)	0.2657	0.33	0.0146	0.1673	1.352	234.9081	0.364 + j0.146	0.103 + j0.052	4679	235	280
3/0 (19)	0.2100	0.27	0.0137	0.1608	1.453	252.6247	0.336 + j0.137	0.082 + j0.050	4852	265	320
4/0 (19)	0.1673	0.21	0.0128	0.1575	1.562	271.3255	0.312 + j0.129	0.066 + j0.048	5042	300	360
250 (37)	0.1411	0.18	0.0119	0.1509	1.667	289.6982	0.296 + j0.121	0.057 + j0.047	5225		
350 (37)	0.1017	0.13	0.0107	0.1476	1.864	323.8189	0.269 + j0.109	0.043 + j0.045	5573	400	470
500 (37)	0.0722	0.10	0.0094	0.1378	2.110	366.4698	0.244 + j0.096	0.032 + j0.043	6007	485	560
750 (61)	0.0459	0.08	0.0079	0.1312	2.464	428.1496	0.218 + j0.081	0.025 + j0.040	6646	595	670
1000 (61)	0.0361	0.06	0.0073	0.1247	2.746	477.3622	0.202 + j0.072	0.021 + j0.038	7151	675	745

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.

