MC-PCS HCF Duo™ Power & Control/Signal Cable 277/480V Colors

Copper THHN/THWN Insulated Singles. Green Insulated Copper Grounding Conductor. UL Listed 600 Volts. Rated VW-1. Lightweight Interlocked Armor. Signal: 16 AWG Copper TFN insulated singles.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- 1. Conductor: Solid copper per ASTM B3 and ASTM B8
- 2. Insulation: All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
- 3. **Ground:** Green insulated ground. Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
- 4. Signal: 16 AWG Copper TFN Insulated Singles Pink, Purple. Overall light blue jacket over the signal cables
- 5. **Binder**: Mylar tape
- 6. **Ground:** Full-sized bare 8000 series aluminum grounding/bonding conductor. Armor and bare aluminum conductor form the equipment ground path.
- 7. **Armor**: Lightweight Interlocked Armor

APPLICATIONS AND FEATURES:

Southwire MC-PCS HCF Duo™ Type MC All Purpose Hospital Care Facility Cable is suitable for use as follows:

- Branch-circuit wiring for patient care areas of hospitals, medical centers, and other health care facilities (when installed in accordance with NEC® Articles 517 and 330, and mechanically protected per Article 300.4). Such areas include nursing homes, dental offices, clinics, and outpatient facilities. Use in hazardous anesthetizing areas is prohibited.
- Applications requiring redundant, dedicated or isolated grounding paths.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22 (C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Power, lighting, control, and signal circuits.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(D)(2)
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Use with UL Listed MCI-A fittings.
- Binder tape with print legend wrapped around assembly.
- Type THHN/THWN rated 90°C Dry.

Southwire MC-PCS HCF Duo™ Type MC Cable - meets or exceeds the following requirements:

- UL Online Product Guide Info Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A59544 (formerly J-C-30B)





- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

SAMPLE PRINT LEGEND:

ALUMINUM CLAD CABLE WITH COPPER CDRS TYPE THHN OR THWN MAX VOLTAGE 600V, FOR USE IN CABLE TRAY90(D)C - WET OR DRY LOCATIONS GASOLINE & OIL RESISTANT CDRS LISTED FOR FIREWALL PENTRATION (GREEN INSULATED GROUND)

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Diameter Over Armor	Copper Weight	Overall Weight			
	AWG/ Kcmil			inch		mils	No. x AWG	inch	lbs/1000ft	lbs/1000ft			
	12 AWG Solid												
598129◊	12	2	BN,GY	0.080	Solid	20	1x12	0.637	75	165			
597661◊	12	2	OE,GY	0.080	Solid	20	1x12	0.632	75	164			
597663◊	12	2	YW,GY	0.080	Solid	20	1x12	0.632	75	164			
12 AWG 19 Strands													
597675◊	12	2	BN,GY	0.080	19	20	1x12	0.651	76	170			
12 AWG Solid													
597667◊	12	3	BN,0E,GY	0.080	Solid	20	1x12	0.674	95	193			
12 AWG 19 Strands													
597679◊	12	3	BN,OE,GY	0.080	19	20	1x12	0.697	96	198			
641094	12	2	OE,GY,GN,LBE	0.088	19	20	1x10	0.646	76	169			
641096	12	2	YW,GY,GN,LBE	0.088	19	20	1x10	0.646	76	169			
10 AWG Solid													
597671◊	10	2	BN,GY	0.101	Solid	25	1x10	0.697	108	215			

All dimensions are nominal and subject to normal manufacturing tolerances

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.





[♦] Cable marked with this symbol is a standard stock item

Note: Conductor number = number of phase conductors plus neutral. Does not include green ground.

Table 2 – Electrical and Engineering Data

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C						
AWG/ Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp						
	12 AWG Solid												
12	2	4.5	1.662	2.002	0.054	25	30						
12	2	4.4	1.662	2.002	0.054	25	30						
12	2	4.4	1.662	2.002	0.054	25	30						
	12 AWG 19 Strands												
12	2	4.6	1.662	2.002	0.054	25	30						
12 AWG Solid													
12	3	4.7	1.662	2.002	0.054	25	30						
12 AWG 19 Strands													
12	3	4.9	1.662	2.002	0.054	25	30						
12	2	4.5	1.662	2.002	0.054	25	30						
12	2	4.5	1.662	2.002	0.054	25	30						
10 AWG Solid													
10	2	4.9	1.040	1.253	0.050	35	40						

^{*} Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

