



NS75 CSA Quadruplex LLDPE/PVC Service Drop. ACSR Neutral - Messenger

Aluminum Conductors With Linear Low Density Polyethylene And Polyvinyl Chloride Insulation.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Conductors are stranded, compact 1350-H19 aluminum
- Messenger:** ACSR Neutral
- Insulation:** Linear Low Density Polyethylene (LLDPE) and Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Used to supply power, usually from a pole-mounted transformer, to the user's service head where connection to the service entrance cable is made. To be used at voltages of 600 volts phase-to-phase or less and at conductor temperatures 75°C for Linear Low Density Polyethylene (LLDPE) and Polyvinyl Chloride (PVC) insulated conductors.

SPECIFICATIONS:

- ASTM B230 Aluminum, 1350-H19 Wire for Electrical Purposes
- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ASTM B400 Standard Specification for Compact Round Concentric-Lay-Stranded, Aluminum 1350 Conductors
- ASTM B901 Standard Specification for Compressed Round Stranded Aluminum Conductors Using Single Input Wire Construction. *(The number of strands for both phase and neutral may differ)*
- CSA 22.2 No. 129 Neutral Supported Cable

Table 1 – Weights and Measurements

Stock Number	Phase Cond. Size	Phase Strand	Dia. Over Phase Conductor	Phase Insul. Thickness	Dia. Over Phase Insulation	Neutral Cond. Size	Approx. OD	Approx. Weight
	AWG/Kcmil	No.	inch	mil	inch	AWG/Kcmil	inch	lb/1000ft
662272	6	7	0.169	75	0.319	6	0.77	196
663160	2	7	0.268	75	0.418	2	1.009	401
663122	2/0	7	0.376	105	0.586	2/0	1.415	801
663204	3/0	7	0.423	105	0.633	3/0	1.528	972
663148	4/0	7	0.475	105	0.685	4/0	1.654	1185

All dimensions are nominal and subject to normal manufacturing tolerances

1. The actual number of strands may differ for single input wire per ASTM B901





Table 2 – Electrical and Engineering Data

Phase Cond. Size AWG/Kcmil	DC Resistance @ 25°C Ω/1000ft	AC Resistance @ 75°C Ω/1000ft	Inductive Reactance @ 60Hz Ω/1000ft	GMR ft
6	0.6742	0.9237	0.0365	0.0054
2	0.2666	0.3652	0.0336	0.0086
2/0	0.1303	0.1821	0.0331	0.0121
3/0	0.1054	0.1444	0.032	0.0139
4/0	0.0837	0.1146	0.0314	0.0157

Notes:

1. DC resistances include a 1% length factor for plexing.
2. Inductive reactance assumes the neutral is carrying current.
3. Phase conductors assumed to be reverse lay stranded, compressed construction.
4. Phase spacing assumes cables are touching.
5. Resistances shown are for the phase conductor only.
6. Ampacity based on conductor temperature of 75°; ambient temperature of 40°C; emissivity 0.9; 2 ft./sec. wind in sun.

Neutral Code Word

Size	Code Word	OD (inches)
#6	Bass	0.182
#2	Carp	0.290
2/0	Hake	0.410
3/0	Cusk	0.461
4/0	Scup	0.517

