Armorlite® Type MC THHN/THWN PVC Jacketed Aluminum Conductor Feeder Cable 120/208V Colors. Silicone Free

Aluminum THHN/THWN Insulated Singles with 8000 series Triple E™ Aluminum Alloy. Bare AlumaFlex™ Aluminum Alloy Grounding Conductor. UL Listed. 600 Volts. Rated VW-1. Lightweight Aluminum Interlocked Armor. Overall PVC Jacket. Sunlight Resistant.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B801
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Ground:** Bare aluminum ground
4. **Filler:** Fillers as needed
5. **Binder:** Mylar tape
6. **Armor:** Aluminum Interlocked Armor
7. **Jacket:** Polyvinyl Chloride (PVC) sunlight resistant, and corrosion resistant

APPLICATIONS AND FEATURES:

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Southwire Armorlite® Type MC Feeder cable is suitable for use as follows:

- Feeder and service power distribution in commercial, industrial, institutional, and multi-residential buildings.
- Where exposed to cinder fills, strong chlorides, caustic alkalis, or vapors of chlorine or of hydrochloric acids.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Suitable for Wet Location per NEC 330.10(A)(11)
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways, or as aerial cable on a messenger.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(D)(2)
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.
- Type THHN/THWN rated 90ºC Dry/ 75ºC Wet

Southwire Armorlite® Type MC Feeder Cable - meets or exceeds the following requirements:

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

Color Code - 3/C: Black, Red, White
- 4/C: Black, Red, Blue, White

SPECIFICATIONS:

- ASTM B800 8000 Series Aluminum Alloy Wire
- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify “Made in the USA Only!” when ordering to ensure your project receives American made products.

SAMPLE PRINT LEGEND:

SOUTHWIRE {UL} E96627 X/C XXX KCMIL COMPACT 8000 AL. --- TRIPLE E ALLOY AA8176 THHN OR THWN CDRS 600 VOLTS GW 1 X X AWG TYPE MC EZ-JKT FOR CT USE SUN. RES. 90 DEGREES C

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

UPDATED: Dec. 31, 2024, 11:08 p.m.UTC REVISION: 1.000.007

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Ground Size	Diameter Over Armor	Jacket Thickness	Approx. OD	Overall Weight
	AWG/ Kcmil			inch		mils	No. x AWG	inch	mil	inch	lbs/ 1000ft
678282	1/0	2	BK,RD	0.336	10	50	1x2	1.118	50	1.224	595
679278	3/0	2	BK,RD	0.423	16	50	1x1/0	1.358	50	1.464	847
593086	4/0	2	BK,WE	0.475	19	50	1x1/0	1.396	50	1.502	929
675674	300	2	BK,RD	0.57	21	60	1x4/0	1.716	60	1.842	1448
679281	350	2	BK,RD	0.616	35	60	1x250	1.808	60	1.934	1618
552587	1/0	3	BK,RD,WE	0.336	10	50	1x4	1.257	50	1.363	768
552465	2/0	3	BK,RD,WE	0.376	12	50	1x4	1.343	50	1.449	882
552464	3/0	3	BK,RD,WE	0.423	16	50	1x4	1.465	50	1.571	1079
552484	4/0	3	BK,RD,WE	0.475	19	50	1x2	1.577	60	1.703	1311
555667	250	3	BK,RD,WE	0.52	22	60	1x2	1.735	60	1.861	1481
563804	250	3	BK,RD,WE	0.52	22	60	1x1	1.735	60	1.861	1501
599377	250	3	BK,RD,WE,GN	0.52	22	60	1x1/0	1.789	60	1.915	1620
561248	350	3	BK,RD,WE	0.616	35	60	1x1	1.926	60	2.052	1901
555809	500	3	BK,RD,WE	0.736	34	60	1x1	2.184	60	2.31	2469
563589	500	3	BK,RD,WE	0.736	34	60	1x3/0	2.189	60	2.315	2563
555812	750	3	BK,RD,WE	0.908	53	70	1x1/0	2.608	75	2.766	3568
554282	1/0	4	BK,RD,BE,WE	0.336	10	50	1x4	1.384	50	1.49	957
555807	2/0	4	BK,RD,BE,WE	0.376	12	50	1x4	1.472	50	1.578	1109
554283	4/0	4	BK,RD,BE,WE	0.475	19	50	1x2	1.738	60	1.864	1657
679730	250	4	BK,RD,BE,WE	0.52	22	60	1x2	1.89	60	2.016	1932
554284	250	4	BK,RD,BE,WE	0.52	22	60	1x1	1.901	60	2.027	1939
554935	300	4	BK,RD,BE,WE	0.57	21	60	1x1	2.022	60	2.148	2186
555808	350	4	BK,RD,BE,WE	0.616	35	60	1x1/0	2.131	60	2.257	2472
554932	500	4	BK,RD,BE,WE	0.736	34	60	1x3/0	2.435	75	2.593	3330
555811	600	4	BK,RD,BE,WE	0.813	58	70	1x3/0	2.64	75	2.798	3895
560782	600	4	BK,RD,BE,WE	0.813	58	70	1x400	2.756	75	2.914	4174
554933	750	4	BK,RD,BE,WE	0.908	53	70	1x3/0	2.88	75	3.038	4664
563603	750	4	BK,RD,BE,WE	0.908	53	70	1x750	3.106	85	3.284	5330

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Strand count meets minimum number per ASTM
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 2 – Electrical and Engineering Data

Cond. Size	Conductor Number	Min. Bend Radius	Max Pull Tension	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/ Kcmil		Inches	Lbs	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
1/0	2	8.6	1267	0.167	0.208	0.044	120	135
3/0	2	10.2	2013	0.105	0.131	0.042	155	175
4/0	2	10.5	2539	0.084	0.105	0.041	180	205
300	2	12.9	3600	0.059	0.074	0.041	230	260
350	2	13.5	4200	0.051	0.064	0.04	250	280
1/0	3	9.5	1900	0.167	0.208	0.044	120	135
2/0	3	10.1	2395	0.133	0.166	0.043	135	150
3/0	3	11	3020	0.105	0.131	0.042	155	175
4/0	3	11.9	3808	0.084	0.105	0.041	180	205
250	3	13	4500	0.07	0.087	0.041	205	230
250	3	13	4500	0.07	0.087	0.041	205	230
250	3	13.4	4500	0.07	0.087	0.041	205	230
350	3	14.4	6300	0.051	0.064	0.04	250	280
500	3	16.2	9000	0.036	0.045	0.039	310	350
500	3	16.2	9000	0.036	0.045	0.039	310	350
750	3	19.4	13500	0.023	0.03	0.038	385	435
1/0	4	10.4	2534	0.167	0.208	0.044	96	108
2/0	4	11	3194	0.133	0.166	0.043	108	120
4/0	4	13	5078	0.084	0.105	0.041	144	164
250	4	14.1	6000	0.07	0.087	0.041	164	184
250	4	14.2	6000	0.07	0.087	0.041	164	184
300	4	15	7200	0.059	0.074	0.041	184	208
350	4	15.8	8400	0.051	0.064	0.04	200	224
500	4	18.2	12000	0.036	0.045	0.039	248	280
600	4	19.6	14400	0.03	0.038	0.039	272	308
600	4	20.4	14400	0.03	0.038	0.039	272	308
750	4	21.3	18000	0.023	0.03	0.038	308	348
750	4	23	18000	0.023	0.03	0.038	308	348

* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.
* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved