



Covered Line Wire With Crosslinked Polyethylene (XLPE)

Aluminum Conductor Covered with Black Crosslinked Polyethylene




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Conductors are solid or stranded compressed aluminum
2. **Insulation:** Black Crosslinked Polyethylene (XLPE)

APPLICATIONS AND FEATURES:

Aluminum alloy 1350-H19 or 6201 concentrically stranded. Covered with crosslinked polyethylene (XLP). Used primarily for, but not limited to, overhead secondary distribution lines. Installed on insulators, otherwise treated as a bare conductor. Crosslinked covered line wires have the below temperature ratings:

- Normal Service temperature of 90°C
- Emergency Overload of 130°C
- Short Circuit temperature of 250°C

SPECIFICATIONS:

- ASTM B230 Aluminum, 1350-H19 Wire for Electrical Purposes
- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ASTM B400 Standard Specification for Compact Round Concentric-Lay-Stranded, Aluminum 1350 Conductors
- ICEA S-70-547 Weather Resistant Polyethylene Covers Conductors





Table 1 – Weights and Measurements

Stock Number	Code Word	Phase Cond. Size AWG/Kcmil	Phase Strand No.	Phase Insul. Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft
TBA	Apple	6	Solid	30	0.222	31
TBA	Plum	6	7	30	0.238	56
457350	Pear	4	Solid	30	0.264	47
663570	Apricot	4	7	30	0.285	51
TBA	Cherry	2	Solid	45	0.348	78
104240	Peach	2	7	45	0.373	84
TBA	Nectarine	1	7	45	0.408	104
104257	Quince	1/0	7	60	0.477	136
TBA	Orange	2/0	7	60	0.522	167
104273	Fig	3/0	7	60	0.57	205
104281	Olive	4/0	7	60	0.626	253
104299	Pomegranate	4/0	19	60	0.632	247
TBA	Mulberry	266.8	19	60	0.694	305
104315	Annona	336.4	19	60	0.765	377
148130	Chinquapin	350	19	60	0.778	390
TBA	Molles	397.5	19	80	0.861	462
104331	Huckleberry	477	37	80	0.931	538
104349	Paw Paw	556.5	37	80	0.992	619
202127	Breadfruit	636	61	95	1.081	715
148460	Persimmon	795	61	95	1.186	877
202135	Grapefruit	1033.5	61	95	1.326	1128
TBA	Hornbeam	4	7	30	310	60
104547	Linden	2	7	45	406	99
104554	Oilnut	1/0	7	60	518	159
TBA	Waterash	2/0	7	60	567	195
104570	Shellbark	3/0	7	60	622	240
TBA	Planetree	4/0	7	60	683	297

All dimensions are nominal and subject to normal manufacturing tolerances
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.





Table 2 – Electrical and Engineering Data

Code Word	Phase Cond. Size AWG/Kcmil	Neutral Rated Breaking Strength lb	Allowable Ampacity In Air 75/90°C Amp
Apple	6	445	105
Plum	6	510	105
Pear	4	710	135
Apricot	4	790	140
Cherry	2	1100	180
Peach	2	1220	180
Nectarine	1	1470	210
Quince	1/0	1790	240
Orange	2/0	2260	280
Fig	3/0	2740	320
Olive	4/0	3450	370
Pomegranate	4/0	3620	370
Mulberry	266.8	4470	430
Annona	336.4	5540	495
Chinquapin	350	5751	506
Molles	397.5	6400	545
Huckleberry	477	7820	610
Paw Paw	556.5	8950	670
Breadfruit	636	10500	720
Persimmon	795	12900	825
Grapefruit	1033.5	16500	970
Hornbeam	4	1360	145
Linden	2	2160	190
Oilnut	1/0	3440	250
Waterash	2/0	4160	290
Shellbark	3/0	5240	335
Planetree	4/0	6610	385

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

