

## Multi-Conductor CU 600 V FR-XLPE Shielded Drain Wire PVC Jacket Control Cable Color Method 1 Table 2

Control Cable 600 Volt Copper Conductors, Flame Retardant Cross Linked Polyethylene (FR-XLPE) Insulation Shielded With Drain Wire Polyvinyl Chloride (PVC) Jacket, Control Cable Conductor Identification Method 1 Table 2. Silicone Free




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** 7 strands class B compressed bare copper per ASTM B3 and ASTM B8
- Insulation:** Flame Retardant Cross Linked Polyethylene (FR-XLPE)
- DrainWire:** Bare copper drain wire
- Filler:** Polypropylene filler on cables with 5 or less conductors
- Binder:** Polyester flat thread binder tape applied for cables with more than 5 conductors
- Shielding:** 5 mil copper Helically-Applied Tape shield
- Rip Cord:** Rip cord for ease of jacket removal
- Overall Jacket:** Polyvinyl Chloride (PVC) Jacket

### APPLICATIONS AND FEATURES:

Southwire's 600 Volt control cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. UL rated constructions can be used in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. UL rated constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- CSA *CSA marking is available upon request*
- ICEA S-58-679 Control Cable Conductor Identification Method 1 Table 2
- ICEA S-73-532 Standard for Control, Thermocouple Extension and Instrumentation Cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- VW-1 (Vertical-Wire) Flame Test



**SAMPLE PRINT LEGEND:****UL Listed**

{SQFTG} SOUTHWIRE E75755 {UL} XX AWG X/C XHHW-2 CDRS 90°C PVC JKT TYPE TC-ER SHIELDED 600V SUN. RES. DIRECT BURIAL {YYYY}

**Non UL Listed**

{SQFTG} SOUTHWIRE XX AWG X/C FR-XLPE CDRS 90°C PVC JKT SHIELDED 600V SUN. RES. DIRECT BURIAL {YYYY}



**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance	Min Bending Radius	Allowable Ampacity 75°C	Allowable Ampacity 90°C	Jacket Color
	AWG	No.	strands	inch	mil	mil	inch	lb / 1000ft	lb / 1000ft	Ω / 1000ft	Ω / 1000ft	Ω / 1000ft	inch	Amp	Amp	
12 AWG																
668743 <sup>^</sup>	12	2	7	0.088	30	45	0.412	72	122	1.662	2.002	0.054	4.9	25	30	Black
668737 <sup>^</sup>	12	4	7	0.088	30	45	0.477	118	187	1.662	2.002	0.054	5.7	20	24	Black
668739 <sup>^</sup>	12	12	7	0.088	30	60	0.762	300	467	1.662	2.002	0.054	9.1	12	15	Black
10 AWG																
606611 <sup>^</sup>	10	4	7	0.113	30	60	0.560	175	275	1.040	1.253	0.050	3.9	28	32	Black
662657	10	4	7	0.113	30	60	0.562	171	268	1.040	1.253	0.050	3.9	28	32	Black
616767 <sup>^</sup>	10	4	7	0.113	30	60	0.566	169	271	1.040	1.253	0.050	4.0	28	32	Black
662655 <sup>^</sup>	10	9	7	0.113	30	60	0.771	347	511	1.040	1.253	0.050	5.4	24	28	Black
662652 <sup>^</sup>	10	19	7	0.113	30	80	1.077	685	1020	1.040	1.253	0.050	12.9	17	20	Black
8 AWG																
662622 <sup>^</sup>	8	2	7	0.141	45	60	0.618	145	263	0.653	0.786	0.052	4.3	50	55	Black
668741 <sup>^</sup>	8	4	7	0.141	45	60	0.710	257	417	0.653	0.786	0.052	5.0	40	44	Black
662185!	8	4	7	0.141	45	60	0.720	267	426	0.653	0.786	0.052	8.6	40	44	Black
6 AWG																
662629 <sup>^</sup>	6	3	7	0.177	45	60	0.789	298	437	0.411	0.495	0.051	9.5	65	75	Black
662624	6	4	7	0.177	45	60	0.792	382	547	0.411	0.495	0.051	5.5	52	60	Black
4 AWG																
662638 <sup>^</sup>	4	4	7	0.225	45	80	0.946	595	833	0.258	0.310	0.048	6.6	68	76	Black

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

<sup>^</sup> UL listed part number

! Tinned copper drain wire

\* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements. Ampacities have been adjusted for stock numbers containing more than Three Current-Carrying Conductors.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

