



## Cable-in-Conduit (CIC) AL 600V UD Secondary SCH 40



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductors: Triplex 600 Volt USE-2 Underground Service Entrance per SPEC 83013
- Conduit: High-Density Polyethylene (HDPE)

### APPLICATIONS AND FEATURES:

Southwire's SIMpull® CIC has been utilized by end users in various applications, including the US Department of Transportation (DOT), the US Department of Energy (DOE), commercial constructions, EV infrastructure expansions, Utility grid-hardening efforts, airports, mass transit, renewables, petrochemical, agriculture, and data centers. Manufactured by continuously extruding HDPE loosely around the cable assembly with no adhesion between the conduit and the cable, thus leaving the cables free in the conduit. Lubrication is applied to the cable, allowing for cables to be pulled out and replaced if necessary.

### SPECIFICATIONS:

- ASTM D3350 Standard Specification for Polyethylene Plastics Pipe and Fittings Materials
- ASTM D3485 Standard Specification for Coilable High Density Polyethylene (HDPE) Cable in Conduit (CIC)
- ASTM F2160 Standard Specification for Solid Wall High Density Polyethylene (HDPE) Conduit Based on Controlled Outside Diameter (OD)
- UL 854 Service Entrance Cable
- UL 1990 Standard for Nonmetallic Underground Conduit with Conductors
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

### SAMPLE PRINT LEGEND:

{SQFTG} FEET (LOGO) SOUTHWIRE CABLE IN CONDUIT (UL) HDPE X.XX" SCH40 NEMA TC 7 / ASTM F2160 (NESC) {MMM/DD/YYYY} {MACH/SHFT/OP}





**Table 1 – Physical and Electrical Data**

Stock Number	Description	Cable Color	Duct Nominal Size	Duct Nominal Outside Dia.	Duct Min. Wall Thickness	Duct Nominal Inside Dia.	Duct Min. Bending Radius	Duct Max. Pull Tension	Duct Color	Approx. Cable and Duct Weight
			inch	inch	inch	inch	inch	lb		lb/1000ft
632891	3 x 4 AWG AL UD Secondary	BK, BK, BK/YW	1.25	1.660	0.140	1.360	18	1420	BK/3-RD Stripes	484
631149	3 x 1/0 AWG AL UD Secondary	BK, BK, BK/YW	1.50	1.900	0.145	1.590	21	1700	Black	888
633183	3 x 4/0 AWG AL UD Secondary	BK, BK, BK/YW	2.00	2.375	0.154	2.047	26	2280	BK/3-RD Stripes	1555
630196	2 x 350 AWG 1 x 4/0 AL UD Secondary	BK, BK, BK/YW	2.50	2.875	0.203	2.445	32	3615	BK/3-RD Stripes	1832

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◊ Cable marked with this symbol is a standard stock item

**Cable Specification**

Stock Number	Cable Specification
632891 / 631149 / 633183	<a href="#">SPEC 83013</a>

**Cell Classification for HDPE Conduit**

Property	Test Method	Value
Density	D4883	0.953 g/cc
Melt Index	D1238	0.25 g/10 min
Flexural Modulus	D790	168,000 psi
Tensile Strength	D638	3900 yield @ 2 in/min
SP-NCLS ESCR	F2136	>1000 hrs
Hydrostatic Design Basis	D2837	N/A

- (PE436580C-BK), (PE436580E-Colors)

CIC Labor Saving Calculator

