



Cable-in-Conduit (CIC) AL UD Primary EPEC-40/SCH 40



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

Conduit: High-Density Polyethylene (HDPE)

APPLICATIONS AND FEATURES:

Southwire's SIMpull® CIC has been utilized by end users in various applications, including the US Department of Transportation (DOT), the US Department of Energy (DOE), commercial constructions, EV infrastructure expansions, Utility grid-hardening efforts, airports, mass transit, renewables, petrochemical, agriculture, and data centers. Manufactured by continuously extruding HDPE loosely around the cable assembly with no adhesion between the conduit and the cable, thus leaving the cables free in the conduit. Lubrication is applied to the cable, allowing for cables to be pulled out and replaced if necessary. May be installed directly buried or encased in concrete as permitted by The National Electrical Code® Article 353. For above ground applications, HDPE conduit must be encased in a minimum of 2 inches of concrete.

SPECIFICATIONS:

- ASTM D3350 Standard Specification for Polyethylene Plastics Pipe and Fittings Materials
- ASTM D3485 Standard Specification for Coilable High Density Polyethylene (HDPE) Cable in Conduit (CIC)
- ASTM F2160 Standard Specification for Solid Wall High Density Polyethylene (HDPE) Conduit Based on Controlled Outside Diameter (OD)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661
- NEMA TC-7 Smooth-Wall Coilable Electrical Polyethylene Conduit

SAMPLE PRINT LEGEND:

{SQFTG} FEET (LOGO) SOUTHWIRE CABLE IN CONDUIT HDPE X" EPEC-40 NEMA TC 7 / SCH40 ASTM F2160 (NEC)
{MMM/DD/YYYY} {MACH/SHFT/OP}





Table 1 – Physical and Electrical Data

Stock Number	Description	Cable Color	Duct Nominal Size	Duct Nominal Outside Dia.	Duct Min. Wall Thickness	Duct Nominal Inside Dia.	Duct Min. Bending Radius	Duct Max. Pull Tension	Duct Color	Approx. Cable and Duct Weight
			inch	inch	inch	inch	inch	lb		lb/1000ft
616990	2-7 CPRESS AL 15KV 175 mils 100% TRXLP 90C 10x14CN POLY JACKET/RED STRIPE	BK/RD Stripe	1.50	1.900	0.145	1.590	21	1700	BK/3-RD Stripes	826
630474	2 SOL AL 15KV 220 mils 133% TRXLP 90C 10x14CN HiDri Plus POLY JACKET/RED STRIPE	BK/RD Stripe	1.50	1.900	0.145	1.590	21	1700	BK/3-RD Stripes	865
630135	2-7 MB CPRESS AL 15KV 220 mils 133% TRXLP 90C 10x14CN POLY JACKET/RED STRIPE	BK/RD Stripe	1.50	1.900	0.145	1.590	21	1700	BK/3-RD Stripes	888
633561	1/0CR MBAL 15KV220E 16x14 PES 1-1/2" EPEC-40 BLACK-RED STRIPES HDPE CIC	BK/RD Stripe	1.50	1.900	0.145	1.590	21	1700	BK/3-RD Stripes	888
630918	1/0-19 MB CPRESS AL 15KV 220 mils 133% EPR 105C 16x14CN POLY JACKET/RED STRIPE	BK/RD Stripe	2.00	2.375	0.154	2.047	26	2280	BK/3-RD Stripes	1214
634368	4/0-19 MB CPRESS AL 15KV 220 mils 133% TRXLP 90C 20x12CN POLY JACKET/RED STRIPE	BK/RD Stripe	2.00	2.375	0.154	2.047	26	2280	RD	1550
632916	1/0-19 MB CPRESS AL 25KV 260 mils 100% EPR 105C 16x14CN POLY JACKET/RED STRIPE	BK/RD Stripe	2.00	2.375	0.154	2.047	26	2280	RD	1284
630141	1/0 CR MBAL 25KV 260X 16X14 PES 2" EPEC-40 BLACK-RED STRIPES HDPE CIC	BK/RD Stripe	2.00	2.375	0.154	2.047	26	2280	BK/3-RD Stripes	1284
456483	4/0-19 CR MBAL 25KV 260 EPR 13x10 PES 2" EPEC-40 RED HDPE CIC	BK/RD Stripe	2.00	2.375	0.154	2.047	26	2280	BK/3-RD Stripes	1284
631158	4/0-19 MB CPRESS AL 35KV 345 mils 100% EPR 105C 11x14CN POLY JACKET/RED STRIPE	BK/RD Stripe	2.50	2.875	0.203	2.445	32	3615	BK/3-RD Stripes	1927
634068	4/0-19 MB CPRESS AL 35KV 345 mils 100% TRXLP 90C 11x14CN POLY JACKET/RED STRIPE	BK RD/Stripe	2.50	2.875	0.203	2.445	32	3615	BK	1927

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item





Cell Classification for HDPE Conduit

Property	Test Method	Value
Density	D4883	0.953 g/cc
Melt Index	D1238	0.25 g/10 min
Flexural Modulus	D790	168,000 psi
Tensile Strength	D638	3900 yield @ 2 in/min
SP-NCLS ESCR	F2136	>1000 hrs
Hydrostatic Design Basis	D2837	N/A

- (PE436580C-BK), (PE436580E-Colors)

CIC Labor Saving
Calculator



We've got it.
MADE IN AMERICA