CU Compressed 15kV NLEPR Insulation 133% IL Black SIM-PVC Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Single Conductor Copper, 220 Mil No Lead Ethylene Propylene Rubber (NL-EPR) Lead-Free EAM 133% Insulation Level, Tape Shield, SIM*pull* Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and B8 (tinned copper optional per ASTM B33)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 15kV, 133% insulation level, 220 mil No Lead Ethylene Propylene Rubber (NL-EPR) / No-Lead Ethylene Alkene Copolymer (EAM)
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** SIM*pull*® Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 15kV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial when installed with a grounding conductor in close proximity that conforms to NEC section 311.36 and 250.4(A)(5), aerially supported by a messenger and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -25°C for cold bend and cold impact and marked with "LTGG" when CSA listed. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lb/ft maximum sidewall pressure. These cables feature sunlight and moisture resistance, exceptional corona resistance, resistance to most chemicals, oils and acids and are flame retardant. Cable Tray CT rated 1/0 AWG and larger.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No.230 Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)

We've got it MADE IN AMERICA

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

SOUTHWIRE SIMpull{R} POWER CABLE MASTER-DESIGN {UL} XXX KCMIL CU 220 MILS NL-EPR 15KV 133% INS LEVEL 25%TS MV-105 FOR CT USE SUN RES {NESC} -- {CSA} XXX KCMIL CU X.XXmm (220 mils) NL-EPR 15KV 133% INS LEVEL 25%TS MV68.10 SR 105{D}C FT4 -25{D}C LTDD -- PAT www.patentSW.com -- RoHS

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size
	AWG/ Kcmil	No. of Strands	inch	inch	inch	mil	inch	lb/1000ft	lb/1000ft	lb	inch	inch
953638◊	2	7	0.283	0.761	0.821	80	1.001	276	648	530	12	2.5
955104	1	19	0.322	0.8	0.86	80	1.04	333	726	669	12.5	2.5
955989◊	1/0	19	0.362	0.84	0.9	80	1.08	403	820	844	13	2.5
955997◊	2/0	19	0.405	0.884	0.944	80	1.124	492	934	1064	13.5	3
956003	3/0	19	0.456	0.934	0.994	80	1.174	603	1074	1342	14.1	3
956011◊	4/0	19	0.512	0.99	1.05	80	1.23	744	1247	1692	14.8	3
956029◊	250	37	0.558	1.044	1.104	80	1.284	866	1403	2000	15.4	3.5
956037◊	350	37	0.661	1.147	1.207	80	1.387	1183	1780	2800	16.6	3.5
956045◊	500	37	0.789	1.252	1.312	80	1.492	1654	2313	4000	17.9	4
139631**	500	37	0.789	1.275	1.335	80	1.515	1656	2328	4000	18.2	4
643755◊	600	61	0.866	1.336	1.396	80	1.576	1970	2682	4800	18.9	4
956052◊	750	61	0.968	1.464	1.524	110	1.764	2443	3329	6000	21.2	4.5
956060◊	1000	61	1.117	1.613	1.673	110	1.913	3226	4209	8000	23	5
581886	1250	91	1.25	1.78	1.84	110	2.08	4011	5115	10000	25	5.5
567443	1500	91	1.37	1.93	1.99	110	2.23	4795	6014	12000	26.8	6
550811	2000	127	1.583	2.143	2.203	110	2.443	6356	7724	16000	29.3	6.5

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
Conduit size based on 3 phase 40% fill-factor without ground
** Tinned Copper

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.221	0.045	0.051	0.581+j0.462	0.222+j0.057	2575	150/160	165/185
1	0.128	0.175	0.042	0.049	0.536+j0.444	0.176+j0.054	2696	170/185	185/210
1/0	0.102	0.139	0.039	0.047	0.500+j0.427	0.140+j0.052	2820	195/210	215/240
2/0	0.082	0.112	0.036	0.045	0.473+j0.409	0.113+j0.051	2956	220/235	245/275
3/0	0.064	0.087	0.033	0.043	0.447+j0.391	0.088+j0.049	3111	250/270	285/315
4/0	0.051	0.07	0.031	0.042	0.428+j0.371	0.071+j0.047	3284	285/305	325/360
250	0.043	0.059	0.029	0.041	0.415+j0.353	0.060+j0.046	3452	310/335	360/400
350	0.031	0.043	0.025	0.039	0.393+j0.323	0.044+j0.044	3771	375/400	435/490
500	0.021	0.03	0.021	0.036	0.373+j0.294	0.031+j0.042	4096	450/485	535/600
500	0.022	0.032	0.022	0.037	0.374+j0.289	0.033+j0.042	4167	450/485	535/600
600	0.018	0.026	0.019	0.035	0.363+j0.274	0.027+j0.040	4356	488/525	589/658
750	0.014	0.021	0.019	0.035	0.347+j0.248	0.022+j0.041	4753	545/585	670/745
1000	0.011	0.018	0.017	0.034	0.332+j0.221	0.019+j0.039	5215	615/660	770/860
1250	0.008	0.014	0.016	0.033	0.315+j0.196	0.015+j0.039	5732	685/735	870/975
1500	0.007	0.014	0.016	0.033	0.303+j0.177	0.015+j0.038	6197	780/835	1005/1120
2000	0.005	0.013	0.014	0.032	0.286+j0.154	0.015+j0.037	6857	895/960	1170/1320

* NEC ampacities are based on:
* For Duct: Table 310.60(C)(11) Detail 1.
* For Free Air: Table 310.60(C)(3).
* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
* Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center..
* Capacitive Reactance is between Phase-to-Shield.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved