CU Compressed 15kV TRXLPE Insulation 133% IL Black PVC Jacket. MV 105 - Sunlight Resistant - For Direct Burial

Type MV-105 Single Conductor Copper, 220 Mils Tree Retardant Cross Linked Polyethylene (TRXLPE) 133% Insulation Level, Tape Shield, SIMpull Polyvinyl Chloride (PVC) Jacket.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 220 Mils Tree Retardant Cross Linked Polyethylene (TRXLPE) 133% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** SIMpull® Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 15KV cables are suited for use in wet and dry areas, conduits, ducts, troughs and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -40°C for cold bend. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE SIMpull® POWER CABLE {UL} XXX KCMIL CU 220 MILS XLP 15KV 133% INS LEVEL 25%TS MV-105 SUN. RES. {NESC} PAT www.patentSW.com

Copyright © 2026 Southwire Company, LLC. All Rights Reserved
UPDATED: June 3, 2025, 6:54 p.m.UTC REVISION: 1.000.005

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size
	AWG/ Kcmil	No. of Strands	inch	inch	inch	mil	inch	lb/1000ft	lb/1000ft	lb	inch	inch
673433	2	7	0.283	0.761	0.821	80	1.001	276	611	530	12	2.5
673432	1	19	0.322	0.8	0.86	80	1.04	333	687	669	12.5	2.5
673431	1/0	19	0.362	0.84	0.9	80	1.08	403	778	844	13	2.5
673430	2/0	19	0.405	0.884	0.944	80	1.124	492	889	1064	13.5	3
641179	2/0	19	0.405	0.884	0.944	80	1.124	493	893	1064	13.5	3
673429	3/0	19	0.456	0.934	0.994	80	1.174	598	1021	1342	14.1	3
673428	4/0	19	0.512	0.99	1.05	80	1.23	742	1194	1692	14.8	3
673427	250	37	0.558	1.044	1.104	80	1.284	865	1347	2000	15.4	3.5
673425	350	37	0.661	1.147	1.207	80	1.387	1182	1717	2800	16.6	3.5
673415	500	37	0.789	1.252	1.312	80	1.492	1653	2243	4000	17.9	4
669891	750	61	0.968	1.464	1.524	110	1.764	2443	3245	6000	21.2	4.5
TBA	1000	61	1.117	1.613	1.673	110	1.913	3226	4265	8000	23	5
TBA	1250	91	1.25	1.75	1.81	110	2.05	4008	5145	10000	24.6	5.5
TBA	1500	91	1.37	1.87	1.93	110	2.17	4790	6010	12000	26	5.5
TBA	2000	127	1.583	2.083	2.143	110	2.383	6351	7718	16000	28.6	6.5

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Conduit size based on 3 phase 40% fill-factor without ground

§ CSA listed
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance	Positive Sequence Impedance	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.221	0.059	0.051	0.581+j0.462	0.222+j0.057	2575	150/160	165/185
1	0.128	0.175	0.054	0.049	0.536+j0.444	0.176+j0.054	2696	170/185	185/210
1/0	0.102	0.139	0.05	0.047	0.500+j0.427	0.140+j0.052	2820	195/210	215/240
2/0	0.082	0.112	0.047	0.045	0.473+j0.409	0.113+j0.051	2956	220/235	245/275
2/0	0.082	0.112	0.047	0.045	0.473+j0.409	0.113+j0.051	2956	220/235	245/275
3/0	0.064	0.087	0.043	0.043	0.447+j0.391	0.088+j0.049	3111	250/270	285/315
4/0	0.051	0.07	0.04	0.042	0.428+j0.371	0.071+j0.047	3284	285/305	325/360
250	0.043	0.059	0.037	0.041	0.415+j0.353	0.060+j0.046	3452	310/335	360/400
350	0.031	0.043	0.033	0.039	0.393+j0.323	0.044+j0.044	3771	375/400	435/490
500	0.021	0.03	0.028	0.036	0.373+j0.294	0.031+j0.042	4096	450/485	535/600
750	0.014	0.021	0.024	0.035	0.347+j0.248	0.022+j0.041	4753	545/585	670/745
1000	0.011	0.018	0.022	0.034	0.332+j0.221	0.019+j0.039	5215	615/660	770/860
1250	0.008	0.014	0.02	0.033	0.317+j0.200	0.015+j0.038	5639	685/735	870/975
1500	0.007	0.014	0.018	0.032	0.308+j0.184	0.015+j0.038	6011	780/835	1005/1120
2000	0.005	0.013	0.016	0.031	0.290+j0.159	0.014+j0.036	6671	895/960	1170/1320

* NEC ampacities are based on:
* For Duct: Table 310.60(C)(11) Detail 1.
* For Free Air: Table 310.60(C)(3).
* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.
* Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center..
* Capacitive Reactance is between Phase-to-Shield.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved